

## Clipsal Brand



## ARGUS Standard 360° False ceiling indoor movement detector - 2 channel



Version	Art. no.
white	<b>753CF2</b>

Ceiling indoor movement detector with 360° surface monitoring.

- Attractive small sensor
  - The sensor detects the movement in the room, switches the light on and leaves it on until no further movement is detected
  - Quick and easy settings for switch on time, sensitivity and light sensitivity levels
- The device consists of the sensor and a power box with a permanently attached interconnecting cable (length 35 cm). Sensor is installed in 63 mm ceiling openings.

**Functions:**

- Movement detection via passive infra-red technology
- 2 outputs (e.g. 1x light + 1x fan)

**Mains voltage:** AC 220-240 V, 50/60 Hz

**Nominal power:****Output 1**

- LED lamps: 100 W
- Incandescent lamps AC 230 V: 1000 W
- Halogen lamps AC 230 V: 900 W
- Halogen with electronic transformer: 250 VA
- Halogen with iron core transformer: 500 VA
- Fluorescent tubes: 200 VA
- Compact fluorescent lamps: 100 W

**Output 2**

- Relay switching capacity: AC 250 V, 5 A (cosφ=1)
- Motor: 100 W

**Upstream fuse:** 6 A

**Power consumption:** < 1.5 W

**Angle of detection:** 360°

**Range:** Radius of max. 3.5 m (at 2.5 m mounting height)

**Light sensor:** 5–1000 Lux

**Time setting:**

**Time 1:** from approx. 30 s to approx. 30 min

**Time 2:** from approx. 10 s to approx. 15 min

**Switching mode:** Automatic

**Connection:** 3-wire, neutral conductor **required**

**Operating temperature:** at room temperature

**IP protection rating:** IP 20

**Colour:** white

**Dimensions (LxWxH):**

Sensor: Ø 80 x 36 mm

Power box: 123 x 56 x 34 mm