



# ÖVE-CERTIFICATE

including the entitlement to use the Austrian Safety Mark



Certificate No.: **4900-047-09**

Valid from: 2024 06 23  
until: 2025 07 09

The Austrian Electrotechnical Association (OVE) hereby grants the right to the company mentioned below to label the listed products with the Austrian Safety Mark.

Certificate holder: **Schneider Electric Industries SAS**  
35, rue Joseph Monier  
92500 Rueil-Malmaison  
France

Product: **Two pole socket outlet with side earthing contacts**

The products submitted by the applicant were type tested in accordance with the requirements of the technical standards and specifications listed in this certificate. OVE certifies the conformity of the listed products and those products manufactured strictly identical to the submitted ones (EN ISO/IEC 17067, Conformity Assessment Scheme Type 5).

The manufacturing process and the products are subject to ongoing surveillance based on harmonized European procedures. This certificate has been issued under the presumption and conditional on the fact that the certificate holder holds all necessary legal rights with regard to the product, presented for the testing and certification.

Results of testing are shown in file No(s): **TGM-VA EE 33388C**

**Österreichischer Verband für Elektrotechnik**  
Head of OVE Certification

*T. Neumayer*  
Digitally signed by T. Neumayer  
Email=[t.neumayer@ove.at](mailto:t.neumayer@ove.at)  
Dipl.-Ing. T. Neumayer



Wien, 2024 06 25

## **OVE Certification**

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.



**Manufacturer:**

Schneider Electric Industries SAS  
35, rue Joseph Monier  
92500 Rueil-Malmaison  
France

**Factory location(s):**

Merten GmbH  
Fritz Kotz Straße 8  
51674 Wiehl-Bornig  
Germany

**Tested and certified according to:**

ÖVE/ÖNORM IEC 60884-1:2005-09-01  
ÖVE/ÖNORM E 8684-1:2010-03-01

**Product: Two pole socket outlet with side earthing contacts**

**Type designation:**

*Rating:*

**Trademark:**

**270**

Rated voltage: AC 250 V  
Rated current: 16 A  
SCHUKO socket-outlet  
screw-type terminals, flush-type  
see typelist

MERTEN/SCHNEIDER ELECTRIC

**OVE Certification**

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

## Typelist

### System M (Thermo/Duro)

**270/2371** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert

**270/2373** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

**270/2376** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid

**270/2376 IP44** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid and gasket

**270/2374 IP44** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 44

Insert with hinged lid and improved protection against accidental contact

**270/2374** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with hinged lid and improved protection against accidental contact

**270/2300** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

**270/2301** MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet

### OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

**270/2309** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Central plate with labelling field and control light incl. Modul 2003

**270/2309** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with labelling field and improved protection against accidental contact

**270/2474** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with hinged lid and labelling field

**270/2485** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with improved protection against accidental contact

**270/2496** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with labelling field and improved protection against accidental contact

**270/2334** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Central plate with light opening and LED display lighting incl. Modul 2334

**270/2300-35 (M-Creativ)** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with transparent cover and improved protection against accidental contact

### **System Design (Thermo/Duro)**

**270/2375** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert

### **OVE Certification**

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

**270/2377** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with improved protection against accidental contact

**270/2372** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with hinged lid

**270/2379** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with labelling field

**270/2378 IP44** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 44  
Insert with hinged lid, gasket and improved protection against accidental contact

**270/2378** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with hinged lid and improved protection against accidental contact

**270/2306** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with improved protection against accidental contact, Trarcent

**270/2379** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with labelling field and control light incl. Modul 2003

**270/2308** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with labelling field and improved protection against accidental contact

**270/2478** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with hinged lid and labelling field

### **OVE Certification**

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

**270/2476** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with improved protection against accidental contact

**270/2477** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert 45° with labelling field and improved protection against accidental contact

### System Design D-Life (Thermo/metal)

**270/NHA2920902 (thermo)** MERTEN/SCHNEIDER ELECTRIC  
**270/NHA2922002 (metal)**  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with improved protection against accidental contact

**270/NHA5195702** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 44  
Insert with hinged lid, gasket and improved protection against accidental contact

### AQUADESIGN

**270/2330 IP44** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 44  
Insert with hinged lid and improved protection against accidental contact

**270/2335** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 20  
Insert with improved protection against accidental contact

**270/2330 IP44** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 44  
Insert with hinged lid, labelling field and improved protection against accidental contact

**270/2330 IP44** MERTEN/SCHNEIDER ELECTRIC  
Rated voltage: AC 250 V  
Rated current: 16 A  
IP 44  
Insert with hinged lid, lockable and improved protection against accidental contact

### OVE Certification

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.

**Renova**

**270/EAV54699**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Insert with improved protection against accidental contact

**Anti vandalism**

**270/S1B7217902**

MERTEN/SCHNEIDER ELECTRIC

Rated voltage: AC 250 V

Rated current: 16 A

IP 20

Socket-outlet with improved protection against accidental contact

**OVE Certification**

Accredited by the Austrian National Accreditation Body as Certification Body for products within the scope as given in the official decree and published under <https://akkreditierung-austria.gv.at>.