

Product Compliance Certificate



Certificate Number: 5020787S210027-01A

Notice to Authorities:

This certificate indicates that a third party Accredited Body has tested and verified that the products listed comply with the relevant harmonized standards to directives listed on this certificate. The manufacturer may indicate compliance to said directive by signing a Declaration of Conformity to products identical to the tested samples.

In addition, annual factory inspection has been performed for further verification of compliance. Intertek requests all whom may be concerned to allow products entry into the European market without delay or prejudice. The applicant may rightfully use this certificate to mark their products with the ETL^{EU} mark identified above.

Intertek is a leading international provider of quality and safety services to a wide range of global and local industries. Intertek's laboratories are included in IECEE CB scheme as operational CBTL and hold several local accreditations.

For further information:
 Email: ETL_EU@intertek.com
 Website: www.intertek.com/ETLeu

Or Certification Body:
 Intertek Testing Services Ltd.
 Shanghai
 West Area, 2nd Floor, No. 707,
 Zhangyang Road, China
 (Shanghai) Pilot Free Trade
 Zone, Shanghai, P. R. China

Accredited by China National
 Accreditation Service for
 Conformity Assessment
(CNAS C058-P)

Applicant

Schneider Electric South Africa (Pty) Ltd
 9 Old Pretoria Main Road, Halfway Gardens, Midrand 1685, Gauteng
 South Africa

Manufacturing Site

SCHNEIDER ELECTRIC INDIA PRIVATE LIMITED
 No. 172 POONAMALLEE BY PASS ROAD, POONAMALLEE 600056,
 CHENNAI Tamil Nadu
 India

Product Name

Moulded Case Circuit-Breakers

Trademark



Model Number(s)

iC60N ** (A9F7****)
 Details see attachment

Description

Ue= 240V~(1P), 415V~(2P, 3P, 4P)
 In= 1, 2, 3, 4, 6, 10, 16, 20, 25, 32, 40, 50, 63A
 Icu= 10kA, Ics= 7,5kA, Cat. A, Ref. temperature: +30°C, +50°C

Test Report No

210202036SHA-001

Standards/Directives

EN 60947-2:2017+A1:2020
 IEC 60947-2:2016+A1:2019

Issued Date

October 15, 2021

Validity

October 14, 2026

Maximum 5 years or the validity limitation of the standards/directives used, whichever is sooner.

If the product is to be marketed in different European countries, it must be provided with a certified plug appropriate for each country. Safety related parts of the user instructions shall be written in a language acceptable to the country where the product is to be used.

This certificate, which includes production control, is considered to constitute sufficient support for an EC Declaration of Conformity and CE marking of the product according to the Low Voltage Directive 2014/35/EU. Other EU directives may apply.

Certification procedure SMS-ETLeu-OP-19

Product certification scheme type: Type testing + Initial factory inspection + Surveillance after certification


 Gary

This certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement and in this Certificate. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement. They are not for the purpose of production quality control and do not relieve the Client of their obligation in this respect.



Attachment to Certificate Number: 5020787S210027-01A

The type/model list:

	1-pole	2-pole	3-pole	4-pole
iC60N B 1A	A9F73101	A9F73201	A9F73301	A9F73401
iC60N B 2A	A9F73102	A9F73202	A9F73302	A9F73402
iC60N B 3A	A9F73103	A9F73203	A9F73303	A9F73403
iC60N B 4A	A9F73104	A9F73204	A9F73304	A9F73404
iC60N B 6A	A9F76106	A9F76206	A9F76306	A9F76406
iC60N B 10A	A9F76110	A9F76210	A9F76310	A9F76410
iC60N B 16A	A9F76116	A9F76216	A9F76316	A9F76416
iC60N B 20A	A9F76120	A9F76220	A9F76320	A9F76420
iC60N B 25A	A9F76125	A9F76225	A9F76325	A9F76425
iC60N B 32A	A9F76132	A9F76232	A9F76332	A9F76432
iC60N B 40A	A9F76140	A9F76240	A9F76340	A9F76440
iC60N B 50A	A9F76150	A9F76250	A9F76350	A9F76450
iC60N B 63A	A9F76163	A9F76263	A9F76363	A9F76463
iC60N C 1A	A9F74101	A9F74201	A9F74301	A9F74401
iC60N C 2A	A9F74102	A9F74202	A9F74302	A9F74402
iC60N C 3A	A9F74103	A9F74203	A9F74303	A9F74403
iC60N C 4A	A9F74104	A9F74204	A9F74304	A9F74404
iC60N C 6A	A9F77106	A9F77206	A9F77306	A9F77406
iC60N C 10A	A9F77110	A9F77210	A9F77310	A9F77410
iC60N C 16A	A9F77116	A9F77216	A9F77316	A9F77416
iC60N C 20A	A9F77120	A9F77220	A9F77320	A9F77420
iC60N C 25A	A9F77125	A9F77225	A9F77325	A9F77425
iC60N C 32A	A9F77132	A9F77232	A9F77332	A9F77432
iC60N C 40A	A9F77140	A9F77240	A9F77340	A9F77440
iC60N C 50A	A9F77150	A9F77250	A9F77350	A9F77450
iC60N C 63A	A9F77163	A9F77263	A9F77363	A9F77463
iC60N D 1A	A9F75101	A9F75201	A9F75301	A9F75401
iC60N D 2A	A9F75102	A9F75202	A9F75301	A9F75401
iC60N D 3A	A9F75103	A9F75203	A9F75301	A9F75401
iC60N D 4A	A9F75104	A9F75204	A9F75301	A9F75401
iC60N D 6A	A9F75106	A9F75206	A9F75306	A9F75406
iC60N D 10A	A9F75110	A9F75210	A9F75310	A9F75410
iC60N D 16A	A9F75116	A9F75216	A9F75316	A9F75416
iC60N D 20A	A9F75120	A9F75220	A9F75320	A9F75420
iC60N D 25A	A9F75125	A9F75225	A9F75325	A9F75425
iC60N D 32A	A9F75132	A9F75232	A9F75332	A9F75432
iC60N D 40A	A9F75140	A9F75240	A9F75340	A9F75440
iC60N D 50A	A9F75150	A9F75250	A9F75350	A9F75450
iC60N D 63A	A9F75163	A9F75263	A9F75363	A9F75463

This certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement and in this Certificate. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement. They are not for the purpose of production quality control and do not relieve the Client of their obligation in this respect.