

## Product Compliance Certificate



**Certificate Number: 5020856S210028-01A**

### Notice to Authorities:

This certificate indicates that a third party Accredited Body has tested and verified that the products listed comply with the relevant harmonized standards to directives listed on this certificate. The manufacturer may indicate compliance to said directive by signing a Declaration of Conformity to products identical to the tested samples.

In addition, annual factory inspection has been performed for further verification of compliance. Intertek requests all whom may be concerned to allow products entry into the European market without delay or prejudice. The applicant may rightfully use this certificate to mark their products with the ETL<sup>EU</sup> mark identified above.

Intertek is a leading international provider of quality and safety services to a wide range of global and local industries. Intertek's laboratories are included in IECEE CB scheme as operational CBTL and hold several local accreditations.

For further information:  
Email: [ETL.EU@intertek.com](mailto:ETL.EU@intertek.com)  
Website: [www.intertek.com/ETLeu](http://www.intertek.com/ETLeu)

Or Certification Body:  
Intertek Testing Services Ltd.  
Shanghai  
West Area, 2<sup>nd</sup> Floor, No. 707,  
Zhangyang Road, China  
(Shanghai) Pilot Free Trade  
Zone, Shanghai, P. R. China

Accredited by China National  
Accreditation Service for  
Conformity Assessment  
(CNAS C058-P)

### Applicant

Schneider Electric South Africa (Pty) Ltd  
9 Old Pretoria Main Road, Halfway Gardens, Midrand 1685, Gauteng  
South Africa

### Manufacturing Site

MERLIN GERIN ALES  
16 Boulevard CHARLES PEGUY, 30319 ALES CEDEX, ALES  
France

### Product Name

**Moulded Case Circuit-Breakers**

### Trademark



### Model Number(s)

iC60N \*\* (A9F7\*\*\*\*)  
Details see attachment

### Description

Ue= 240V~(1P), 415V~(2P, 3P, 4P)  
In= 1, 2, 3, 4, 6, 10, 16, 20, 25, 32, 40, 50, 63A  
Icu= 10kA, Ics= 7,5kA, Cat. A, Ref. temperature: +30°C, +50°C

### Test Report No

210202036SHA-001

### Standards/Directives

EN 60947-2:2017+A1:2020  
IEC 60947-2:2016+A1:2019

### Issued Date

October 15, 2021

### Validity

October 14, 2026  
Maximum 5 years or the validity limitation of the standards/directives used, whichever is sooner.

If the product is to be marketed in different European countries, it must be provided with a certified plug appropriate for each country. Safety related parts of the user instructions shall be written in a language acceptable to the country where the product is to be used.

This certificate, which includes production control, is considered to constitute sufficient support for an EC Declaration of Conformity and CE marking of the product according to the Low Voltage Directive 2014/35/EU. Other EU directives may apply.

Certification procedure SMS-ETLeu-OP-19

Product certification scheme type: Type testing + Initial factory inspection + Surveillance after certification

  
Gary Hu

**Attachment to Certificate Number: 5020856S210028-01A**

**The type/model list:**

|             | 1-pole   | 2-pole   | 3-pole   | 4-pole   |
|-------------|----------|----------|----------|----------|
| iC60N B 1A  | A9F73101 | A9F73201 | A9F73301 | A9F73401 |
| iC60N B 2A  | A9F73102 | A9F73202 | A9F73302 | A9F73402 |
| iC60N B 3A  | A9F73103 | A9F73203 | A9F73303 | A9F73403 |
| iC60N B 4A  | A9F73104 | A9F73204 | A9F73304 | A9F73404 |
| iC60N B 6A  | A9F76106 | A9F76206 | A9F76306 | A9F76406 |
| iC60N B 10A | A9F76110 | A9F76210 | A9F76310 | A9F76410 |
| iC60N B 16A | A9F76116 | A9F76216 | A9F76316 | A9F76416 |
| iC60N B 20A | A9F76120 | A9F76220 | A9F76320 | A9F76420 |
| iC60N B 25A | A9F76125 | A9F76225 | A9F76325 | A9F76425 |
| iC60N B 32A | A9F76132 | A9F76232 | A9F76332 | A9F76432 |
| iC60N B 40A | A9F76140 | A9F76240 | A9F76340 | A9F76440 |
| iC60N B 50A | A9F76150 | A9F76250 | A9F76350 | A9F76450 |
| iC60N B 63A | A9F76163 | A9F76263 | A9F76363 | A9F76463 |
| iC60N C 1A  | A9F74101 | A9F74201 | A9F74301 | A9F74401 |
| iC60N C 2A  | A9F74102 | A9F74202 | A9F74302 | A9F74402 |
| iC60N C 3A  | A9F74103 | A9F74203 | A9F74303 | A9F74403 |
| iC60N C 4A  | A9F74104 | A9F74204 | A9F74304 | A9F74404 |
| iC60N C 6A  | A9F77106 | A9F77206 | A9F77306 | A9F77406 |
| iC60N C 10A | A9F77110 | A9F77210 | A9F77310 | A9F77410 |
| iC60N C 16A | A9F77116 | A9F77216 | A9F77316 | A9F77416 |
| iC60N C 20A | A9F77120 | A9F77220 | A9F77320 | A9F77420 |
| iC60N C 25A | A9F77125 | A9F77225 | A9F77325 | A9F77425 |
| iC60N C 32A | A9F77132 | A9F77232 | A9F77332 | A9F77432 |
| iC60N C 40A | A9F77140 | A9F77240 | A9F77340 | A9F77440 |
| iC60N C 50A | A9F77150 | A9F77250 | A9F77350 | A9F77450 |
| iC60N C 63A | A9F77163 | A9F77263 | A9F77363 | A9F77463 |
| iC60N D 1A  | A9F75101 | A9F75201 | A9F75301 | A9F75401 |
| iC60N D 2A  | A9F75102 | A9F75202 | A9F75301 | A9F75401 |
| iC60N D 3A  | A9F75103 | A9F75203 | A9F75301 | A9F75401 |
| iC60N D 4A  | A9F75104 | A9F75204 | A9F75301 | A9F75401 |
| iC60N D 6A  | A9F75106 | A9F75206 | A9F75306 | A9F75406 |
| iC60N D 10A | A9F75110 | A9F75210 | A9F75310 | A9F75410 |
| iC60N D 16A | A9F75116 | A9F75216 | A9F75316 | A9F75416 |
| iC60N D 20A | A9F75120 | A9F75220 | A9F75320 | A9F75420 |
| iC60N D 25A | A9F75125 | A9F75225 | A9F75325 | A9F75425 |
| iC60N D 32A | A9F75132 | A9F75232 | A9F75332 | A9F75432 |
| iC60N D 40A | A9F75140 | A9F75240 | A9F75340 | A9F75440 |
| iC60N D 50A | A9F75150 | A9F75250 | A9F75350 | A9F75450 |
| iC60N D 63A | A9F75163 | A9F75263 | A9F75363 | A9F75463 |

This certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Certificate. Only the client is authorized to permit copying or distribution of this Certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement and in this Certificate. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement. They are not for the purpose of production quality control and do not relieve the Client of their obligation in this respect.