

## Rack Automatic Transfer Switch AP4432A




### Overview

The APC Rack Automatic Transfer Switch (ATS) provides reliable, redundant power to single-corded equipment loads, such as servers. The Rack ATS has two input power cords supplying power to the connected loads. If the primary source becomes unavailable or goes out of the selected range, the Rack ATS will seamlessly source power from the secondary source without interrupting critical loads.


The Rack ATS has built-in network connectivity, which allows for remote management via Web, SNMP, SSH or Data Center Expert® interfaces.

### ATS Schematic




pdu1052a

Front



Rear



**Input power cords:** Two (2) cords connect the Rack ATS to two (2) separate power sources (A and B). The Rack ATS draws power from the preferred source and automatically switches to the secondary source when necessary. The two (2) 2.44-m (8-ft) power cords have L6-30P plugs.

**Outlets:** The outlets connect the Rack ATS to equipment in the rack or enclosure, providing a redundant source of power to the connected equipment. Each Rack ATS has sixteen (16) C13 outlets and two (2) C19 outlets.

**Circuit breakers:** The Rack ATS is protected by two (2) 20-A double-pole circuit breakers.

## Specifications

<b>Electrical</b>	
Nominal input voltage	200/208 VAC
Acceptable input voltage	±10% of nominal
Input frequency	50/60 Hz
Input connectors	Two (2) 2.44-m (8-ft) L6-30P power cords
Output connectors	Sixteen (16) C13 outlets Two (2) C19 outlet
Maximum output current	12 A–C13, 16 A–C19 (UL) 10 A–C13, 16 A–C19 (PSE) 16 A (UL) / 16 A (PSE)–bank 12 A (UL) / 10 A (PSE)–gang
Maximum output/input current	24 A (UL) / 30 A (PSE)
Overload protection	
Internal	Two (2) 20 A double-pole circuit breakers
External (recommended)	30 A facility provided
Transfer time	10 ms maximum (high sensitivity, 50–60 Hz) 12 ms maximum (low sensitivity, 50–60 Hz)
Short circuit current rating	10 kA
<b>Physical</b>	
Dimensions (H x W x D)	88.1 x 431.8 x 236.2 mm (3.47 x 17.00 x 9.30 in)
Shipping dimensions (H x W x D)	209.5 x 584.2 x 355.6 mm (8.25 x 23.00 x 14.00 in)
Weight	6.58 kg (14.50 lb)
Shipping weight	9.07 kg (20.00 lb)
<b>Environmental</b>	
Maximum elevation (above MSL)	
Operating	0 to 3 000 m (0 to 10,000 ft)
Storage	0 to 15 000 m (0 to 50,000 ft)
Temperature	
Operating	–5 to 45°C (23 to 113°F)
Storage	–25 to 65°C (–13 to 149°F)
Humidity	
Operating	5 to 95%, non-condensing
Storage	5 to 95%, non-condensing
<b>Compliance</b>	
EMC	FCC Part 15 / ICES-003
Safety	cULus / PSE - UL/EN/IEC 62368-1