

# CERTIFICATE

Issued to:  
Applicant:  
**Schneider Electric Industries SAS**  
31, rue Pierre Mendes Eybens  
38050 Grenoble Cedex 9, France

Licensee:  
**Schneider Electric Industries SAS**  
31, rue Pierre Mendes Eybens  
38050 Grenoble Cedex 9, France

Product : 2-pole socket-outlet  
Trade name(s) : SCHNEIDER ELECTRIC  
Type(s)/model(s) : A9A15310

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to NEN 1020:2019, NEN-IEC 60884-1:2019, NEN-IEC 60884-1:2019/A1:2019 and NEN-IEC 60884-1:2019/A2:2019
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 2115383


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 7 April 2025 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-156311

DEKRA Certification B.V.



B.T.M. Holtus  
Managing Director



Henk Schendstok  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

Product	: 2-pole socket-outlet
Trade name(s)	: SCHNEIDER ELECTRIC
Type(s)/model(s)	: A9A15310
Rated current	: 16 A
Rated voltage	: 250 V~
Standard sheet	: III
Method of mounting	: surface-type; special design for DIN-rail
Terminals	: screw terminals
Earthing	: with side earthing-contacts
Shutter	: with shutter
Markings	: are shown on the body

**TESTS****Test requirements**

NEN 1020:2019  
NEN-IEC 60884-1:2019  
NEN-IEC 60884-1:2019/A1:2019  
NEN-IEC 60884-1:2019/A2:2019

**Test result**

The test results are documented in DEKRA test file 224945900, 229799100.

**Additional information**

This certificate replaces certificate No. 71-116627 which we hereby declare invalid.

**Conclusion**

The examination has confirmed that all requirements were met.

**Factory location**

Schneider Electric Hungaria Villamosagi Zrt.  
Hock János út. 55  
8900 Zalaegerszeg, Hungary