



# Flexible, fast, and efficient charge sessions

EVlink Pro DC 120, 150, or 180 kW

## What are the key advantages of EVlink Pro DC?

### Benefits

- Designed for fleets depots and commercial and industrial buildings
- Fully integrated into Schneider Electric end-to-end solutions, leveraging its expertise in energy management, electrical solutions and digital technologies
- Supported by high-end services with a worldwide network of technicians to optimize the performance of the EV infrastructure and keep the assets running in optimum condition.
- Ensures a seamless user experience for EV installers, operators and drivers



## Unique features

### Flexibility

- Scalable from 120 kW to 150 and 180 kW
- Dynamic simultaneous charging
- Customizable look and feel

### Advanced Connectivity

- Embedded 4G modem and Wi-Fi module enabling remote monitoring and smart charging
- Interoperability thanks to OCPP 1.6 J2013, certified with dozens of CSMS back-ends
- Prepare for future technologies with ISO15118 Plug & Charge and Smart Charging readiness

### Reliability and safety

- Robust products:
  - 100% tested and certified on the production line
  - Third-party lab certification for IEC 61851-1 ed3 and IEC 61851-23
- Protection directly embedded in the Charger including SPD
- Eichrecht certified

### Serviceability

- Customer support in local language, backed by dedicated expertise either remotely or through advanced on-site assistance
- Comprehensive manufacturer-delivered services covering the entire lifecycle, from installation and commissioning to maintenance and modernization
- High reparability level with full scope available spare parts
- Ecostruxure Energy Asset Portal for remote assistance and diagnostic (Schneider Electric Customer Care Center or field services team)

se.com

Life Is On

**Schneider**  
Electric

# Characteristics

Characteristics	
Range	EVlink
Product name	EVlink Pro DC 180 kW
Product type	DC charging station
Device short name	EVD1S1
Electrical Characteristics	
Power supply	3 PH
Poles description	L1+L2+L3+N+PE
(Us) rated supply voltage	380 V – 415 Vac +/- 10% 50 / 60 Hz
Earthing system	TT TN-S / TN-C-S Compatible IT with additional isolation transformer on the power supply
Power factor	0.99 at nominal output power
Efficiency	94.5% at nominal output power
THDi	≤ 5% at nominal output power without any additional filter
DC meter	Each DC output includes Class A MID/PTB DC meter (1% accuracy at full scale) visible by any user
Standby power	90 W
Protection	Protected against short circuit, overload, Residual Current Device, protected against overheating, temperature regulated
Overvoltage category	OVC III
Rated conditional short-circuit current	30 kA
Charger Interfaces	
Vehicle connector number	2
Output type	Combo CCS type 2
Output Voltage	CCS2 : 150 – 1000 VDC
Output Current	CCS2 : 300 A max
Nominal output power	CCS2 : 180 kW; 150 kW or 120 kW
Dynamic-simultaneous charging	Possibility to charge two vehicles simultaneously. The charging station automatically adapts to use the full charging power available and to respond to the actual power request of each vehicle(s) connected to minimize the charging time.
Cable length	5 m cable length (3.6 m cable range) with cable management or 7.5m cable length and range without cable management

# Current information and protections to use with EVlink Pro DC 120, 150, or 180 kW

Current information and protections with EVlink Pro DC 120 - 150 - 180 kW				
Current				
Power		120 kW	150 kW	180 kW
	Rated current	193 A	242 A	291 A
	Max current	214 A	268 A	323 A
Suggested protections				
<b>Circuit breaker (overcurrent)</b>		<b>3P+N or 4P</b>	<b>3P+N or 4P</b>	<b>3P+N or 4P</b>
<b>Schneider Electric references*</b>		C25F4TM250 or C25F44V250 <sup>1</sup>	C40F42D400 + optional RCD protection LV432465	C40F42D400 + optional RCD protection LV432465

<sup>1</sup> Optional RCD protection included

Note: if there is plan to upgrade later (from 120 to 150 kW or 150 to 180kW...) already consider the protection sizings for DC 180 kW.

## Complementary

Complementary	
<b>Local signal</b>	1x multi-colour LED for status indication for each vehicle connector
<b>User Interface</b>	10.4" screen
<b>Multi-language support</b>	Bulgarian, Czech, Danish, Dutch, English, Estonian, Finnish, French, German, Greek, Hebrew, Hungarian, Indonesian, Italian, Latvian, Lithuanian, Norwegian, Portuguese, Romanian, Spanish, Swedish, Thai, Ukrainian, Vietnamese. Possibility to add additional language.
<b>Communication protocol</b>	OCPP 1.6 Json smart charging ISO15118 / DIN 70121 VDV 261 BCB toggle wake-up ModBus TCP
<b>Embedded network connection</b>	Wi-Fi Ethernet Modem 4G
<b>Access control system</b>	<ul style="list-style-type: none"> <li>– RFID Badge reader conforming to ISO / IEC 14443 Type A&amp;B and ISO/IEC 15693</li> <li>– NFC reader compatible with tag type 1,2,4,5</li> <li>– Reader support : MIFARE Ultralight, MIFARE Classic 1K/4K, MIFARE DESFire EV1/EV2, MIFARE Plus cards</li> <li>– ISO15118 Plug and Charge</li> <li>– Autocharge (EV Mac address)</li> <li>– Payment terminal reader (Option available in Europe)</li> </ul>
<b>Function available</b>	Load management Diagnosis capabilities Software updates Real-time charge cost display EV driver HMI customization for tarrif display EV driver HMI logo customization Connection to manufacturer portal for remote support and troubleshooting (Schneider Electric Customer Care Center or field services team) CSMS notification in case of power outage Advertisement possibility
<b>Cooling</b>	Filter air cooling
<b>Easy to use</b>	Accessible to disable people
<b>Mounting mode</b>	Floor standing

\* To check availability, please contact Schneider Electric front offices.

# Environment

Environment	
<b>Standard Compliance</b>	IEC/EN 61851-1 – Ed 3.0 IEC/EN 61851-23 – Ed 1.0 IEC/EN IEC62196-1 & IEC62196-3 EMC EN 61000-6-2 - Ed 2005 – EN 61000-6-4 - EMC class A  Radio certification RFID/NFC : EN 300 330 V2.1.1 4G : EN 301 908 -13 V13.1.1 Wi-Fi : EN 300 328 V2.2.2 - EN 301 893  EMC radio Equipment EN 301 489-1 V2.2.0 RFID/NFC : EMC EN 301 489-3 V2.1.1 4G : EMC EN 301 489-52 V1.1.0 Wi-Fi : EMC EN 301 489-17 V2.1.1
<b>Product certifications</b>	CE and Eichrecht certification
<b>IP degree of protection</b>	IP55
<b>IK degree of shock protection</b>	IK10 – screen IK08
<b>Ambient air temperature for operation</b>	- 30...+50°C derating above 50°C
<b>Ambient air temperature for storage</b>	-40...+70°C
<b>Relative humidity</b>	5...95 %
<b>Operating altitude</b>	up to 2000 m (without physical derating)
<b>Acoustic noise</b>	Variable under load : 0 to 65 dB at 1m in front of the charger
<b>Sensors</b>	Humidity sensor; door sensor; tilt sensor; water sensor
<b>Charge interrupt button</b>	Yes
<b>Housing corrosion protection</b>	C4M
<b>Colours Charging Station</b>	Front face : RAL 9003 Side and rear : PANTONE black C
<b>Material Charging Station</b>	304 Stainless steel



Offer sustainability	
<b>Sustainable offer status</b>	Green Premium product
<b>EU RoHS Directive</b>	Compliant
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	Yes
<b>Environmental Disclosure</b>	Product Environmental Profile
<b>Circularity Profile</b>	End Of Life information
<b>REACH Regulation</b>	Compliant

# Charging station dimensions

## Charging station dimensions

**Dimensions (cabinet with cable management)** H 2202 x W 1050 x D 982 mm (H 86.69 x W 41.34 x D 38.67 In.)

**Dimensions (cabinet without cable management)** H 2103 x W 845 x D 982 mm (H 83.86 x W 32.80 x D 37.92 In.)

## EVlink Pro DC 120 - 150 - 180 kW references and accessories

Power	Connector(s)	Reference	Weight without power module	Weight with power module	Embed- ded credit card reader	Cable range	Cable man- agement	Eichrecht certified
120 kW	CCS2 + CCS2	EVD1S120TBB	~470 kg / 1037 lb	~530 kg / 1168 lb	No	3.6m	Yes	No
150 kW	CCS2 + CCS2	EVD1S150TBB	~470 kg / 1037 lb	~545 kg / 1201 lb	No	3.6m	Yes	No
180 kW	CCS2 + CCS2	EVD1S180TBB	~470 kg / 1037 lb	~560 kg / 1235 lb	No	3.6m	Yes	No
120 kW	CCS2 + CCS2	EVD1S120TBGCC	~470 kg / 1037 lb	~530 kg / 1168 lb	Yes	3.6m	Yes	No
	CCS2 + CCS2	EVD1S120TBGCC-G	~470 kg / 1037 lb	~530 kg / 1168 lb	Yes	3.6m	Yes	Yes
150 kW	CCS2 + CCS2	EVD1S150TBGCC	~470 kg / 1037 lb	~545 kg / 1201 lb	Yes	3.6m	Yes	No
	CCS2 + CCS2	EVD1S150TBGCC-G	~470 kg / 1037 lb	~545 kg / 1201 lb	Yes	3.6m	Yes	Yes
180 kW	CCS2 + CCS2	EVD1S180TBGCC	~470 kg / 1037 lb	~560 kg / 1235 lb	Yes	3.6m	Yes	No
	CCS2 + CCS2	EVD1S180TBGCC-G	~470 kg / 1037 lb	~560 kg / 1235 lb	Yes	3.6m	Yes	Yes
120 kW	CCS2 + CCS2	EVD1S120TBCC7	~451 kg / 995 lb	~511 kg / 1127 lb	No	7.5m	No	No
	CCS2 + CCS2	EVD1S120TBCC7-G	~451 kg / 995 lb	~511 kg / 1127 lb	No	7.5m	No	Yes
150 kW	CCS2 + CCS2	EVD1S150TBCC7	~451 kg / 995 lb	~526 kg / 1160 lb	No	7.5m	No	No
	CCS2 + CCS2	EVD1S150TBCC7-G	~451 kg / 995 lb	~526 kg / 1160 lb	No	7.5m	No	Yes
180 kW	CCS2 + CCS2	EVD1S180TBCC7	~451 kg / 995 lb	~541 kg / 1193 lb	No	7.5m	No	No
	CCS2 + CCS2	EVD1S180TBCC7-G	~451 kg / 995 lb	~541 kg / 1193 lb	No	7.5m	No	Yes

### References

EVP1BNS

### EVlink accessories

10 RFID badges

se.com

Life Is On

**Schneider**  
Electric

Schneider Electric Industries SAS  
35, rue Joseph Monier - CS 30323  
F92506 Rueil-Malmaison Cedex

© 2025 Schneider Electric. All Rights Reserved. Life Is On Schneider Electric is a trademark and the property of Schneider Electric SE, its subsidiaries and affiliated companies.  
• 998-23232703