

Product data sheet

Characteristics

AP9565

APC NetShelter Basic Rack PDU, 1U, 1PH, 3.7kW 230V 16A or 3.3kW 208V 16A, x12 C13 outlets, C20 cord



EAN Code: 0731304213055



Overview

Presentation	Reliable rack power distribution designed to increase manageability and efficiency in the data c
--------------	--

Main

Colour	Black
Product or component type	PDU
PDU type	Basic
Cable length	2.49 M
Number of cables	1
Provided equipment	Installation guide Rack mounting brackets

Complementary

Main Input Voltage	200 V 208 V 230 V
Height	44 Mm
Width	447 Mm
Output voltage	208 V 230 V
Depth	57 Mm
Product weight	2.05 Kg
Mounting location	Front Rear
Mounting preference	No preference
Input Connection Type	IEC 60320 C20
Mounting mode	Rack-mounted
Number of rack unit	1U
Mounting position	Horizontal
Input current limits	16 A
Load capacity	3680 VA
Network frequency	50/60 Hz
Number of power socket outlets	12 IEC 60320 C13

Environment

Product certifications	cUL listed[RETURN]CE[RETURN]Queensland Australia[RETURN]UL listed[RETURN]VDE
Standards	UL 60950
Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...15240 M

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 Cm
Package 1 Width	46.4 Cm
Package 1 Length	22.9 Cm
Package 1 Weight	3.632 Kg

Offer Sustainability

Recyclability potential, in %	45
Total lifecycle Carbon footprint	2 398 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.2615956056
Carbon footprint of the manufacturing phase [A1 to A3]	0.3 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.2615956056
Carbon footprint of the distribution phase [A4]	0.3 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	2384.9323857868
RECh free of SVHC	Yes
Carbon footprint of the use phase [B2, B3, B4, B6]	2 385 kg CO2 eq.
Lead free	Yes
Sustainable packaging	No
Carbon footprint of the end-of-life phase [C1 to C4]	0.2304947438
Carbon footprint of the end-of-life phase [C1 to C4]	0.2 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile
Total lifecycle Carbon footprint	2398
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
RECh Regulation	Free of Substances of Very High Concern above the threshold ↗
EU RoHS Directive	Compliant ↗
Halogen-free status	Product contains halogen above thresholds
End of life manual availability	End Of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and

Logistical informations

Country of origin	IN
-------------------	----

Contractual warranty

Warranty (in months)	24
----------------------	----

Product Life Status : Commercialised
