



## Switched Rack Power Distribution Unit (AP8661)


### Overview

The APC Switched Rack Power Distribution Unit (PDU) distributes power to devices in a rack. The PDU measures total load plus phase, bank, and outlet load. In addition, configured users can control the state of the outlets. You can access the PDU through Web, Telnet, SNMP, SSH, or EcoStruxure™ IT Expert interfaces for comprehensive control and monitoring functionality.

**Outlets.** The Rack PDU has twenty-one (21) IEC-320-C13 and three (3) IEC-320-C19 locking outlets **2**. (The locking feature is compatible with APC locking input cords and APC locking jumper cords.)

**Display interface.** The liquid crystal display (LCD) **3** and input buttons **4** allow you to monitor current, power, and voltage measurements of the Rack PDU. Local communication can be established through the serial port **8**, and remote communication through the network port **5**. The USB **9** port allows for firmware upgrades, and the CAN **7** ports enable data transfer for future expansion options. The environmental sensor port **6** allows for monitoring of the temperature and humidity of the room or enclosure.

**Power cord.** The 1.83-m (6-ft) power cord terminates with a 3-phase, 20 A, NEMA L21-20P connector **10**.



## Specifications

### Electrical

Acceptable input voltage	120/208 VAC 3W+N+PE
Maximum input current (phase)	16A
Input frequency	50/60 Hz
Input connection	3-phase, 20 A, NEMA L21-20P
Input power	5.8 kVA
Output voltage	208 VAC (line-to-line)
Maximum output current (outlet)	IEC-320-C13: 12 A; IEC-320-C19: 16 A
Maximum output current (phase)	16 A
Output connections	Twenty-one (21) IEC-320-C13; three (3) IEC-320-C19

### Physical

Dimensions (H x W x D) (depth does not include toolless pegs)	182.9 x 5.6 x 5.1cm (72.0 x 2.2 x 2.0 in)
Power cord length	1.83 m (6 ft)
Shipping dimensions (H x W x D)	203.8 x 16.2 x 11.7 cm (80.25 x 6.38 x 4.62 in)
Weight/shipping weight	8.23 kg (18.1 lb) / 10.5kg (23.1 lb)

### Environmental

Maximum elevation (above MSL) Operating/Storage	0–3 000 m (0–10,000 ft) / 0–15 000 m (0–50,000 ft)
Temperature Operating/Storage	–5 to 60 °C (23 to 140 °F) / –25 to 65 °C (–13 to 149 °F)
Humidity Operating/Storage	5–95% RH, non-condensing

### Compliance

EMC verification	FCC Part 15, ICES-003
Safety verification	cULus