

ASTA TYPE CERTIFICATE

VERIFICATION OF TEST

Project No: SHA009188 **Certificate No:** ASTA-TYPE-0002694

Vendor: Schneider Electric Industries SAS
Rua Joseph Monier, 92500 Rueil Malmaison, France

Apparatus: Two 250 A, 1000 V / 1000 V / 8 kV ($U_n=U_e, / U_i / U_{imp}$), 50/60 Hz, single stack Busbar Trunking Systems, each comprising three joints, one flanged end unit, two straight BTU without tap-off facilities with three-phase and neutral, copper busbars, and integrated earthing bar for 3P4W type or an internal earth copper busbar for 3P5W type in a painted aluminium alloy enclosure.

Manufactured By: Schneider Busway (Guangzhou) Limited
No. 85 Junye Road, Eastern Section of Economic & Technological Development Zone, Guangzhou 510530, China

Test Report No: 200910001GZA/A and YGY20-001723/A

Designation: I-LINE Track 250 A 4P and I-LINE Track 250 A 5P

The apparatus which is representative of the designation, supplied drawings and photographs has been evaluated in accordance with:

IEC 61439-6: 2012

Verifications with reference to the tests listed in Annex D, Table D1 of IEC 61439-6: 2012, and Annexes BB, CC and EE:

1: Strength of material and parts	6/7/8: No verification by testing required
2: Degree of protection of enclosures	9: Dielectric properties
3: Clearances	10: Temperature-rise limits
4: Creepage distances	11: Short circuit withstand strength
5: Protection against electric shock and integrity of protective circuits	12: Electromagnetic compatibility (EMC)
	13: Mechanical operation

The results are shown in the record of tests attached hereto. The values obtained and the general performance is considered to comply with the above Standard(s) and to justify the ratings assigned by the manufacturer as stated on the ratings page(s) of this Certificate. This Certificate applies only to the apparatus tested. Responsibility for conformity of any apparatus having the same or other designations rests with the Manufacturer.



0010

Gorochang

Certification Engineer

Zamir

Certification Officer

8th October 2023

Date

Project No: SHA009188

Certificate No: ASTA-TYPE-0002694

Conditions of use:

ASTA Type Certificates, verification of test is issued by Intertek for the exclusive use of the party applying for the Certificate. Intertek assumes no liability to any parties other than those with which it has an agreement and then only in accordance with the agreed Terms and Conditions.

The Applicant is authorised to copy or distribute Certificates and Test Reports provided the entire contents are included, or Certificate Front Sheets accompanied by any associated pages on which are stated the assigned rated characteristics and no part is obscured or illegible. Permission must be obtained from Intertek before any other kind of reproduction is made.

The holder of a Certificate may claim in Trade Journals, Catalogues, Technical Articles etc., and without the prior approval of Intertek that the product identified in a Certificate is Certified.

To minimise the possibility of any misunderstanding such claims must clearly identify the product(s) certified or approved, the ratings verified and the Standard against which certification/approval has been made.

Any other use of the Intertek or ASTA brand must first be approved in writing by Intertek. Test results and ratings verified by testing included in the Certificate and related Test Reports shall relate specifically to the sample(s) tested.

Authenticity:

Authenticity of any ASTA document can be confirmed by contacting the Intertek ASTA Certification Office at the following address:

Intertek Testing & Certification Ltd., Centre Court, Meridian Business Park, Leicester, LE19 1WD, United Kingdom.
Email: asta@intertek.com

Project No: SHA009188
Certificate No: ASTA-TYPE-0002694

Verification of: BUSBAR TRUNKING SYSTEM

No ¹⁾	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
1	Strength of material and parts	10.2	
	Resistance to corrosion	10.2.2	Verified for Severity test A
	Properties of insulating materials	10.2.3	-
	Thermal stability	10.2.3.1	Verified
	Resistance to abnormal heat and fire due to internal electric effects	10.2.3.2	Verified
	Resistance to ultra-violet (UV) radiation	10.2.4	Not applicable to indoor enclosures
	Lifting	10.2.5 ²⁾	Verified
	Mechanical impact	10.2.6	Verified for IK08
	Marking	10.2.7	Verified
	Ability to withstand mechanical loads	10.2.101 ²⁾	Verified for normal mechanical loads
Thermal cycling test	10.2.102	Not applicable as no plug-in tap-off units has been included	
2	Degree of protection of enclosures	10.3³⁾	
	External enclosure		IP42/IP20
3	Clearances	10.4	Verified for $U_{imp} = 8 \text{ kV}$
4	Creepage distances	10.4	Verified for $U_i = 1000 \text{ V}$ Material Group: IIIa Pollution degree: 3
5	Protection against electric shock and integrity of protective circuits:	10.5²⁾	-
	Effective continuity between the exposed conductive parts of the assembly and the protective circuit	10.5.2	Verified
	Short-circuit withstand strength of the protective circuit	10.5.3	Verified
	250 A 5P (PE Separated) 1 – 54.3 mm x 1.2 mm U-type copper bar	10.5.3.4	$I_{cw} = 6 \text{ kA rms for 1 sec}$ $I_{pk} = 16.8 \text{ kA peak}$

Project No: SHA009188

Certificate No: ASTA-TYPE-0002694

No ¹⁾	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
5	Protection against electric shock and integrity of protective circuits:	10.5²⁾	-
	Short circuit withstand strength of the protective circuit	10.5.3.5 and 10.11.5.6	Verified
	Earth busbar size: 250 A 4P (PE Integrated)		I_{cw} = 6 kA rms for 1 sec I_{pk} = 16.8 kA peak
9	Dielectric properties	10.9²⁾	Verified
	The BTS-Assembly:		-
	Rated voltage		U_n = 1000 V
	Rated operational voltage		U_e = 1000 V
	Rated insulation voltage	10.9.2	U_i = 1000 V
	Rated impulse withstand voltage	10.9.3	U_{imp} = 8 kV
	Testing of enclosures made of insulating material	10.9.4	Verified
External operation handles of insulating material	10.9.5	Not applicable	
10	Temperature rise	10.10²⁾	
	The rated current of the assemblies is based upon a mean/maximum ambient temperature of:		35/40°C
	Verification by testing Orientation: Horizontal	10.10.2	
	Main busbar size: 250 A 4P (PE Integrated) 1 – 54.3 mm x 1.2 mm U-type copper bar per phase	10.10.2.3.5	I_{nA} = 250 A
	250 A 5P (PE Separated) 1 – 54.3 mm x 1.2 mm U-type copper bar	10.10.3	I_{nA} = 250 A
11	Short-circuit withstand strength	10.11²⁾	
	Three-phase Main busbar size: 250 A 4P (PE Integrated) 1 – 54.3 mm x 1.2 mm U-type copper bar per phase	10.11.5.3.3	I_{cw} = 10 kA rms for 1 sec I_{pk} = 28 kA peak

Project No: SHA009188

Certificate No: ASTA-TYPE-0002694

No ¹⁾	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
11	Short-circuit withstand strength (Continued)	10.11²⁾	
	250 A 5P (PE Separated) 1 – 54.3 mm x 1.2 mm U-type copper bar per phase	10.11.3	I_{cw} = 10 kA rms for 1 sec I_{pk} = 28 kA peak
	Neutral conductor Neutral busbar size: 250 A 4P (PE Integrated) 1 – 54.3 mm x 1.2 mm U-type copper bar	10.11.5.3.5	I_{cw} = 6 kA rms for 1 sec I_{pk} = 16.8 kA peak
	250 A 5P (PE Separated) 1 – 54.3 mm x 1.2 mm U-type copper bar	10.11.3	I_{cw} = 6 kA rms for 1 sec I_{pk} = 16.8 kA peak
12	Electromagnetic compatibility (EMC)	10.12	Conditions for no testing (J.9.4.3.1 and 9.4.4.1) verified
13	Mechanical operation	10.13	Not applicable. no plug-in tap-off units.
<p>Note:</p> <p>¹⁾ Design verification tests required by IEC 61439-1, Annex D, Table D1. No Verification by testing was required for items 6, 7 and 8 clauses 10.6, 10.7 and 10.8.</p> <p>²⁾ The tests for clauses 10.2.5, 10.2.101, 10.3, 10.5, 10.9, 10.10 and 10.11 were performed on I-LINE Track 250A 4P considering to be representative of the I-LINE Track 250A 5P.</p> <p>³⁾ The tests for clause 10.3 were performed on I-LINE Track 400A 4P considering to be representative of the I-LINE Track 250A 4P and 5P.</p>			

Note: The apparatus tested was manufactured by Schneider Busway (Guangzhou) Limited No. 85 Junye Road, Eastern Section of Economic & Technological Development Zone, Guangzhou 510530, China, for which ASTA Certificate of Verification no. ASTA-TYPE-000470R1, dated 27th January 2022 has been issued.

Project No: SHA009188

Certificate No: ASTA-TYPE-0002694

Certificate Contents:

The following documents are attached to and form part of this certificate:

Documents:	Number of pages
Test report no: 200910001GZA/A and YGY20-001723/A dated 19 January 2022	62
Drawings	18

Certificate Revision Amendment Table

Certificate Number	Issue Date	Amendment
ASTA-TYPE-0002694	8th October 2023	Initial issue