



## Switched Rack Power Distribution Unit (AP8659)

### Overview


The APC Switched Rack Power Distribution Unit (PDU) distributes power to devices in a rack. The PDU measures total load plus phase, bank, and outlet load. In addition, configured users can control the state of the outlets. You can access the PDU through Web, Telnet, SNMP, SSH, or EcoStruxure™ interfaces for comprehensive control and monitoring functionality.

**Outlets:** The Rack PDU has twenty-one (21) IEC-320-C13 and three (3) IEC-320-C19 locking outlets **2**. (The locking feature is compatible with APC locking input cords and APC locking jumper cords.)

**Display interface:** The liquid crystal display (LCD) **3** and input buttons **4** allow you to monitor current, power, and voltage measurements of the Rack PDU. Local communication can be established through the serial port **8**, and remote communication through the network port **5**. The USB **9** port allows for firmware upgrades, and the CAN **7** ports enable data transfer for future expansion options. The environmental sensor port **6** allows for monitoring of the temperature and humidity of the room or enclosure.

**Power cord:** The Rack PDU has one (1) IEC-320 inlet **10**. (Power cord provided on AP8659EU3 and AP8659NA3 only.)

**Toolless mounting:** The Rack PDU has two (2) toolless mounting pegs **1** for 0 U mounting capability in a rack or enclosure.



## Specifications

### Electrical

Acceptable input voltage	100-240 VAC +6%, -10%
Maximum input current (phase)	16 A cULus 20 A PSE 16 A UL-EU
Input frequency	50/60 Hz
Input connection	IEC-320-C20
Input power	3.8 kVA UL 3.7 kVA UL-EU 3.2 kVA PSE
Output voltage	100-240 VAC
Maximum output current (outlet)	IEC-320-C13: 12 A; IEC-320-C19: 16 A UL (derated), PSE IEC-320-C13: 10 A; IEC-320-C19: 16 A UL-EU
Maximum output current	16 A cULus 20 A PSE 16 A UL-EU
Output connections	Twenty-one (21) IEC-320-C13; three (3) IEC-320-C19

### Physical

Dimensions (H x W x D) (depth does not include toolless pegs)	182.9 x 5.6 x 5.1 cm (72.0 x 2.2 x 2.0 in)
Shipping dimensions (H x W x D)	203.8 x 16.2 x 11.7 cm (80.25 x 6.38 x 4.62 in)
Weight/shipping weight	6.09 kg (13.4 lb) / 8.36 kg (18.4 lb)

### Environmental

Maximum elevation (above MSL) Operating/Storage	0–3 000 m (0–10,000 ft) / 0–15 000 m (0–50,000 ft)
Temperature Operating/Storage	–5 to 60 °C (23 to 140°F) / –25 to 65 °C (–13 to 149 °F)
Humidity Operating/Storage	5–95% RH, non-condensing

### Compliance

EMC verification	FCC Part 15, ICES-003, VCCI-CISPR 32, EN 55032, EN 55035, EN 61000-3-2, EN 61000-3-3
Safety verification	cULus-EU, CE, PSE, RCM, EAC, CMIM, UKCA