



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
BMH0703P01A2A

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:	
Frame Size (mm):	70
Degree of Protection (Shaft / housing):	IP54 / IP65
Maximum Current (Arms):	12.57
Holding brake:	No
Encoder Type:	ABS Single turn 128 Sin/Cos period
Torque Constant (Nm/A):	0.87
CSA:	Yes
RoHS:	Yes
Weight without brake (kg / lb):	6.61 / 3

Specification:	
Description:	BMH
Family:	8000
Maximum Permissible Speed (rpm):	3.40 / 30.1
Continuous Stall Torque (Nm / lbs-in):	10.2 / 90.28
Peak Torque (Nm / lbs-in):	