



FRONT VIEW




LEFT SIDE VIEW

REAR VIEW


ISOMETRIC VIEW




VIEW A  
IEC 60309, 3P, 4W, 9H,  
IP44 (SPLASH PROOF)  
60A(48A DERATED), 250V MAX,  
3PH PLUG  
ENLARGED VIEW




DETAIL B  
PEG TOOL LESS MOUNTING  
ENLARGED VIEW



C13/C15/C19/C21 RECEPTACLE  
16A, 250V MAX  
ENLARGED VIEW



C13/C15 RECEPTACLE  
10A, 250V MAX  
ENLARGED VIEW



DETAIL C  
NMC - ENLARGED VIEW


NOTES:

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL ELECTRICAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND PREPARATION WORK.
3. UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].
4. NET WEIGHT OF UNIT IS 11.1kg [24.47 lb].
5. LENGTH OF THE CORD IS 1.8 Meters.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: APC NetShelter Rack PDU Advanced Switched, 3PH, 17.3kW, 208V, 60A INPUT: IEC 60309 - 460P9 OUTPUT:(21)C13/C15 & (21)C13/C15/C19/C21 GENERAL ARRANGEMENT	DWG NO: APDU10452SW	REV: 0
PROJECT: SUBMITTAL DRAWING SHEET 1 OF 2	DRAWN: Jayaprakash ENGINEER: Yuchun Jiang APPROVED: Mark Reinders	20-OCT-21 02-MAR-22 02-MAR-22
		FIRST ANGLE PROJECTION



INPUT CORD:  
IEC 60309

INPUT  
L1 (BLACK)  
L2 (ORANGE)  
L3 (RED)  
PE (GREEN)

10A, 250V Max  
Rated Output (TYP.)  
10/16A, 250V Max  
Rated Output (TYP.)

RATED POWER:	17.3kVA
INPUT:	208V, 60A (48A DERATED), 3PH, 50/60Hz
OUTPUT:	C13/C15 Combo: 208V, 10A per Outlet C13/C15/C19/C21 Combo: 208V, 16A per Outlet
PERMISSIBLE VOLTAGE:	200-240V

**NOTES:**

1. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE AND LOCAL ELECTRICAL CODES.
2. REFER TO PRODUCT DOCUMENTATION FOR ADDITIONAL DETAILS PRIOR TO INSTALLATION AND PREPARATION WORK.
3. THIS DRAWING DEPICTS THE POWER SYSTEM CONNECTIONS AND IS NOT REPRESENTATIVE OF THE PHYSICAL LAYOUT. PLEASE REFER TO MECHANICAL DRAWINGS FOR PHYSICAL LAYOUT.

THIS DRAWING AND SPECIFICATIONS HEREIN ARE THE PROPERTY OF SCHNEIDER ELECTRIC AND SHALL NOT BE COPIED, REPRODUCED OR USED IN WHOLE OR IN PART, AS THE BASIS FOR THE MANUFACTURE OR SALE OF ITEMS WITHOUT WRITTEN PERMISSION FROM SCHNEIDER ELECTRIC. THIS DRAWING IS BASED UPON LATEST AVAILABLE INFORMATION AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



TITLE: APC NetShelter Rack PDU Advanced Switched, 3PH, 17.3kW, 208V, 60A  
INPUT: IEC 60309 - 460P9  
OUTPUT: (21)C13/C15 & (21)C13/C15/C19/C21  
SCHEMATIC DIAGRAM

DWG NO: APDU10452SW

REV: 0

PROJECT: SUBMITTAL DRAWING	SHEET 2 OF 2	APPROVED:	Mark Reinders	02-MAR-22	ANGLE PROJECTION
		DRAWN:	Jayaprakash	20-OCT-21	N.A.
		ENGINEER:	Yuchun Jiang	02-MAR-22	