

# PowerTag

Selection guide for product compatibility\*  
(Compatibility for terminal not equipped with comb busbar)



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9</b>					
<b>Circuit breakers</b>					
<b>iC60/iK60/DT60</b>	Top	✓	-	-	-
	Bottom	✓	-	-	-
<b>iC60 (double terminal)</b>	Top	-	-	-	✓
	Bottom	-	-	-	✓
<b>iC40</b>	Top	-	✓	-	-
	Bottom	-	✓	-	-
<b>DT40/iDPN/C40</b>	Top	-	✓	-	-
	Bottom	-	✓	-	-
<b>C120 ≤ 63 A NG125 ≤ 63 A</b>	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
<b>iC65N-K (China) iC65 (China)</b>	Top	✓	-	-	-
	Bottom	✓	-	-	-
<b>iDPN (China)</b>	Top	-	✓	-	-
	Bottom	-	✓	-	-
<b>iKQ (1P+W PowerTag on each pole)</b>	Top	NA	-	-	-
	Bottom	✓ (1P+W only)	-	-	-
<b>N40</b>	Top	-	✓	-	-
	Bottom	-	✓	-	-
<b>Reflex iC60</b>	Top	✓	-	-	-
	Bottom	✓	-	-	-
<b>Reflex XC40</b>	Top	✓	-	-	-
	Bottom	-	-	-	✓ (1)
<b>C32/C45/C60/C65/K60/T60/ C60-OEM</b>	Top	✓	-	-	-
	Bottom	✓	-	-	-
<b>Circuit breakers equipped with Vigi module</b>					
<b>iC60/iC65/iC60/iC65N-K with Vigi module</b>	Top	✓ (CB)	-	-	-
	Bottom	-	-	-	✓ (Vigi) (1)
<b>iC40 with Vigi iCG40</b>	Top CB	-	✓ (CB)	-	-
	Top (Vigi)	-	✓ (Vigi 1P+N) (2)	-	-
	Bottom (Vigi)	-	-	-	✓ (Vigi 3P+N)
<b>iC40 with "outgoer" Vigi module</b>	Top	-	✓ (CB)	-	-
	Bottom	-	-	-	✓ (Vigi)
<b>DT40/DPN/C40 with "group feeder" Vigi module</b>	Top CB	-	✓ (CB)	-	-
	Top Vigi	-	✓ (Vigi 1P+N)	-	✓ (Vigi 3P+N)
<b>DT40/DPN/C40 with "outgoer" Vigi module</b>	Top	-	✓ (CB)	-	-
	Bottom	-	-	-	✓ (Vigi)
<b>DT60 with Vigi TG60</b>	Top CB	✓ (CB) only A9MEM1541	-	-	-
	Top Vigi	-	-	-	✓ (Vigi) (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.  
(2) Product usually associated with a comb busbar

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

Selection guide for product compatibility\* (cont.)  
(Compatibility for terminal not equipped with comb busbar)



Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9</b>					
<b>Residual current devices</b>					
IID/iID K	Top	✓	-	-	-
	Bottom	✓	-	-	-
IID (double terminal)	Top	-	-	-	✓
	Bottom	-	-	-	✓
iID40	Top	-	☑ 1P+N (2)	-	☑ 3P+N (2)
	Bottom	✓	-	-	-
iDPN Vigi "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
iC60H RCBO/iC60H2 RCBO/ IKQE RCBO	Top	NA (fishbone)	-	-	-
	Bottom	-	-	✓	-
iC60 RCBO	Top	✓	-	-	-
	Bottom	✓	-	-	-
iCV40 "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
iCV40 "outgoer" 3P+N	Top	-	✓	-	-
	Bottom	-	-	-	✓
DPN Vigi/DT40 Vigi/C40 Vigi "outgoer" 1P+N	Top	-	✓	-	-
	Bottom	-	✓	-	-
DPN Vigi/DT40 Vigi/C40 Vigi/ iDPN Vigi "outgoer" 3P+N	Top	-	✓	-	-
	Bottom	-	-	-	✓
DPN Vigi K	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
N40 Vigi "outgoer"	Top	-	✓	-	-
	Bottom	-	✓	-	-
iDc/ITG40/C40	Top Left	-	✓	-	-
	Top Right	-	✓	-	-
DCP Vigi	Top	✓	-	-	-
	Bottom	✓	-	-	-
C60H RCBO (Multi9)	Top	NA (fishbone)	-	-	-
	Bottom	-	-	✓	-
ID ≤ 63 A/iD K biconnect/ ID Type B ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
RED/REDs/REDTest	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.  
(2) Product usually associated with a comb busbar

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

Selection guide for product compatibility\* (cont.)  
(Compatibility for terminal not equipped with comb busbar)







Products (AC network)	Mounting position	A9 M63	A9 P63	A9 P63 RCBO	A9 F63
<b>Acti9/Multi9 Switches</b>					
iSW ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
iSW-NA ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
iSW 20/32 A	Top	-	-	-	✓
	Bottom	-	-	-	✓
i-NA ≤ 63 A	Top	✓	-	-	-
	Bottom	✓	-	-	-
NG125 NA ≤ 63 A	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
<b>Fuse disconnectors</b>					
STI	Top	-	✓	-	-
	Bottom	-	✓	-	-
SBI 14x51/SBI 22x58 ≤ 63 A	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
D01/D02	Top	-	-	-	✓ (1)
	Bottom	-	-	-	✓ (1)
<b>TeSys</b>					
<b>Circuit breakers</b>					
GV2	Top	-	-	-	✓ (1) (2)
	Bottom	-	-	-	✓ (1) (2)
GV3 ≤ 63 A	Top	-	-	-	✓ (1) (2)
	Bottom	-	-	-	✓ (1) (2)
<b>Contactors</b>					
LC1D ≤ 63 A	Top	-	-	-	✓ Upstream only (1)
	Bottom	-	-	-	-

(1) You may need to change the voltage measurement cable terminals of the PowerTag F63 by other cable ends (wire AWG22/0.33 mm<sup>2</sup>) for a more suitable connection to this product.  
(2) PowerTag Energy sensors withstand motor starting in-rush currents. Environmental mission profile : Buildings as per 60721-3-3.

(\*): Refer to the product catalogue for technical characteristics

## PowerTag

## Selection guide for product compatibility\* (cont.)

			PowerTag NSX			
						
Products (AC network)		Mounting position	250 3P	250 3P+N	630 3P	630 3P+N
<b>Compact</b>						
<b>Circuit breakers</b>						
<b>NSX100/160/250 B/F/N/H/S/L/R Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NSX400/630 F/N/H/S/L/R Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NSX100/160/250 B/F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
<b>NSX400/630 F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top / Bottom	-	-	☑ (4)	-
	4P	Top / Bottom	-	-	-	☑ (3) (4)
<b>NS100/160/250 N/ SX/H/L Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NS400/630 N/H/L Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NS100/160/250 N/ SX/H/L Plug-In (mounted on the base)</b>	3P	Top / Bottom	☑	-	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
<b>NS400/630 N/H/L Plug-In (mounted on the base)</b>	3P	Top / Bottom	-	-	☑ (4)	-
	4P	Top / Bottom	-	-	-	☑ (3) (4)
<b>Circuit breakers equipped with Vigi block</b>						
<b>NSX100/160/250 B/F/N/H/S/L/R Fixed</b>	3P	Bottom	☑	-	-	-
	4P	Bottom	-	☑	-	-
<b>NSX400/630 F/N/H/S/L/R Fixed</b>	3P	Bottom	-	-	☑	-
	4P	Bottom	-	-	-	☑
<b>NSX100/160/250 B/F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top	☑	-	-	-
<b>NSX400/630 F/N/H/S/L/R Plug-In (mounted on the base)</b>	3P	Top	-	-	☑ (4)	-
<b>Switches</b>						
<b>INS250/INV - 100/160/200/250</b>	3P	Bottom	-	☑	-	-
	4P	Top / Bottom	-	☑ (3)	-	-
<b>INS/INV - 320/400/500/630</b>	3P	Bottom	-	-	-	☑
	4P	Top / Bottom	-	-	-	☑ (3)










(3) neutral on the right when mounted on top side

(4) when plate mounted, need to add a 4 mm intercalary under the PowerTag module (see Compact NSX catalog)

(\*) Refer to the product catalogue for technical characteristics

# PowerTag

## Selection guide for concentrator compatibility\*

		Concentrators				
						
		Acti9 PowerTag Link C A9XELC10	Acti9 Smartlink SI B A9XMZA08	Acti9 Smartlink SI D A9XMWA20	Acti9 PowerTag Link A9XMWD20	Acti9 PowerTag Link HD A9XMWD100
<b>PowerTag Acti9 M63</b>						
	A9MEM1520	✓	✓	✓	✓	✓
	A9MEM1521	✓	✓	✓	✓	✓
	A9MEM1522	✓	✓	✓	✓	✓
	A9MEM1540	✓	✓	✓	✓	✓
	A9MEM1541	✓	✓	✓	✓	✓
	A9MEM1542	✓	✓	✓	✓	✓
	A9MEM1543	✓	-	-	✓	✓
<b>PowerTag Acti9 P63</b>						
	A9MEM1561	✓	✓	✓	✓	✓
	A9MEM1562	✓	✓	✓	✓	✓
	A9MEM1563	✓	✓	✓	✓	✓
	A9MEM1571	✓	✓	✓	✓	✓
	A9MEM1572	✓	✓	✓	✓	✓
<b>PowerTag Acti9 F63</b>						
	A9MEM1560	✓	✓	✓	✓	✓
	A9MEM1573	-	-	-	✓	✓
	A9MEM1570	✓	✓	✓	✓	✓
<b>PowerTag NSX</b>						
	LV434020	✓	✓	✓	✓	✓
	LV434021	✓	✓	✓	✓	✓
	LV434022	✓	✓	✓	✓	✓
	LV434023	✓	✓	✓	✓	✓

(\*) Refer to the product catalogue for technical characteristics