

ASTA TYPE CERTIFICATE

VERIFICATION OF TEST

Project No: SHA042830 **Certificate No:** ASTA-TYPE-0002696

Vendor: Schneider Electric Industries SAS
Rua Joseph Monier, 92500 Rueil Malmaison, France

Apparatus: Two 630 A, 1000 V / 1000 V / 8 kV ($U_n=U_e, / U_i / U_{imp}$), 50/60 Hz, single stack Busbar Trunking Systems, each comprising of three joints, one flanged end unit, two straight BTU without tap-off facilities with three-phase and neutral copper busbars, and integrated earthing bar for 3P4W type or an internal earth copper busbar for 3P5W type in a painted aluminium alloy enclosure.

Manufactured By: Schneider Busway (Guangzhou) Limited
No. 85 Junye Road, Eastern Section of Economic & Technological Development Zone, Guangzhou 510530, China

Test Report No: 210603002GZA and YDY21-000776

Designation: I-LINE Track 630 A 4P and I-LINE Track 630 A 5P

The apparatus which is representative of the designation, supplied drawings and photographs has been evaluated in accordance with:

IEC 61439-6: 2012

Verifications with reference to the tests listed in Annex D, Table D1 of IEC 61439-6: 2012, and Annexes BB, CC and EE:

1: Strength of material and parts	6/7/8: No verification by testing required
2: Degree of protection of enclosures	9: Dielectric properties
3: Clearances	10: Temperature-rise limits
4: Creepage distances	11: Short circuit withstand strength
5: Protection against electric shock and integrity of protective circuits	12: Electromagnetic compatibility (EMC)
	13: Mechanical operation

The results are shown in the record of tests attached hereto. The values obtained and the general performance is considered to comply with the above Standard(s) and to justify the ratings assigned by the manufacturer as stated on the ratings page(s) of this Certificate. This Certificate applies only to the apparatus tested. Responsibility for conformity of any apparatus having the same or other designations rests with the Manufacturer.



0010

Gorschang
.....

Certification Engineer

[Signature]
.....

Certification Officer

8th October 2023

.....

Date

Project No: SHA042830

Certificate No: ASTA-TYPE-0002696

Conditions of use:

ASTA Type Certificates, verification of test is issued by Intertek for the exclusive use of the party applying for the Certificate. Intertek assumes no liability to any parties other than those with which it has an agreement and then only in accordance with the agreed Terms and Conditions.

The Applicant is authorised to copy or distribute Certificates and Test Reports provided the entire contents are included, or Certificate Front Sheets accompanied by any associated pages on which are stated the assigned rated characteristics and no part is obscured or illegible. Permission must be obtained from Intertek before any other kind of reproduction is made.

The holder of a Certificate may claim in Trade Journals, Catalogues, Technical Articles etc., and without the prior approval of Intertek that the product identified in a Certificate is Certified.

To minimise the possibility of any misunderstanding such claims must clearly identify the product(s) certified or approved, the ratings verified and the Standard against which certification/approval has been made.

Any other use of the Intertek or ASTA brand must first be approved in writing by Intertek. Test results and ratings verified by testing included in the Certificate and related Test Reports shall relate specifically to the sample(s) tested.

Authenticity:

Authenticity of any ASTA document can be confirmed by contacting the Intertek ASTA Certification Office at the following address:

Intertek Testing & Certification Ltd., Centre Court, Meridian Business Park, Leicester, LE19 1WD, United Kingdom.
Email: asta@intertek.com

Project No: SHA042830
Certificate No: ASTA-TYPE-0002696

Verification of: BUSBAR TRUNKING SYSTEM

No	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
1	Strength of material and parts	10.2	
	Resistance to corrosion	10.2.2 [#]	Severity test A for metallic indoor enclosure: verified
	Properties of insulating materials	10.2.3 [#]	–
	Thermal stability	10.2.3.1	Verified
	Resistance to abnormal heat and fire due to internal electric effects	10.2.3.2	Verified
	Resistance to ultra-violet (UV) radiation	10.2.4	Not applicable to indoor enclosures
	Lifting	10.2.5	Verified
	Mechanical impact	10.2.6	Verified for IK08
	Marking	10.2.7	Verified
	Ability to withstand mechanical loads	10.2.101	Verified for normal mechanical loads
	Thermal cycling test	10.2.102	Not applicable as no plug-in tap-off units has been included
2	Degree of protection of enclosures	10.3	Verified
	External enclosure		IP42/IP20
3	Clearances	10.4	Verified for $U_{imp} = 8 \text{ kV}$
4	Creepage distances	10.4	Verified for $U_i = 1000 \text{ V}$ Pollution degree 3 Material Group IIIa
5	Protection against electric shock and integrity of protective circuits:	10.5	Verified
	Effective continuity between the exposed conductive parts of the assembly and the protective circuit	10.5.2	Verified
	Short-circuit withstand strength of the protective circuit	10.5.3	Verified
* Note: Design verification tests required by IEC 61439-6: 2012, Annex D, Table D1. No Verification by testing was required for items 6, 7 and 8 clauses 10.6, 10.7 and 10.8.			

Project No: SHA042830

Certificate No: ASTA-TYPE-0002696

No	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
5	Protection against electric shock and integrity of protective circuits (continued):	10.5	Verified
	Earth busbar size: 630 A 3W4P earth bar integrated	10.5.3 and 10.11.5.6	$I_{cw} = 18.6$ kA rms for 1 sec $I_{pk} = 37.2$ kA peak
	630 A 3W5P earth bar separated 126.7 mm ² copper bar	10.5.3.3	$I_{cw} = 18.6$ kA rms for 1 sec $I_{pk} = 37.2$ kA peak
9	Dielectric Properties	10.9	Verified
	The BTS-Assembly		-
	Rated voltage		$U_n = 1000$ V
	Rated operational voltage		$U_e = 1000$ V
	Rated insulation voltage	10.9.2	$U_i = 1000$ V
	Rated impulse withstand voltage	10.9.3	$U_{imp} = 8$ kV
Testing of enclosures of insulating material	10.9.4	Verified	
External operation handles of insulating material	10.9.5	Not applicable	
10	Temperature rise	10.10	
	The rated current of the assemblies was based upon a mean/maximum ambient temperature of: Verification by testing Orientation: Horizontal	10.10.2	35/40°C
	Main busbar size: 630 A 4P (PE Integrated) 215.4 mm ² copper bar per phase	10.10.2.3.5	$I_{nA} = 630$ A
	630 A 5P (PE Separated) 215.4 mm ² copper bar per phase	10.10.3	$I_{nA} = 630$ A
11	Short-circuit withstand strength	10.11	
	Three-phase Main busbar size: 630 A 4P (PE Integrated) 215.4 mm ² copper bar per phase	10.11.5.3.3	$I_{cw} = 31$ kA rms for 1sec $I_{pk} = 65.1$ kA peak

Project No: SHA042830
Certificate No: ASTA-TYPE-0002696

No	Characteristic Verified	Clause/ Subclause	Verified Tests and Ratings
11	Short-circuit withstand strength (Continued)	10.11	
	630 A 5P (PE Separated) 215.4 mm ² copper bar per phase	10.11.3	I_{cw} = 31 kA rms for 1sec I_{pk} = 65.1 kA peak
	Neutral conductor Neutral busbar size: 630 A 4P (PE Integrated) 215.4 mm ² copper bar per phase	10.11.5.3.3	I_{cw} = 18.6 kA rms for 1 sec I_{pk} = 37.2 kA peak
	630 A 5P (PE Separated) 215.4 mm ² copper bar per phase	10.11.3	I_{cw} = 18.6 kA rms for 1 sec I_{pk} = 37.2 kA peak
12	Electromagnetic compatibility (EMC)	10.12	Conditions for no testing (J.9.4.3.1 and 9.4.4.1) verified
13	Mechanical operation	10.13	Not applicable to busbar trunking system

The record of proving tests is available in ASTA certificate No. ASTA-TYPE-000924 dated 9th February 2021.

The tests for clauses 10.2.5, 10.2.101, 10.3, 10.5, 10.9, 10.10 and 10.11 were performed on I-LINE Track 630A 4P considering to be representative of the I-LINE Track 630A 5P.

Note: The apparatus tested was manufactured by Schneider Busway (Guangzhou) Limited, No. 85 Junye Road, Eastern Section of Economic & Technological Development Zone, Guangzhou 510530, China, for which ASTA Certificate of Verification no. ASTA-TYPE-0001236R1, dated 24th January 2023 has been issued.

Project No: SHA042830

Certificate No: ASTA-TYPE-0002696

Certificate Contents:

The following documents are attached to and form part of this certificate:

Documents:	Number of pages
Test report no: 210603002GZA and YDY21-000776 dated 4 November 2021	50
Drawings	19

Certificate Revision Amendment Table

Certificate Number	Issue Date	Amendment
ASTA-TYPE-0002696	8th October 2023	Initial issue