

**Security related elements/components**

Type Designation	Description	Graphical Keypad Commercial reference / HW / SW	HW Revision	Product Variant	FW Revision	Report-No.:	Certification Status
ATH630	Altivar HVAC IP20	VW3A1123 / 0.0 / SV 2.1	0.0	U07N4(Z)	V1.1IExx (started from V1.1IE03)	968/CSP 1060.00/26	Valid
				U15N4(Z)		968/CSP 1060.00/26	Valid
				U22N4(Z)		968/CSP 1060.00/26	Valid
				U30N4(Z)		968/CSP 1060.00/26	Valid
				U40N4(Z)		968/CSP 1060.00/26	Valid
				U55N4(Z)		968/CSP 1060.00/26	Valid
				U75N4(Z)		968/CSP 1060.00/26	Valid
				D11N4(Z)		968/CSP 1060.00/26	Valid
				D15N4(Z)		968/CSP 1060.00/26	Valid
				D18N4(Z)		968/CSP 1060.00/26	Valid
				D22N4(Z)		968/CSP 1060.00/26	Valid
				D30N4(Z)		968/CSP 1060.00/26	Valid
				D37N4(Z)		968/CSP 1060.00/26	Valid
				D45N4(Z)		968/CSP 1060.00/26	Valid
				D55N4(Z)		968/CSP 1060.00/26	Valid
				D75N4(Z)		968/CSP 1060.00/26	Valid
				D90N4(Z)		968/CSP 1060.00/26	Valid
				C11N4Z		968/CSP 1060.00/26	Valid

Type Designation	Description	Graphical Keypad Commercial reference / HW / SW	HW Revision	Product Variant	FW Revision	Report-No.:	Certification Status
				C13N4Z		968/CSP 1060.00/26	Valid
				C16N4Z		968/CSP 1060.00/26	Valid
				C22N4Z		968/CSP 1060.00/26	Valid
				C25N4Z		968/CSP 1060.00/26	Valid
ATH650	Altivar HVAC IP55	VW3A1121 / 0.0 / SV 2.4	0.0	U07N4	V1.1IExx (started from V1.1IE03)	968/CSP 1060.00/26	Valid
				U15N4		968/CSP 1060.00/26	Valid
				U22N4		968/CSP 1060.00/26	Valid
				U30N4		968/CSP 1060.00/26	Valid
				U40N4		968/CSP 1060.00/26	Valid
				U55N4		968/CSP 1060.00/26	Valid
				U75N4		968/CSP 1060.00/26	Valid
				D11N4		968/CSP 1060.00/26	Valid
				D15N4		968/CSP 1060.00/26	Valid
				D18N4		968/CSP 1060.00/26	Valid
				D22N4		968/CSP 1060.00/26	Valid
				D30N4		968/CSP 1060.00/26	Valid
				D37N4		968/CSP 1060.00/26	Valid
				D45N4		968/CSP 1060.00/26	Valid
				D55N4		968/CSP 1060.00/26	Valid

Type Designation	Description	Graphical Keypad Commercial reference / HW / SW	HW Revision	Product Variant	FW Revision	Report-No.:	Certification Status
				D75N4		968/CSP 1060.00/26	Valid
				D90N4		968/CSP 1060.00/26	Valid
				U07N4C		968/CSP 1060.00/26	Valid
				U15N4C		968/CSP 1060.00/26	Valid
				U22N4C		968/CSP 1060.00/26	Valid
				U30N4C		968/CSP 1060.00/26	Valid
				U40N4C		968/CSP 1060.00/26	Valid
				U55N4C		968/CSP 1060.00/26	Valid
				U75N4C		968/CSP 1060.00/26	Valid
				D11N4C		968/CSP 1060.00/26	Valid
				D15N4C		968/CSP 1060.00/26	Valid
				D18N4C		968/CSP 1060.00/26	Valid
				D22N4U		968/CSP 1060.00/26	Valid
				D30N4U		968/CSP 1060.00/26	Valid
				D37N4U		968/CSP 1060.00/26	Valid
				D45N4U		968/CSP 1060.00/26	Valid
				D55N4U		968/CSP 1060.00/26	Valid
				D75N4U		968/CSP 1060.00/26	Valid
				D90N4U		968/CSP 1060.00/26	Valid

**Optional Communication Module included in Certification**

Type Designation	Description	Commercial reference / HW / SW	HW Revision	Product Variant	FW Revision	Report-No.:	Certification Status
VW3A3726	BacNet/IP fieldbus module	VW3A3726 / 1.1 / 1.0.x	2.2.1	NO	1.0. x (started from 1.0.IE7)	968/CSP 1060.00/26	Valid

**Important Note:**

- FW/SW Version Definition – (e.g. V1.1IE01) – is defined as “V<major>.<minor>IE”

**The content of this Revision List has been agreed between Manufacturer and Certification Body.**

**Revision:**

Date	Rev.	Description / Changes	Author
2026-04-15	1.0	Initial creation, based on Report-No.: 968/CSP 1060.00/25	FD/A-FS