

CERTIFICATE OF APPROVAL

Authorised marking: TUV-026442-EA

TÜV Rheinland Australia Pty Ltd "Electrical Product Safety Certification (EPSC) Scheme", accredited by JAS-ANZ in accordance with ISO/IEC 17065, has issued this certificate under the Gas and Electricity (Consumer safety) Act 2017 as a declared Recognised External Approval Scheme (REAS). The electrical equipment described hereunder has been evaluated and found to be electrically safe at the time of certification. It is a requirement that all equipment supplied under this certificate shall be identical to the equipment as certified. The certificate holder shall place the above mentioned authorised marking on the product. The certificate holder may use the Regulatory Compliance Mark (RCM) provided all the requirements of AS/NZS 4417.1 & AS/NZS 4417.2 applicable to the article are fulfilled.

CERTIFICATE HOLDER:

Schneider Electric
(Australia) Pty. Ltd.
33-37 Port Wakefield Road
Gepps Cross SA 5094
Australia

DESCRIPTION OF EQUIPMENT

Declared class: RESIDUAL CURRENT DEVICE
Product: Residual current device with Integral Overcurrent Protection
Trade Name / Manufacturer: Schneider Electric®
Model Number: Vigi C120 series RCBOs
Ratings: Ratings refer to Continuation Sheets 1 to 4 for details
Remarks: Alternative Authorised Marking "TUV022699EA" is applicable to above mentioned model.

Standard: AS/NZS 61009.1:2015

Issue Date: 23/05/2023

Expiry Date: 23/05/2028

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



CERTIFICATE OF APPROVAL

Authorised marking: TUV-026442-EA

CONTINUATION SHEET 1

Description of Equipment

Schneider Vigi C120 series RCBO with associated C120N

series MCB:

For all Vigi C120 series:

Rated Frequency(Hz) / Rated Current In (A)/ Tripping Curve:

50 / 63,80,100,125 / B,C.

Model Number/ No. of Poles/ Rated Voltage Un(V) /

Rated Residual Operating Current I_{Δn} (mA) / Type /

Generic model number:

A9N18572 / 2 / 230/240V~/ 30 /A/ VC1202PA030;

A9N18573 / 2 / 230/240V~400/415V~/ 300 /A/ VC1202PA300;

A9N18575 / 3 / 400/415V~/ 30 / A / VC1203PA030;

A9N18576 / 3 / 230/240V~/400/415V~/ 300 /A/ VC1203PA300;

A9N18578 / 4 / 400/415V~/ 30 /A/ VC1204PA030;

A9N18579 / 4 / 230/240V~/400/ 415V~/ 300 /A/ VC1204PA300;

A9N18587 / 4 / 230/240V~/400/415V~/ 300 /S-A/ VC1204PA300;

A9N 18591 / 2 / 230/240V~/ 30 /A,SI/ VC 1202PSI030;

A9N18592 / 2 / 240/415 / 300 /A,SI/ VC1202PSI300;

A9N18594 / 3 / 400/415V~/ 30 /A,SI/ VC1203PSI030;

A9N18595 / 3 / 230/240V~/400/415V~/ 300 /A,SI/ VC1203PSI300;

A9N 18597 / 4 / 400/ 415 V~/ 30 /A,SI/ VC1204PSI030;

A9N18598 / 4 / 230/240V~/400/415V~/ 300 /A,SI/ VC1204PSI300;

Issue Date: 23/05/2023

Expiry Date: 23/05/2028

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



CERTIFICATE OF APPROVAL

Authorised marking: TUV-026442-EA

CONTINUATION SHEET 2

Description of Equipment

A9N18556 / 2 / 230/240V~/400/415V~/300 / S-A,SI /
VC1202PSI300;
A9N 18558 / 3 / 230/240V~/400/415V~/300 / S-A,SI /
VC1203PSI300;
A9N 18560 / 4 / 230/240V~/400/415V~/300 / S-A,SI /
VC1204PSI300.

Schneider C120N Miniature Circuit Breaker's(MCB's) used
in construction of Vigi C120 series RCBOs:

For all Schneider C120N MCB's:

Rated Short-circuit Capacity Icn (kA): 10.

Product Equipment/ Model Number / Tripping Curve:

C120N 1 P 63A B 10000A 230/240V~/400/415V~ MCB /
A9N18340 / B;
C120N 1P 80A B 10000A 230/240V~/400/415V~ MCB /
A9N18341 / B;
C120N 1P 100A B 10000A 230/240V~/400/415V~ MCB /
A9N18342 / B;
C120N 1P 125A B 10000A 230/240V~/400/415V~ MCB /
A9N18343 / B;
C120N 2P 63A B 10000A 400/415V~ MCB / A9N18344 / B;
C120N 2P 80A B 10000A 400/415V~ MCB / A9N18345 / B;

Issue Date: 23/05/2023

Expiry Date: 23/05/2028

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



www.jas-anz.org/register

CERTIFICATE OF APPROVAL

Authorised marking: TUV-026442-EA

CONTINUATION SHEET 3

Description of Equipment

C120N 2P 100A B 10000A 400/415V~ MCB / A9N18346 / B;
C120N 2P 125A B 10000A 400/415V~ MCB / A9N18347 / B;
C120N 3P 63A B 10000A 400/ 415V~ MCB / A9N18348 / B;
C120N 3P 80A B 10000A 400/ 415V~ MCB / A9N18349 / B;
C120N 3P 100A B 10000A 400/ 415V~ MCB / A9N18350 / B;
C120N 3P 125A B 10000A 400/ 415V~ MCB / A9N18351 / B;
C120N 4P 63A B 10000A 400/ 415V~ MCB / A9N18352 / B;
C120N 4P 80A B 10000A 400/ 415V~ MCB / A9N18353 / B;
C120N 4P 100A B 10000A 400/ 415V~ MCB / A9N18354 / B;
C120N 4P 125A B 10000A 400/ 415V~ MCB / A9N18355 / B;

Schneider C120N Miniature Circuit Breaker's(MCB's) used
in construction of Vigi C120 series RCBOs:

For all Schneider C120N MCB's:

Rated Short-circuit Capacity Icn (kA): 10.

Product Equipment / Model Number/ Tripping Curve:

C 120N 1 P 63A C 1 0000A 230/240V~/400/415V~ MCB /
A9N 18356 / C;
C120N 1P 80A C 10000A 230/240V~/400/415V~ MCB /
A9N18357 / C;
C120N 1P 100A C 10000A 230/240V~/400/415V~ MCB /
A9N18358 / C;

Issue Date: 23/05/2023

Expiry Date: 23/05/2028

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li



CERTIFICATE OF APPROVAL

Authorised marking: TUV-026442-EA

CONTINUATION SHEET 4

Description of Equipment

C 120N 1 P 125A C 1 0000A 230/240V~/400/415V~ MCB / A9N 18359 / C;
C120N 2P 63A C 10000A 400/415V~ MCB / A9N18360 / C;
C120N 2P 80A C 10000A 400/415V~ MCB / A9N18361 / C;
C120N 2P 100A C 10000A 400/415V~ MCB / A9N18362 / C;
C120N 2P 125A C 10000A 400/415V~ MCB / A9N18363 / C;
C120N 3P 63A C 10000A 400/415V~ MCB / A9N18364 / C;
C120N 3P 80A C 10000A 400/415V~ MCB / A9N18365 / C;
C120N 3P 100A C 10000A 400/415V~ MCB / A9N18367 / C;
C120N 3P 125A C 10000A 400/415V~ MCB / A9N18369 / C;
C120N 4P 63A C 10000A 400/415V~ MCB / A9N18371 / C;
C120N 4P 80A C 10000A 400/415V~ MCB / A9N18372 / C;
C120N 4P 100A C 10000A 400/415V~ MCB / A9N18374 / C;
C120N 4P 125A C 10000A 400/415V~ MCB / A9N18376 / C.

Issue Date: 23/05/2023

Expiry Date: 23/05/2028

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd



Grant Li

