

# Altivar Machine ATV340

V4.6IE39

## 1. Safety information

You can Download and install **EcoStruxure Automation Device Maintenance** here:

- <https://www.se.com/ww/en/download/document/EADM/>

Carefully read the instructions contained in the

**Altivar User Manual for EcoStruxure Automation Device Maintenance,**

- available here: <https://www.se.com/ww/en/download/document/JYT50472/>
- or available on *Windows Start Menu > EcoStruxure Automation Device Maintenance > Documents.*

## 2. Software enhancements in this version

- Introduced a new slip-compensation strategy in generator mode, configurable via the **SLPC [Gen Mode Slip Comp]** parameter.
- Expanded the allowable range of **PHS [Syn. EMF constant]** to support selected PM motors.
- Refined the behavior of **Synchronous Reluctance Motors [SRVC]** Control Law.
- Enhanced the configuration process for the I/O scanner.
- Enabled passive filter support within the **VVC [SVC V]** control law by activating the **IFI [Input Filter]** parameter.
- Added new parameters (**SMFP, SMBW, SMBA**) to mitigate encoder-related oscillations when using flexible couplings.
- Improved the availability and reliability of monitoring values for **IDAD [Opt Magn Current]** and **TRAD [Opt Rotor Time Const]**.
- Increased the upper limit of **BRTC [Braking Resist T Constant]** to accommodate braking resistors with heavy-duty cycles.
- Improved RTC handling at power-on after extended storage periods to avoid INFL issues.
- Refined the behavior of analog input intermediate points (**Alx**) at range boundaries.
- Improved configuration switching behavior when mixing open-loop and closed-loop modes to prevent unexpected **MDCF** events.
- **Hoisting:** The **TDCL [TDC Rope Length]** parameter can now be modified while the motor is running.
- Enhanced **undervoltage handling functions** when **AEMC [Adv. Motor Control] = Yes**
- Implemented additional cybersecurity enhancements.

## 3. Notes

- To ensure that the new parameters and menus are correctly displayed, the Altivar Graphic Display Terminal labels can be updated. Refer to the instructions inside [https://www.se.com/ww/en/download/document/Languages\\_Drives\\_VW3A1111/](https://www.se.com/ww/en/download/document/Languages_Drives_VW3A1111/)

## 4. Software enhancements history

### Version V4.5IE38

- [Hoisting] Improved behavior in Open Loop with Encoder
- [Hoisting] Support of a new feature: Time Delay Control
- Support of VW3A3530D ATV dPAC Module
- Ability to configure I/O scanner from Graphic Display Terminal
- [Master / Slave] Improved behavior at Power ON
- Added new configuration of the braking resistor to be enabled only when motor is running
- Improved Undervoltage handling function
- [Braking] Offers consistent behavior of BRI and BCI settings
- [HMI] Improved refresh of Operating points for Torque curve
- Cybersecurity enhancements with the embedded Ethernet V2.3IE40

### Version V4.3IE37

- Firmware evolution to support the VW3A3802 Safety Module
- Firmware evolution to support the VW3A3809 Safety over Ethernet IP Module
- Firmware evolution to support the VW3A3807 PROFIsafe Module  
Improvement of the Safety Function SLS (Safely Limited Speed) behavior with the VW3A3802 Safety Module
- [DC bus management] CRDR parameter is now available via the Graphic Display terminal to set the Damping ratio of the current loop controller.
- Cybersecurity enhancements with the embedded Ethernet V2.3IE38B4
- Cybersecurity enhancements
- Enhancement of the motor setting by providing a recommendation on parameters [Magnetizing Current] IDA and [Rotor Time Const] TRA

### Version V4.2IE36

- [Ethernet] Cybersecurity enhancements with the embedded Ethernet V2.3IE37B1
- Cybersecurity enhancements
- Enhance the DC bus management by automatically activating the DC Bus Ripple monitoring
- Improve Torque Control behavior with long [Torque ramp time]
- Improve the internal errors description by displaying subcode on Error History
- Improve the Reference Copy on Channel switch to manage the bidirectional copy
- Extend the maximum Relay Holding time
- Improve the configuration save result on keypad when using more than 16 files
- Improve Master/Slave management on multi-motor switching
- Support of the new Profinet module VW3A3647

### Version V4.1IE35

- Added TTOB and TOUT timeout parameters to the Graphic Display Terminal menus.
- [High Speed Hoisting] Ability to set COR and COF up to 200%
- Improvement of Gain & offset management of measured voltage & current when PHR=ACB
- Support of Undervoltage handling function with DC supply
- Ability to reset Electrical Energy counters.
- Improved PID behavior when switching from Manu to Auto
- Improvement of Encoder check function
- [Ethernet] Improved handling of ETHF alarm when switching the command channel.
- [Ethernet] ATV340\*\*E Cybersecurity enhancements with the embedded Ethernet V2.3IE36B1

### Version V3.7IE33

- New parameters CRB (Current loop configured gain) and CRBA (Current loop default gain) now available to enhance the motor speed stability.
- High speed hoisting enhancement to avoid sporadic SCF1, ANF or OPF in specific use case.
- Improvement of the AB Encoder feedback in closed loop in Ready mode.
- PID behavior enhancement when the LSP (Low Speed) is different from 0.
- Improvement of the synchronous motor setting to avoid CFF in some specific cases.
- [Ethernet] ATV340\*\*E Ethernet cybersecurity enhancements with the embedded Ethernet V2.3IE35B1
- [Ethernet] ATV340\*\*E Improvement in EtherNet/IP with assembly 21/71 using messaging

### Version V3.6IE31

- It is now possible to set the parameter [Braking Resistor] BRC to [No] NO even when [Dec.Ramp Adapt] BRA is also set to [No] NO, which results in both the deceleration ramp adaptation and braking resistor deactivated at the same time.
- New possible setting [STO fct status] STOS is now available on drive outputs (digital outputs and relays). It allows to show the status of the Safe Torque Off STO function.
- In the menu [Motor monitoring] MOP, new parameter [Torque Filter Time] TPFV has been added to define a filter time constant applicable on the non-filtered output torque and power.
- Setting the date and time through the display terminal is now possible with version V3.6IE31
- With VW3A3424 HTL encoder interface module, it is now possible to use an encoder having a pulse number [PGI] which is not a multiple of 2 or which is lower than 256.

#### About Schneider Electric

At Schneider Electric, we believe access to energy and digital is a basic human right. We empower all to make the most of their energy and resources, ensuring Life Is On everywhere, for everyone, at every moment. We provide energy and automation digital solutions for efficiency and sustainability. We combine world-leading energy technologies, real-time automation, software and services into integrated solutions for Homes, Buildings, Data Centers, Infrastructure and Industries. We are committed to unleash the infinite possibilities of an open, global, innovative community that is passionate about our Meaningful Purpose, Inclusive and Empowered values. [www.se.com](http://www.se.com)