



## UK DECLARATION OF CONFORMITY

**We : MANUFACTURER**  
**Schneider Electric Industries SAS**  
**35 rue Joseph Monier**  
**Rueil Malmaison 92500 – France**

**UK REPRESENTATIVE**  
**Schneider Electric Limited**  
**Stafford Park 5**  
**Telford, TF3 3BL - United Kingdom**

Hereby declare under our sole responsibility that the product:

|                                       |  |
|---------------------------------------|--|
| <b>Trademark</b>                      | <b>Schneider Electric</b>                        |
| <b>Product, Type</b>                  | ATVProcess <b>ATV630 / ATV930 - 600V</b> Series. |
| <b>List of references and options</b> | See next pages                                   |

are in conformity with the requirements of the following regulations and conformity was checked in accordance with the following standards.

| <b>Regulation</b>   | <b>Designated standard / Notified body reference</b>   |
|---|--|
| <b>Electrical Equipment (Safety) Regulations</b><br>SI 2016 No. 1101  | <b>EN 61800-5-1:2007</b><br><b>EN 61800-5-1:2007 + A1:2017</b><br><b>EN 61800-5-1:2007 + A11:2021</b><br>Adjustable speed electrical power drive systems – Part 5-1: Safety requirements – Electrical, thermal and energy.<br>Other standard considered: (IEC 61800-5-1:2016)      |
| <b>The Electromagnetic Compatibility Regulations</b><br>SI 2016 No. 1091  | <b>EN 61800-3:2004</b><br><b>EN 61800-3:2004/A1:2012</b><br>Adjustable speed electrical power drive systems – part 3: EMC requirements and specific test methods.<br>Other standard considered: (IEC 61800-3:2017)   |
| <b>The Ecodesign for Energy-Related Products Regulations</b><br>SI 2010 No 2617   | <b>EN 61800-9-2:2017</b><br>Ecodesign for power drive systems, motor starters, power electronics and their driven applications - Energy efficiency indicators for power drive systems and motor starters (IEC 61800-9-2:2017)  |
| <b>The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012</b><br>SI 2012 No. 3032 | <b>EN IEC 63000:2018</b><br>Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances.<br>Specific offer compliance information about RoHS are publicized on <a href="http://www.se.com">se.com</a> |

Subject to correct installation, maintenance and use conforming to its intended purpose, to the applicable regulations and standards, to the supplier's instructions and to accepted rules of the art.

This declaration becomes invalid in the case of any modification to the products not authorized by Schneider Electric.

Compliance with the ATEX, Machinery & EMC Regulation will require the application of the ATEX guide, Safety guide and EMC guide giving requirements, details and advices for installation of products used.

The guides are available on <http://www.se.com>

The undersigned also agrees to transmit relevant information in response to a reasoned request from any adequate way by a national authority.

**Person in charge of technical documentation:**

Sylvain Ballet, Schneider Toshiba Inverter Europe, rue André Blanchet, 27120 Pacy/Eure – France.

**Issued at Telford - United Kingdom (Representative): 2023-10-17**

DocuSigned by:

*David Williams*

485DFE6A98894C3...

**David WILLIAMS**  
 VP Marketing UK&I  
 Zone UK & Ireland

Name :

Customer Satisfaction & Quality - Vice President



## UK DECLARATION OF CONFORMITY

List of references :

Three phase 575V to 600Vac IP21

| Reference (1) | Range  |
|---------------|--------|
| ATV630D18S6   | 18.5KW |
| ATV630D22S6   | 22KW   |
| ATV630D30S6   | 30KW   |
| ATV630D37S6   | 37KW   |
| ATV630D45S6   | 45KW   |
| ATV630D55S6   | 55KW   |
| ATV630D75S6   | 75KW   |

|             |        |
|-------------|--------|
| ATV930D18S6 | 18.5KW |
| ATV930D22S6 | 22KW   |
| ATV930D30S6 | 30KW   |
| ATV930D37S6 | 37KW   |
| ATV930D45S6 | 45KW   |
| ATV930D55S6 | 55KW   |
| ATV930D75S6 | 75KW   |

(1) may be followed by 1 to 3 characters.



## UK DECLARATION OF CONFORMITY

| <b>Option module and accessories</b>               |              |
|--|--------------|
| Extention digital inputs & outputs + analog inputs | VW3A3203     |
| Extention relays outputs                           | VW3A3204     |
| EtherCat Bus extention                             | VW3A3601     |
| PROFIBUS DP V1                                     | VW3A3607     |
| PROFIBUS STRAIGHT CONNECTOR                        | LU9AD7       |
| CANOPEN Daisy Chain                                | VW3A3608     |
| CANOPEN SUB-D                                      | VW3A3618     |
| CANOPEN SCREW TERMINAL BLOCK                       | VW3A3628     |
| DEVICENET  | VW3A3609     |
| PROFINET   | VW3A3627     |
| Ethernet IP & Modbus TCP                           | VW3A3720     |
| Ethernet IP & Modbus TCP & MD-Link                 | VW3A3721     |
| ATV dPAC Module                                    | VW3A3530D    |
| BACNET   | VW3A3725     |
| Digital encoder interface                          | VW3A3420     |
| Digital encoder interface                          | VW3A3422     |
| Resolver interface                                 | VW3A3423     |
| HTL encoder interface                              | VW3A3424     |
| ADVANCED KEYPAD                                    | VW3A1111     |
| Remote IP65 Mounting kit                           | VW3A1112     |
| BASIC KEYPAD                                       | VW3A1113     |
| IP65 remote connection kit for Ethernet            | VW3A1115     |
| Remote-mounting cordset 1m                         | VW3A1104R10  |
| Remote-mounting cordset 3m                         | VW3A1104R30  |
| Remote-mounting cordset 5m                         | VW3A1104R50  |
| Remote-mounting cordset 10m                        | VW3A1104R100 |
| Interconnection cable 0.3m                         | VW3A8306R03  |
| Interconnection cable 1m                           | VW3A8306R10  |
| Interconnection cable 3m                           | VW3A8306R30  |
| Modbus line terminator                             | VW3A8306RC   |
| Straight shielded twisted pair cables 2m           | 490NTW00002  |
| Straight shielded twisted pair cables 5m           | 490NTW00005  |
| Straight shielded twisted pair cables 12m          | 490NTW00012  |
| Pocket Wi-Fi dongle                                | TCSEGB13FA0  |