

Certificate Number: AZ 69024131

Page: 0001



CERTIFICATE OF APPROVAL

Authorised marking: TUV024131EA

This is to certify that TÜV Rheinland Australia Pty Ltd as accredited by JAS-ANZ in accordance with ISO/IEC Guide 65 has examined for compliance with certification standards, the electrical equipment described hereunder and authorises the certificate holder to affix the above mentioned mark to products of the same type; or the Regulatory Compliance Mark (RCM) provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled

CERTIFICATE HOLDER:

Schneider Electric (Australia) Pty. Ltd.
33-37 Port Wakefield Road
Gepps Cross, SA 5094
Australia

DESCRIPTION OF EQUIPMENT

Declared class:

SOCKET-OUTLET

Product:

RCD Protected Twin Switched Socket Outlet

Trade Name / Manufacturer:

Clipsal ; PDL .

Model Number:

P3025RCD10 ; P395RCD10

Ratings:

250V~, 50Hz

Clipsal: P3025RCD10:Socket: 10A, RCD: 20A, I_{Δn} 10mA, Type I

PDL: P395RCD10:Socket: 10A, RCD: 20A, I_{Δn} 10mA, Type I

Standard:

AS/NZS 3112:2017

AS/NZS 3190:2016

AS/NZS 3133:2013+A1+A2

AS/NZS 3100:2017+A1

Issue Date:

17/03/2020

Expiry Date:

17/03/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

A handwritten signature in black ink, appearing to read "Grant Li".

Grant Li



Acc. No. Z2870404AA
www.jas-anz.org/register

TÜV Rheinland Australia Pty Ltd
182 Dougherty Road, Heidelberg West VIC 3081
Phone: +61 (3) 9450 1400
Email: certification@au.tuv.com
Website: www.au.tuv.com

Certificate Number: AZ 69024131

Page: 0002



CERTIFICATE OF APPROVAL

Authorised marking: TUV024131EA

CONTINUATION SHEET 1

(Modification 1)

Add additional models:

Clipsal : 3025RCD30 : Socket: 250V~, 50Hz, 10A, RCD: 20A,
IΔn 30mA, 3kA, Type II

PDL : 395RCD30 : Socket: 250V ~, 50Hz, 10A, RCD: 20A,
IΔn 30mA, 3kA, Type II

PDL : 391RCD30 : Socket: 250V ~, 50Hz, 10A, RCD: 20A,
IΔn 30mA, 3kA, Type II

Clipsal : P3025RCD30 : Socket: 250V ~, 50Hz, 10A,
RCD: 20A, IΔn 30mA, 3kA, Type II

PDL : P395RCD30 : Socket: 250V ~, 50Hz, 10A, RCD: 20A,
IΔn 30mA, 3kA, Type II

PDL : P391RCD30 : Socket: 250V ~, 50Hz, 10A, RCD: 20A,
IΔn 30mA, 3kA, Type II

- Add alternative plunger for all models 10mA and 30mA.

- Add alternative core of sensing coil for 10mA models.

Test standard update:

From: AS/NZS 3100:2017 + A1

To: AS/NZS 3100:2017 + A1 + A2 + A3

Issue Date: 16/06/2020

Expiry Date: 17/03/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

A handwritten signature in black ink, appearing to read "Billy Chu".

Billy Chu



Acc. No. Z2870404AA
www.jas-anz.org/register

TÜV Rheinland Australia Pty Ltd
182 Dougherty Road, Heidelberg West VIC 3081
Phone: +61 (3) 9450 1400
Email: certification@au.tuv.com
Website: www.au.tuv.com

Certificate Number: AZ 69024131

Page: 0003



CERTIFICATE OF APPROVAL

Authorised marking: TUV024131EA

CONTINUATION SHEET 2

(Modification 2)

Modify voltage rating for RCD module:

Socket: 250V~, 50Hz, 10A, RCD: 230-240V~, 20A, I Δ n 10mA,
Type I

Socket: 250V~, 50Hz, 10A, RCD: 230-240V~, 20A, I Δ n 30mA,
3kA, Type II

Issue Date: 22/12/2021

Expiry Date: 17/03/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

TÜV Rheinland

A handwritten signature in blue ink, appearing to read "Grant Li", positioned above a horizontal line.

Grant Li

JAS-ANZ



Acc. No. Z2870404AA
www.jas-anz.org/register

TUV Rheinland Australia Pty Ltd
182 Dougherty Road, Heidelberg West VIC 3081
Phone: +61 (3) 9450 1400
Email: certification@au.tuv.com
Website: www.au.tuv.com