

Certificate Number: AZ 69024266

Page: 0001



CERTIFICATE OF APPROVAL

Authorised marking: TUV024266EA

This is to certify that TÜV Rheinland Australia Pty Ltd as accredited by JAS-ANZ in accordance with ISO/IEC Guide 65 has examined for compliance with certification standards, the electrical equipment described hereunder and authorises the certificate holder to affix the above mentioned mark to products of the same type; or the Regulatory Compliance Mark (RCM) provided that the requirements of all relevant parts of AS/NZS 4417 applicable to the article are fulfilled

CERTIFICATE HOLDER:

Schneider Electric
33-37 Port Wakefield Road
Gepps Cross SA 5094
Australia

DESCRIPTION OF EQUIPMENT

Declared class:

SOCKET-OUTLET

Product:

RCD Protected Twin Switched Socket Outlet

Trade Name / Manufacturer:

Clipsal , PDL

Model Number:

Model Number details refer to CONTINUATION SHEET 1

Ratings:

230-240V a.c., 50Hz,
Socket: 10A, RCD: 20A, 3kA,
Further Ratings refer to CONTINUATION SHEET 1

Standard:

AS/NZS 3112:2017
AS/NZS 3190:2016
AS/NZS 3133:2013+A1+A2
AS/NZS 3100:2017+A1+A2+A3

Issue Date:

19/05/2020

Expiry Date:

19/05/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

A handwritten signature in black ink, appearing to read 'Billy Chu'.

Billy Chu



Acc. No. Z2870404AA
www.jas-anz.org/register

Certificate Number: AZ 69024266

Page: 0002



CERTIFICATE OF APPROVAL

Authorised marking: TUV024266EA

CONTINUATION SHEET 1

DESCRIPTION OF EQUIPMENT

RCD protected socket outlet:

Clipsal type 2025RCD10 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

Clipsal type 2025RCD10C : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

Clipsal type C2025RCD10 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

Clipsal type ML2025RCD10 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

Clipsal type ML2025RCD10C : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

Clipsal type 2025RCD30 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 30mA, 3kA, Type II

Clipsal type C2025RCD30 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 30mA, 3kA, Type II

PDL type 695RCD-10 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 10mA, 3kA, Type I

PDL type 695RCD-30 : Socket: 230-240Va.c. 50Hz, 10A;

RCD: 20A, I Δ n 30mA, 3kA, Type II

Issue Date: 19/05/2020

Expiry Date: 19/05/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

A handwritten signature in black ink, appearing to read 'Billy Chu'.

Billy Chu



Acc. No. Z2870404AA
www.jas-anz.org/register

Certificate Number: AZ 69024266

Page: 0003



CERTIFICATE OF APPROVAL

Authorised marking: TUV024266EA

CONTINUATION SHEET 2

(Modification 1)

- Add alternative plunger for all models 10mA and 30mA.
- Add alternative core of sensing coil for 10mA models.

Issue Date: 16/06/2020

Expiry Date: 19/05/2025

Signed for and on behalf of TÜV Rheinland Australia Pty Ltd

TÜVRheinland

A handwritten signature in blue ink, appearing to read 'Billy Chu', positioned above a horizontal line.

Billy Chu



Acc. No. Z2870404AA
www.jas-anz.org/register