

IEC**IECEE**

®

TM

Ref. Certif. No.

CN54657-M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Motor Circuit-breaker

Name and address of the applicant

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the manufacturer

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Name and address of the factory

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suide Road, Putuo District, Shanghai, P.R.China

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

GZ1E,GZ1N,GZ1LE, GZ1N..S270;

Additional information (if necessary may also be reported on page 2)

The latest CB certificate No. is CN54657-M1, dated 2023-05-04. The issuance of the M2 certificate is to change suppliers of critical components.

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016/AMD1:2019;IEC 60947-2:2016(5th Edition);IEC 60947-4-1:2018;IEC 60947-1:2007;IEC 60947-1:2007/AMD1:2010;IEC 60947-1:2007/AMD2:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2021CQC-097036-1-M2,
00901-CB2021CQC-097036-2-M2**CHINA QUALITY CERTIFICATION CENTRE CO., LTD.**Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Aug.28,2024

Signature:

Xie ZhaoXu

GZ1E, GZ1N, GZ1LE, GZ1N...S270

Uimp: 6kV;

Ui: 690V;

Ue: AC230/240V, AC400/415V, AC500V, AC690V;

In: (GZ1E, GZ1N): 0.16A, 0.25A, 0.4A, 0.63A, 1A, 1.6A, 2.5A, 4A, 6.3A, 10A, 14A, 18A, 23A, 25A, 32A;

(GZ1LE): 0.4A, 0.63A, 1A, 1.6A, 2.5A, 4A, 6.3A, 10A, 14A, 18A, 23A, 25A, 32A;

Over-current release: Thermo-magnetic(GZ1E, GZ1N), Electro-magnetic(GZ1LE);

Ics, Icu:

AC230/240V: 23~32A: Ics: 100%Icu, Icu: 30kA

0.16~18A: Ics: 100%Icu, Icu: 100kA

AC400/415V: 23~32A: Ics: 40%Icu, Icu: 10kA

14~18A: Ics: 50%Icu, Icu: 10kA

0.16~10A: Ics: 100%Icu, Icu: 100kA

AC500V: 23~32A: Ics: 75%Icu, Icu: 3kA

14~18A: Ics: 75%Icu, Icu: 5kA

10A: Ics: 100%Icu, Icu: 8kA

6.3A: Ics: 100%Icu, Icu: 30kA

0.16~4A: Ics: 100%Icu, Icu: 100kA

AC690V: 2.5~32A: Ics: 75%Icu, Icu: 2kA

0.16~1.6A: Ics: 100%Icu, Icu: 100kA

Selectivity category: A;

Utilization category: AC-3, AC-3e;

Suitable for isolation;

50/60Hz;

Tripping class:10A;

3P

Page 1 of 1

Additional information (if necessary)

Date:

Aug.28,2024

Signature:

谢肇煦

Xie ZhaoXu