


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product	Enclosures for pre-determined equipment for household and similar fixed electrical installations
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIE ITALIA S.p.A. Via Circonvallazione Est, 1 24040 – Stezzano (BG) Italy
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC INDUSTRIE ITALIA S.p.A. Via Circonvallazione Est, 1 24040 – Stezzano (BG) Italy
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Flush-mounting enclosures; -25 °C to +60 °C; IP40; rated current = 50 or 63 A; rated voltage = 230/400 V; rated insulation voltage = 400 V (see also pages 4 and 24 of Test Report MI17-0015348-02 and Additional Sheet)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series MiniPragma (see Additional Sheet)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60670-1:2002, IEC 60670-1:2002/AMD1:2011, IEC 60670-24:2011
As shown in the Test Report Ref. No. which forms part of this Certificate	MI17-0015348-02

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43, IT-I-20138 Milano, Italy



**Description of flush-mounting enclosures series MiniPragma**

Type reference	Dimensions H × W × D (mm)	Number of modules / Number of DIN rail guides	Rated current (A)
MIPF104 <i>or</i> MIPF104FR	252 × 150 × 97	4 / 1	50
MIPF106 <i>or</i> MIPF106FR	252 × 186 × 97	6 / 1	63
MIPF108 <i>or</i> MIPF108FR	252 × 222 × 97	8 / 1	63
MIPF112 <i>or</i> MIPF112FR	252 × 294 × 98	12 / 1	63
MIPF118 <i>or</i> MIPF118FR	252 × 402 × 99	18 / 1	63
MIPF124 <i>or</i> MIPF124FR	377 × 294 × 98	24 / 2	63
MIPF136 <i>or</i> MIPF136FR	502 × 294 × 98	36 / 3	63