


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Residual current units for household and similar uses
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC ESPAÑA, S.A. Camino Barranquet, 57 46133 Meliana (Valencia) Spain
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	3P+N – Un = 400 V – In = max 25 A type A, A SI or AC – IΔn = 30 or 300 mA (Icn of the overcurrent circuit-breakers with which the r.c. units are intended to be associated: 10000 A) (see pages 5 and 7 of Test Report PB20-0050235-01-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series Vigi iQPN40 (see page 7 of Test Report PB20-0050235-01-00 or Additional Sheet)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61009-1:2010, IEC 61009-1:2010/AMD1:2012, IEC 61009-1:2010/AMD2:2013, IEC 61009-2-1:1991 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	PB20-0050235-01-00 and from PB20-0050235-01-01 to PB20-0050235-01-11

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-20138 Milano, Italy

Description of the residual current units series Vigi iQPN40

Series	Terminals	Type	Rated residual current (I Δ n)	Rated current (In)	Generic reference
Vigi iQPN40	Downstream terminals	A	300 mA	≤ 25 A	RCD3PN300A25L
		AC	300 mA	≤ 25 A	RCD3PN300AC25L
		A SI (1)	300 mA	≤ 25 A	RCD3PN300ASI25L
		A	30 mA	≤ 25 A	RCD3PN30A25L
		AC	30 mA	≤ 25 A	RCD3PN30AC25L
		A SI (1)	30 mA	≤ 25 A	RCD3PN30ASI25L

(1) – “A SI”-type residual current units are A-type residual current units having an intentional short-time delay

Description of the overcurrent circuit-breakers to which the residual current units series Vigi iQPN40 are intended to be associated

Series	Curve	Rated current	Rated short-circuit capacity	Generic reference
iQPN40	C	6 A	10 kA	MCB3PNSC1010C6
		10 A	10 kA	MCB3PNSC1010C10
		13 A	10 kA	MCB3PNSC1010C13
		16 A	10 kA	MCB3PNSC1010C16

Description of the RCBOs consisting of a residual current unit series Vigi iQPN40 assembled in the factory with an overcurrent circuit-breaker series iQPN40

Residual current unit			Circuit-breaker			RCBO	
Generic reference	Type	Rated residual current (I Δ n)	Generic reference	Curve	Rated current	Generic reference	Generic name
RCD3PN30A25L	A	30 mA	MCB3PNSC1010C6	C	6 A	RCBO3PNSC1010A30C6L	iQPN40 Vigi
RCD3PN30A25L	A	30 mA	MCB3PNSC1010C10	C	10 A	RCBO3PNSC1010A30C10L	iQPN40 Vigi
RCD3PN30A25L	A	30 mA	MCB3PNSC1010C13	C	13 A	RCBO3PNSC1010A30C13L	iQPN40 Vigi
RCD3PN30A25L	A	30 mA	MCB3PNSC1010C16	C	16 A	RCBO3PNSC1010A30C16L	iQPN40 Vigi