



Ref. Certif. No.

SE-71310A1/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Residual current operated circuit-breaker with integral overcurrent protection (RCBO's)

Name and address of the applicant

Schneider Shanghai Low Voltage Terminal Apparatus Co., Ltd.
1319 Pingan Rd., Minhang Zone, Shanghai,
P.R.CHINA

Name and address of the manufacturer

Same as applicant

Name and address of the factory

Note: When more than one factory, please report on page 2

Same as applicant

Ratings and principal characteristics

See page 2

Trademark (if any)

CLIPSAL

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

4RCBE, RCBE

Additional information (if necessary may also be reported on page 2)

See page 2

A sample of the product was tested and found to be in conformity with

IEC 61009-1:2010+A1+A2
IEC 61009-2-2:1991

As shown in the Test Report Ref. No. which forms part of this Certificate

170300488SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Box 1103
SE-164 22 Kista, Sweden
Int +46 8 750 00 00



Date: 7 August 2017

Signature:

Bo Berglöf

Ratings and principal characteristics

Model	Ue(V)	Icn(A)	IΔn(mA)	Type	In(A) and Type
4RCBE	240V	6000	10, 30	A, AC	C6, C10, C16, C20, C25, C32
4RCBE	110V	6000	30	A, AC	C6, C10, C16, C20, C25, C32
4RCBE	240V	4500	30	A, AC	C6, C10, C16, C20, C25, C32
RCBE	240V	4500	30	A, AC	C6, C10, C16, C20, C25, C32

Additional information (if necessary)

Covered also AS/NZS 61009.1-2015 and BS EN 61009-1:2012+A1:2014+A2:2014+A11:2015+A12:2016.

This Certificate replaces CB Certificate No. SE-71310M1, dated 10 July 2017. A new Certificate has been issued due to a revised applicant name.

Date: 7 August 2017

Signature: 