

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Isolating switches

Name and address of the applicant

Schneider Electric Industries SAS  
31 Rue Pierre Mendès France, Eybens, 38050 GRENOBLE CEDEX 9  
France

Name and address of the manufacturer

Schneider Electric Industries SAS  
31 Rue Pierre Mendès France, Eybens, 38050 GRENOBLE CEDEX 9  
France

Name and address of the factory

Schneider Electric Hungaria ZRt Zala Telephely  
Hock Janos ut. 55, 8900 ZALAEGRSZEG  
Hungary*Note: When more than one factory, please report on page 2* Additional information on page 2

Ratings and principal characteristics

See Appendix 1

Trademark / Brand (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Series iSW

Additional information (if necessary may also be reported on page 2)

See the Appendix.  
 Additional information on page 2

A sample of the product was tested and found to be in conformity with


IEC 60669-2-4:2004

**Comments:**  
To be used in conjunction with IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

58182203/00 and 58182202/00, 58182201/00 up to 58182201/07

This CB Test Certificate is issued by the National Certification Body

SGS Belgium N.V. – Division SGS-CEBEC  
Riverside Business Park , Bld Internationelelaan 55 , Build. A  
BRUSSELS 1070  
Belgium

Date: 2024-11-18

Signature: Calogero Lana

**Ratings:**

number of poles	:	1P, 2P, 3P & 4P
pattern no(s).	:	1, 2, 3 & 03
rated voltage (Un)	:	250 Vac (1P) and 415 Vac (2P, 3P & 4P)
rated current (In)	:	20 A & 32 A
rated insulation voltage (Ui)	:	500 V
utilization category	:	AC22A
method of actuating	:	tumbler
rated conditional short-circuit current	:	3 kA
degree of protection	:	IP20 / IP40 under frame
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

0 1 2 3 4 5

CEBEC

Product References:

Base Modules				Ratings	
	Ref	P	Pattern	In (A)	Un (V)
<i>iSW</i>	A9S60120	1	1	20	250
	A9S60220	2	2	20	415
	A9S60320	3	3	20	415
	A9S60420	4	03	20	415
	A9S60132	1	1	32	250
	A9S60232	2	2	32	415
	A9S60332	3	3	32	415
	A9S60432	4	03	32	415
<i>iSW with indicator light</i>	A9S61120	1	1	20	250
	A9S61220	2	2	20	250
	A9S61132	1	1	32	250
	A9S61232	2	2	32	250

