




Ref. Certif. No.

DK-181358-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Emergency stop push button switch
Name and address of the applicant	Schneider Electric Industries SAS Boulevard Salvador Allende, ZI N°3 – BP 660 L'isle D'espagnac 16 340 France
Name and address of the manufacturer	Schneider Electric Industries SAS Boulevard Salvador Allende, ZI N°3 – BP 660 L'isle D'espagnac 16 340 France
Name and address of the factory	Schneider Electric France Zone industrielle, BP 660 F16340 L'Isle d'Espagnac, France <input checked="" type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Utilization Category: AC15 – DC-13 A600 – Q600 A300 – Q300 – P300 B300 – R300 Resistive <input checked="" type="checkbox"/> Additional Information on page 2-3
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	E-stops series XB5, E-stops series ZB4, E-stops series ZB5, E-stops series XB4, Stations: XALK84, XALK178, Illuminated Ring: ZBY9W series. <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	The certificate was revised to include corrections. <input checked="" type="checkbox"/> Additional Information on page 3
A sample of the product was tested and found to be in conformity with	IEC 60947-5-5:1997, IEC 60947-5-5:1997/AMD1:2005, IEC 60947-5-5:1997/AMD2:2016, IEC 60947-1:2007, IEC 60947-1:2007/AMD1:2010, IEC 60947-1:2007/AMD2:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	4791611927B issued on 2026-06-01

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-29
Original Issue Date: 2026-06-10

Signature: Thomas Wilson



Ref. Certif. No.

DK-181358-A1-UL

Factory(ies):

Schneider Electric a. s.
Cizovska 447
397 01 Pisek,
Czech Republic

PT. Schneider Electric Manufacturing Batam
Batamindo Industrial Park JL Beringin Lot 1, 4 & 208,
Muka Kuning Batam
29433ID
Indonesia

Additional Model Detail(s):

Stations: XALK84, XALK178 followed additional suffixes., followed by additional suffixes
E-stops series ZB5, E-stops series ZB4, E-stops series XB5, E-stops series XB4, followed by BS83, BS84, BS86, BS93, BS94, BS96, BT84, BX84, AS83, AS84, AS86, AS93, AS94, AS96, AT84, AT86, AX84 followed by additional suffixes, and fitted with contact blocks : ZB..Z009 + ZBE, ZEN or ZB2 followed by additional digits.
Illuminated Ring: ZBY9W series.,
See test report for details

Additional Ratings:

Supply Rating:
24 V – 0.1 A

Rated Operational Voltage Ue:

120 Vac, 240 Vac,
125 Vdc, 250 Vdc
120 Vac, 240 Vac,
600 Vac,
125 Vdc, 250 Vdc,
600 Vdc
120 Vac, 240 Vac,
600 Vac,
125 Vdc, 250 Vdc
24 V

Uc / Us: same as Ue

Rated Insulation Voltage Ui:

250 V
500 V
600 V

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-29
Original Issue Date: 2026-06-10

Signature:

Thomas Wilson



Ref. Certif. No.

DK-181358-A1-UL

Additional Ratings:

Rated Impulse Withstand Voltage: Uimp:

4 kV

6 kV

Conventional free air thermal current Ith:

6 A

10 A

Conventional enclosed thermal current Ithe:

6 A

10 A

Rated Operational Current:

6 Aac, 3 Aac,

1,2 Aac,

0,55 Adc,

0,27 Adc, 0,1 Adc

0,22 Adc

1,1 Adc

1,5 Aac

Rated frequency:

50 – 60 Hz

Rated conditional short circuit current:

1000 A

Class of insulation:

I (for XB4 series)

II (for XB5 series)

Protection degree:

66 (front, all), Including ZB4BZ014,

67 (front, only for ZB5AS84W, XALK84W, XALK178W series)

20 (back, all)

Pollution Degree: 3

Ambient Air Temperature for Operation / Storage -40...70 °C

See test report for complete set of ratings vs. Models covered

Summary of Modifications:

Correction to model name in certificate ONLY

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-29

Original Issue Date: 2026-06-10

Signature:

Thomas Wilson