



Ref. Certif. No.
SE-105653

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)

Name and address of the applicant

Schneider Electric Industries SAS
35 rue Joseph Monier
92500 Rueil-Malmaison, France

Name and address of the manufacturer

Same as applicant

Name and address of the factory

Note: When more than one factory, please report on page 2

Schneider Shanghai Low Voltage Terminal Apparatus Co., Ltd.
1319 Pingan Rd. Minhang Zone, Shanghai, P.R.China

Ratings and principal characteristics

Un= 240V~, 1P+N, 50/60Hz
In= 10, 16, 20, 25, 32, 40A, C- Type IΔn= 0,03A, Type-A, -AC
Ics= Icn= 6000A, IΔM=3000A
Energy limiting class 3

Trademark (if any)

CLIPSAL

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

MAX9

Additional information (if necessary may also be reported on page 2)

Covered also AS/NZS 61009.1:2015,
BS EN 61009-1:2012+A1:2014+A2:2014+A11:2015+A12:2016,
EN 61009-1:2012+A1:2014+A2:2014+A11:2015+A12:2016.

A sample of the product was tested and found to be in conformity with

IEC 61009-2-2:1991, IEC 61009-1:2010+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

210501338SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

intertek

Signature:

Date: 11 August, 2021

Leif Mattsson