

IEC**IECEE**

®

TM

Ref. Certif. No.

CN48440-M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

AC Contactors

Name and address of the applicant

Schneider Shanghai Industrial Control Co., Ltd.
No.629 Suid Road, Putuo District, Shanghai, P.R.China

Name and address of the manufacturer

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

SCHNEIDER ELECTRIC INDIA Pvt. Ltd
Survey No.215, Village – Gagillapur Medak Road, Rangareddy
District, Hyderabad – 500 043, (A.P.) India*Note: When more than one factory, please report on page 2*

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

LC1E32..., LC1E38..., LC1E40B...;

Additional information (if necessary may also be reported on page 2)

The latest CB certificate No. is CN48440-M1, dated 2022-06-06. The M2 certificate has been issued to add parameters.

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2019CQC-088502-M2

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRESection 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>

Date: Jan.09,2023

Signature:

谢肇煦

Xie ZhaoXu

CB 0070582

LC1E32..., LC1E38..., LC1E40B...

Ui: 690V;Uimp:6kV;lth: 50A;

LC1E32...:

AC-3: Ue/ Ie: 220/230/32A, 380V/32A, 400/415V/32A, 440V/ 32A;

AC-3e: Ue/ Ie: 220/230/32A, 380V/32A, 400/415V/32A, 440V/ 32A;

AC-4: Ue/ Ie: 220/230/26.7A, 380V/26.7A, 400/415V/26.7A,440V / 26.7A;

LC1E38...:

AC-3: Ue/ Ie: 220/230/38A, 380V/38A, 400/415V/38A, 440V / 38A;

AC-3e: Ue/ Ie: 220/230/38A, 380V/38A, 400/415V/38A, 440V / 38A;

AC-4: Ue/ Ie: 220/230/31.7A, 380V/31.7A, 400/415V/31.7A, 440V/ 31.7A;

LC1E40B...:

AC-3: Ue/ Ie: 220/230/40A, 380V/40A, 400/415V/40A, 440V/ 40A;

AC-3e: Ue/ Ie: 220/230/40A, 380V/40A, 400/415V/40A, 440V/ 40A;

AC-4: Ue/ Ie: 220/230/33.3A, 380V/33.3A, 400/415V/33.3A, 440V/ 33.3A;

Us: AC50Hz: 24V, 36V, 48V, 110V, 220V, 240V, 380V, 415V, 440V;

AC60Hz: 24V, 110V, 220V, 380V, 440V;

AC50/60Hz: 24V, 48V, 110V, 220V, 230V, 380V;

AC50Hz (70%~120%Us): 220V, 415V;

Rated frequency: 50/60Hz;

3P;

Auxiliary contacts:(body contact)

Ith: 10A;

AC-15:Ue/Ie:380V/1.3A, 660V/0.75A;

DC-13:Ue/Ie:220V/0.3A;

1NO, 1NC

Page 1 of 1

Additional information (if necessary)

Date: Jan.09,2023

Signature:



Xie ZhaoXu