

IEC**IECEE**

®

TM

Ref. Certif. No.

CN50262-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

AC Contactor

Name and address of the applicant

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, Hubei Province, P.R.China

Name and address of the manufacturer

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, Hubei Province, P.R.China

Name and address of the factory

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, P.R.China*Note: When more than one factory, please report on page 2*

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

LC1N25, LC1E25...

Additional information (if necessary may also be reported on page 2)

Original CB certificate No. is CN50262, dated 2020-05-21.
The M1 modification is to change parameters.

A sample of the product was tested and found to be in conformity with

IEC 60947-4-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

CB2020CQC-090871-M1

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE


Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: <http://www.cqc.com.cn>

Date: Sep.27,2022

Signature:



Xie ZhaoXu

**CB 0067640**

LC1N25, LC1E25...

Ui:690V;

Uimp:6kV;

Ith:32A(LC1N25),36A(LC1E25...);

LC1N25:AC-3:Ue/Ie: 220/230/380V/25A, 400/415V /25A, 440V /25A, 660V/16.5A;

AC-3e: Ue/Ie: 220/230/380V/25A, 400/415V /25A, 440V /25A, 660V/16.5A;

AC-4:Ue/Ie: 220/230/380V/20.9A, 400/415V /20.9A, 440V /20.9A, 660V/13.8A;

LC1E25...: AC-3:Ue/Ie: 220/230/380V/25A, 400/415V /25A, 440V /25A;

AC-3e: Ue/Ie: 220/230/380V/25A, 400/415V /25A, 440V /25A;

AC-4:Ue/Ie: 220/230/380V/20.9A, 400/415V /20.9A, 440V /20.9A;

Us: AC24V, 36V, 48V, 110V, 220V, 240V, 380V, 415V, 440V 50Hz;

AC24V, 110V, 220V, 380V, 440V 60Hz;

AC24V, 48V, 110V, 220V, 230V, 380V 50/60Hz;

3P;

Auxiliary contacts:(body contact)

1NC1NO;

Ith: 10A;

Ue/Ie: AC-15: 380V/1.3A, 660V/0.75A;

DC-13: 220V/0.3A

Page 1 of 3

Additional information (if necessary)

Date: Sep.27,2022

Signature:

谢肇旭

Xie ZhaoXu

<u>LC1E</u>	<u>25</u>	<u>10</u>	<u>M</u>	<u>5</u>	<u>N</u>
I	II	III	IV	V	VI

I	Basic product type: LC1E/ LC1N AC Contactor type
II	Product size 25
III	Auxiliary contact type 10: 1NO 01: 1NC
IV	Coil code See table 2
V	Coil frequency(See table 2) 5: 50Hz 6: 60Hz 7: 50/60Hz
VI	Option N: - LC1N...N China offer optimized type ("N" is only marked on the package label) Blank: - LC1E... Global offer except China optimized type

Additional information (if necessary)

Date: Sep.27,2022

Signature:



Xie ZhaoXu

Table 2

Coil code	voltage -frequency
B5	24V-AC50Hz
CC5	36V-AC50Hz
E5	48V- AC50Hz
F5	110V- AC50Hz
M5	220V- AC50Hz
U5	240V- AC50Hz
Q5	380V- AC50Hz
N5	415V- AC50Hz
R5	440V- AC50Hz
B6	24V-AC60Hz
F6	110V-AC60Hz
M6	220V-AC60Hz
Q6	380V-AC60Hz
R6	440V-AC60Hz
B7	24V-AC50/60Hz
E7	48V- AC50/60Hz
F7	110V- AC50/60Hz
M7	220V- AC50/60Hz
P7	230V- AC50/60Hz
Q7	380V- AC50/60Hz

Additional information (if necessary)

Date: Sep.27,2022

Signature:



Xie ZhaoXu