

Socket Outlets – Classic C2000 Series

The first thing you'll notice about the C2000 Classic Series is the cover that comes in a choice of metal finishes and classic coloured plastic mouldings. This cover also hides all mounting holes, and is easily removed to enable painting right up to the edge of the gridplate without having to worry about marking the cover. When decorating is complete, the cover is simply replaced for a perfect finish.

As C2000 Classic Series covers and gridplates can be mixed and matched, they can produce many combinations to match various décor themes. The popular 'awesome foursome' quad socket outlet is also an ideal solution for power requirements behind televisions, beds, or in home offices

Single Phase Socket Outlets shall:

- Comprise a 10A rocker operated switch and three-pin plug base with flat arth pin, mounted in a two-piece, moulded impact-resistant polycarbonate gloss finish flush plate with a full clip-on cover similar to Clipsal C2000 Range.
- Be manufactured in accordance with AS/NZS3100, AS/NZS3112 and AS/NZS3133.
- For special purpose socket outlets, be provided with 15A and 20A mechanisms and appropriate sockets
- Comprise two switches and plug bases within a common standard size flush plate similar to Clipsal C2025 Series, for double socket outlets
- Be selected as per the schedule of accessories
- Comply with IP recommendations of AS 60529, where located external to the building or in damp situations. For compliance, assistance may be provided via Clipsal 255 or 223H enclosures
- Be flush mounted within a Clipsal 157 Series wall box, having adjustable metal fixing lugs where located in masonry walls
- Be flush mounted within a 155 Series metal bracket when fixed to a stud or noggin or where located in stud partitions
- If unable to be fixed to stud, noggin or masonry, be flush mounted within a 154 Series metal wall clip
- Ensure plates are engraved with circuit identification labelling or a clip-in two-piece tamperproof circuit ID module, similar to Clipsal 30PID, where required
- Ensure plates are engraved with circuit identification labelling or a clip-in two-piece circuit identification module, similar to Clipsal C2000I, where required
- Be of same type and manufacture as switches
- Be installed at a mounting height as shown on the drawings or directed on site
- Be fitted with a Clipsal 90B insulating shroud where located within close proximity to metal framework
- Where fire ratings of walls are required, Clipsal 157/1F (for cavity walls) and F157/1 (for masonry walls) fire rated wall boxes are to be used and installed as per manufacturer's instructions. Wall boxes are to be tested to AS1530.4 and AS 4072.1
- Where acoustic ratings are required for sound transmission, Clipsal 157/1F (for cavity walls) and F157/1 (for masonry walls) are to be used and installed as per manufacturer's instructions. Wall boxes are to be tested in accordance with AS1191, AS1276, AS1045, for sound transmission and achieve a rating of up to Rw50 or STC50 using various Clipsal accessories and wall materials
- Be labelled NO RCD PROTECTION on outlets connected to circuits, which are not protected by a residual current device.