


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Circuit-breakers for overcurrent protection for household and similar installations
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC HUNGÁRIA VILLAMOSSÁGI ZRT. Hock János utca 55 8900 Zalaegerszeg Hungary
Ratings and principal characteristics	3P+N – Ue = 400 V – 50-60 Hz – Icn = 4500 A Curve B, C or D – In = 6, 10, 16, 20, 25, 32 or 40 A (see Additional Sheet and page 6 of Test Report No. PB16-0009380-14-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series iQPN40 (see Additional Sheet and page 8 of Test Report No. PB16-0009380-14-00)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60898-1:2015
As shown in the Test Report Ref. No. which forms part of this Certificate	PB16-0009380-14-00 and from PB16-0009380-14-01 to PB16-0009380-14-21

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-I-20138 Milano, Italy

Description of the circuit-breakers for overcurrent protection series iQPN40 ($I_{cn} = 4500 \text{ A}$)

Curve	Rated current	Generic reference
B	6 A	MCB3PNSC456B6
	10 A	MCB3PNSC456B10
	16 A	MCB3PNSC456B16
	20 A	MCB3PNSC456B20
	25 A	MCB3PNSC456B25
	32 A	MCB3PNSC456B32
	40 A	MCB3PNSC456B40
C	6 A	MCB3PNSC456C6 or MCB3PNSC4545C10
	10 A	MCB3PNSC456C10 or MCB3PNSC4545C16
	16 A	MCB3PNSC456C16 or MCB3PNSC4545C20
	20 A	MCB3PNSC456C20 or MCB3PNSC4545C25
	25 A	MCB3PNSC456C25 or MCB3PNSC4545C32
	32 A	MCB3PNSC456C32 or MCB3PNSC4545C40
	40 A	MCB3PNSC456C40
D	6 A	MCB3PNSC456D6
	10 A	MCB3PNSC456D10
	16 A	MCB3PNSC456D16
	20 A	MCB3PNSC456D20
	25 A	MCB3PNSC456D25
	32 A	MCB3PNSC456D32
	40 A	MCB3PNSC456D40