




Ref. Certif. No.

DK-176369-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Buzzer illuminated and non-illuminated (Control circuit devices and switching elements)
Name and address of the applicant	Schneider Electric Industries SAS 35 rue Joseph Monier Rueil Malmaison 92500 France
Name and address of the manufacturer	Schneider Electric Industries SAS Boulevard Salvador Allende, ZI N°3 – BP 660 L'isle D'espagnac 16 340 France
Name and address of the factory	PT. SCHNEIDER ELECTRIC MANUFACTURING BATAM Batamindo Industrial Park , Jl. Beringin Lot 4, Lot 208, Lot 15, Lot 16, And Lot 16a Muka Kuning Sei Beduk Batam, KEPULAUAN RIAU, 29433 Indonesia <input type="checkbox"/> Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	PD3 OVC III AC/DC 50/60Hz <input checked="" type="checkbox"/> Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	XB5KS may be followed by 2, followed by B, G or M, may be followed by 4 or 8.
Additional information (if necessary may also be reported on page 2)	National Differences: EU Group Differences <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-5-1:2024, IEC 60947-1:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	4791611892.1 issued on 2026-01-26

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-03-23

Signature:
Thomas Wilson



Ref. Certif. No.

DK-176369-UL

Additional Ratings:

Non illuminated - Ue/Ui - Ie / Ith :

- 24 V ac/dc Max 28mA
- 110-120 V ac/dc Max 20mA
- 230-240 V ac Max 18Ma

Illuminated - Ue/Ui - Ie / Ith :

- 24 V ac/dc Max 58mA
- 110-120 V ac/dc Max 20mA
- 230-240 V ac Max 35mA
- suitability for isolation : N/A
- degree of protection : IP20 (rear), IP66, 67 (front)
- number of poles : 1P
- kind of current : AC/DC
- in the case of a.c., number of phases and rated frequency : 1-phase 50/60Hz

Rated and limiting values, main circuit..... :

- rated operational voltage Ue (V)..... : 24...240V
- rated insulation voltage Ui (V) : 250V
- rated impulse withstand voltage Uimp (kV) : 0.8kV (24V products) 2,5kV (120V products) / 4kV (240V products)
- conventional free air thermal current Ith (A) : see table
- rated operational current Ie (A) : see table
- Short-circuit characteristic : N/A

- Wiring:

- Stranded or rigid, 1x or 2x wires
- Minimum cross section / number of conductors: 0.5 mm²
- Maximum cross section / number of conductors: 1.5 mm²
- Torque: 0.8 Nm
- Strip length: 8 mm
- Mounting nut, torque: 2.2Nm +/-0,2 Nm
- Ambient Air Temperature for Operation / Storage -40...70 °C

Additionally evaluated to:

EN 60947-1:2007, EN 60947-1:2007/A1:2011, EN 60947-1:2007/A2:2014, EN 60947-5-1:2017

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-03-23

Signature:

Thomas Wilson