




Ref. Certif. No.

DK-181359-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	SWITCHING ELEMENT: Pushbuttons, Selectors, Mushroom buttons, Pilot lights and illuminated buttons, joystick controllers.
Name and address of the applicant	Schneider Electric Industries SAS Boulevard Salvador Allende, ZI N°3 – BP 660 L'isle D'espagnac 16 340 France
Name and address of the manufacturer	Schneider Electric Industries SAS Boulevard Salvador Allende, ZI N°3 – BP 660 L'isle D'espagnac 16 340 France
Name and address of the factory	Schneider Electric France Zone industrielle, BP 660 F16340 L'Isle d'Espagnac, France
<i>Note: When more than one factory, please report on page 2</i>	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Utilization Category: AC15 – DC-13 A600 – Q600 - A300 – Q300 – P300 - B300 – R300 Resistive <input checked="" type="checkbox"/> Additional Information on page 2-3
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Series XD5P, Series ZB4B, Series XB5EV, Series XB4B, Series XB5F, Series ZBW, Series ZENL, Series ZD5P, Series ZD4P, Series ZB5C, Series XB4F, Series ZBP, Series ZB4S, Series ZALV, Series XB5A, Series ZBV, Series ZBZ, Series ZB4F, Series ZB2BE, Series XD4P, Series ZB5F, Series ZBY, Series ZB5S, Series ZB5A, Series ZBE, Series XAL-D, Series XAL-K, Series XAL-B, Series XAL-J <input checked="" type="checkbox"/> Additional Information on page 3
Additional information (if necessary may also be reported on page 2)	
A sample of the product was tested and found to be in conformity with	IEC 60947-5-1:2024, IEC 60947-1:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	4791611927A issued on 2026-06-01

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/hcbnames

Date: 2026-06-09

Signature: Thomas Wilson



Ref. Certif. No.

DK-181359-UL

Factory(ies):

Schneider Electric a. s.
Cizovska 447
397 01 Pisek,
Czech Republic

PT. Schneider Electric Manufacturing Batam
Batamindo Industrial Park JL Beringin Lot 1, 4 & 208,
Muka Kuning Batam
29433ID
Indonesia

See test report for details

Additional Ratings:

Supply Rating:
24 V – 0.1 A

Rated Operational Voltage Ue:

3.3 Vdc, 5 Vdc, 16 Vdc
12 Vac/dc
12, 24...120 Vac/dc
48...230 Vac
110...120 Vac
110...240 Vac
125 Vdc, 250 Vdc
230...240 Vac
400 Vac, 440...480 Vac
600 Vac/dc
550...600 Vac

Uc / Us: same as Ue

Rated Insulation Voltage Ui:

250 V
500 V
600 V

Rated Impulse Withstand Voltage: Uimp:

4 kV
6 kV

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-09

Signature:

Thomas Wilson



Ref. Certif. No.

DK-181359-UL

Additional Ratings:

Conventional free air thermal current Ith:

6 A
10 A

Conventional enclosed thermal current Ithe:

6 A
10 A

Rated Operational Current:

6 Aac, 3 Aac,
0,1 Adc, 0,27 Adc, 0,22 Adc, 0,55 Adc,
1,1 Adc, 1,2 Aac, 1,5 Aac

Rated frequency: 50 – 60 Hz

Rated conditional short circuit current: 1000 A

Class of insulation:

Class of insulation:

I (for XB4 series)
II (for XB5 series)

Protection degree:

Back: IP 20 (all, Including ZB4BZ014)

Models with faston tab and pin type connection: IP 00

Front:

IP 66
IP 67 only XB4F, XB5F, ZB4F, ZB5F, ZBY9W series

XAL-D, XAL-K, XAL-B, XAL-J: IP66,67

Pollution Degree: 3

Ambient Air Temperature for Operation / Storage -40...70 °C

See CB test report for complete detailed ratings

Additional model details:

See test report for nomenclature

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-09

Signature:

Thomas Wilson