

# C-Bus 4-Channel Dimmer, DIN Rail Series

C-Bus<sup>2</sup>

**CLIPSAL**<sup>®</sup>  
INTEGRATED SYSTEMS



## L5504D2A Series

The L5504D2A DIN Rail Series Dimmers are C-Bus output units suitable for dimming incandescent & low voltage lighting. For ease of installation the units are DIN rail mounted measuring 12M wide.

All units in the series incorporate the C-Bus 'Learn Mode' feature. Learn mode allows the units to be programmed without the need for a PC connected to the system. Alternatively, the units can be programmed via a PC using the installation software.

The dimmers feature four leading edge phase controlled dimming channels. Each channel has a load rating of 2 Amps, capable of controlling incandescent lighting and low voltage lighting (utilizing iron-core transformers and electronic transformers compatible with leading edge dimmers).

C-Bus connections are conveniently achieved at the unit through the use of RJ45 connectors, allowing similar units to be quickly looped together.

During normal operation the units consume no current from the C-Bus network.

Two variants of the product are available. One incorporates a 200mA C-Bus power supply used to source current to the C-Bus network. The other is an economical model with the same features and performance, but does not include the 200mA power supply.

This series of units are capable of generating a C-Bus clock signal and providing a C-Bus network burden. Both the clock signal and the burden are selectable through the C-Bus Installation software.

Local toggle buttons have been included to allow individual channels to be toggled at each unit as well as via C-Bus commands. Remote ON and OFF facilities are available, permitting all channels to be turned ON and OFF without C-Bus Network communication.

Like all other units that make up a C-Bus system, the C-Bus L5504D2A Din Rail Series Dimmers are Australian designed, developed and manufactured by Clipsal Integrated Systems Pty Ltd.

[clipsal.com/cis](http://clipsal.com/cis)

**CLIPSAL**  
IBS Intelligent Building Series™

## L5504D2A Series C-Bus Dimmer Modules

- Provides four leading edge phase controlled dimming channels in a 12M wide DIN rail enclosure.
- Load rating of 4 channels x 2 Amp.
- Capable of controlling incandescent lighting and low voltage lighting utilizing iron-core transformers and electronic transformers compatible with leading edge dimmers.
- A special algorithm ensures that lights do not flicker due to signal injections on the mains.
- Each channel incorporates thermal overload and over current protection.
- Incorporates a linear brightness control, which ensures the change in brightness is uniform throughout the control range.
- Incorporates a Soft Turn ON and Soft Turn OFF feature, providing a soft change in brightness.
- Units available both with and without an inbuilt 200mA C-Bus power supply.
- Up to 100 units without power supply or 10 units with power supply are permitted on any one single C-Bus network (255 networks available in a C-Bus installation).
- Configured via either the C-Bus Installation Software or via the Learn Enabled Features.
- Local ON/OFF toggle buttons allow individual channels to be manually overridden at each unit.
- Remote ON and OFF facility permits all channels to be turned ON or OFF without C-Bus network communication.
- Incorporates C-Bus Network Status, Mains Power Status and Load Status indicators.
- Capable of generating a C-Bus clock signal if enabled.
- A network burden is incorporated and is software selectable.
- Designed to meet Australian and European standards for EMC Compliance and Safety.
- Capable of being programmed via the installation software without the need for a mains connection.
- Draws 18mA when being programmed and no mains connection is made.
- An inbuilt non-volatile memory retains programmed information relating to the current operating status of the unit in the event of a power failure.
- Communication with other C-Bus devices and the supply voltage is obtained via a single C-Bus twisted pair cable.
- Electrical isolation between the safe extra low voltage C-Bus side and the mains voltage output side is provided to maintain safety requirements.
- Dimensions: H = 85mm, W = 215mm, D = 65mm.



### Head Office

12 Park Terrace, Bowden, South Australia 5007  
Telephone (08) 8269 0560  
International +61 8 8269 0560  
Facsimile (08) 8346 0845  
International +61 8 8346 0845  
E-Mail [cis@clipsal.com.au](mailto:cis@clipsal.com.au)  
Internet [clipsal.com/cis](http://clipsal.com/cis)

### International Enquiries

#### Head Office Export Department

Telephone +61 8 8269 0587  
Facsimile +61 8 8340 7350  
E-Mail [export@clipsal.com.au](mailto:export@clipsal.com.au)  
Internet [clipsal.com](http://clipsal.com)

### New Zealand

Clipsal Industries (NZ) Ltd  
Telephone +64 9 576 303

### Malaysia

Clipsal Integrated Systems (M) Sbn Bhd  
Telephone +60 3 7665 3555

### Singapore

CIS Pte Ltd (Singapore)  
Telephone +65 266 1998

### Hong Kong

Clipsal Integrated Systems (HK) Limited  
Telephone +852 2 487 0261

### China

Clipsal China Limited  
Telephone +86 755 246 1122

### Taiwan

Clipsal (Taiwan) Co Ltd  
Telephone +886 2 25583456

### Thailand

Clipsal Thailand Ltd  
Telephone +66 2 952 5338

### South Africa

Clipsal South Africa (Pty) Ltd  
Telephone +27 11 314 5200

### United Kingdom

Clipsal Ltd (UK)  
Telephone +44 1494 521 111

### Greece

Clipsal Hellas S.A.  
Telephone +30 1 993 9165



Patented

© Copyright Clipsal Integrated Systems Pty Ltd 2001