

## Socket Outlets – Slimline SC2000 Series

The Slimline SC2000 Series range of switches and sockets are the thinnest single fix accessories in the world. From the front they look like the Classic C2000 range, however from a side view it can be seen that they have a remarkably thin 4mm profile, making them up to 60% thinner than other products. And because the switch cover simply clicks onto the grid assembly, the Slimline SC2000 range can be mixed and matched as often as you like with either moulded or metal covers.

### Single Phase Socket Outlets shall:

- Comprise a 10A rocker operated switch and three-pin plug base with flat Earth pin, mounted in a two-piece, moulded, one piece impact-resistant polycarbonate/ABS gloss finish grid plate with a full clip-on ABS cover similar to Clipsal Slimline Series.
- Be manufactured in accordance with AS/NZS3100, AS/NZS3112 and AS/NZS3133
- For special purpose socket outlets, be provided with 15A mechanisms and appropriate sockets
- Comprise two switches and plug bases within a common standard size flush plate, similar to Clipsal SL2025 Series, for double socket outlets
- Comply with IP ratings of AS 60529, where located external to the building or in damp or dusty situations
- Be flush mounted within a Clipsal 157 Series wall box (or 157/1PRM wall box for walls thinner than 6mm), having adjustable metal fixing lugs where located in masonry walls
- Be flush mounted within a Clipsal 155 Series metal bracket (or 155PRM or 155NAR bracket for walls thinner than 6mm) fixed to a stud or noggin, where located in stud partitions
- Be flush mounted within a 154 Series metal wall clip (or 154RM wall clip for walls thinner than 6mm) if unable to be fixed to a stud, noggin or masonry
- Ensure plates are engraved with circuit identification labelling or a clip-in, two-piece, tamperproof circuit ID module, similar to Clipsal 30PID, where required Alternatively plates to be identified with clip-in, two-piece, circuit ID module, similar to Clipsal SC2000I
- Be of same type and manufacture as switches
- Be fitted with a Clipsal 90BI insulating shroud where located within close proximity to metal framework
- Where fire ratings of walls are required, Clipsal 157/1F (for cavity walls) or F157/1 (for masonry walls) fire rated wall boxes are to be used and installed as per manufacturer's instructions. Wall boxes are to be tested to AS1530.4 and AS 4072.1
- Where acoustic ratings are required for sound transmission Clipsal 157/1F (for cavity walls) and F157/1 (for masonry walls) wall boxes are to be used and installed as per manufacturer's instructions. Wall boxes to be tested in accordance with AS1191, AS1276, AS1045, for sound transmission and achieve a rating of up to Rw50 or STC50 using various Clipsal accessories and suitable wall materials
- Be labelled NO RCD PROTECTION on outlets connected to circuits which are not protected by a residual current device.
- Be fitted with SL2000PP,TR snap-on paint shield to provide protection during painting.