

IEC**IECEE**

®

™

Ref. Certif. No.

CN71656

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

AC Contactor

Name and address of the applicant

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, Hubei Province, P.R.China

Name and address of the manufacturer

Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, Hubei Province, P.R.China

Name and address of the factory

*Note: When more than one factory, please report on page 2*Schneider Electric Manufacturing (Wuhan) Co., Ltd.
No.1 3rd Fozuling Road, Donghu New&High Tech
Development Zone, Wuhan, Hubei Province, P.R.China

Ratings and principal characteristics

See the appendix

Trademark (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

LC1N06, LC1N09, LC1N09...NS201, LC1N12,
LC1N12...NS201, LC1N18, LC1E06..., LC1E09...,
LC1E12..., LC1E18...;

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-1:2020;IEC 60947-4-1:2023

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-CB2025CQC-121214

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: <http://www.cqc.com.cn>

Date: Apr.22,2025

Signature:

谢肇煦

Xie ZhaoXu



LC1N06, LC1N09, LC1N09...NS201, LC1N12, LC1N12...NS201, LC1N18, LC1E06..., LC1E09...,
LC1E12..., LC1E18...;

Ui: 690V;

Uimp: 6kV;

LC1N06:

Ith: 20A;

AC-1: Ue/Ie: 220/230V/20A, 380V/20A, 400/415V/20A, 440V/20A, 660V/20A;

AC-3: Ue/Ie: 220/230V/6A, 380V/6A, 400/415V/6A, 440V/6A, 660V/4.8A;

AC-3e: Ue/Ie: 220/230V/6A, 380V/6A, 400/415V/6A, 440V/6A, 660V/4.8A;

AC-4: Ue/Ie: 220/230V/5A, 380V/5A, 400/415V/5A, 440V/5A, 660V/4A;

LC1E06...:

Ith: 20A;

AC-1: Ue/Ie: 220/230V/20A, 380V/20A, 400/415V/20A, 440V/20A;

AC-3: Ue/Ie: 220/230V/6A, 380V/6A, 400/415V/6A, 440V/6A;

AC-3e: Ue/Ie: 220/230V/6A, 380V/6A, 400/415V/6A, 440V/6A;

AC-4: Ue/Ie: 220/230V/5A, 380V/5A, 400/415V/5A, 440V/5A;

LC1N09:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A, 660V/25A;

AC-3: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A, 660V/6.6A;

AC-3e: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A, 660V/6.6A;

AC-4: Ue/Ie: 220/230V/7.5A, 380V/7.5A, 400/415V/7.5A, 440V/7.5A, 660V/5.5A;

LC1E09...:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A;

AC-3: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A;

AC-3e: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A;

AC-4: Ue/Ie: 220/230V/7.5A, 380V/7.5A, 400/415V/7.5A, 440V/7.5A;

LC1N12:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A, 660V/25A;

Page 1 of 3

Additional information (if necessary)

Date:

Apr.22,2025

Signature:

谢肇煦

Xie ZhaoXu

AC-3: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A, 660V/6.9A;
 AC-3e: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A, 660V/6.9A;
 AC-4: Ue/Ie: 220/230V/10A, 380V/10A, 400/415V/10A, 440V/10A, 660V/5.8A;
 LC1E12...:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A;
 AC-3: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A;
 AC-3e: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A;
 AC-4: Ue/Ie: 220/230V/10A, 380V/10A, 400/415V/10A, 440V/10A;

LC1N18:

Ith: 32A;

AC-1: Ue/Ie: 220/230V/32A, 380V/32A, 400/415V/32A, 440V/32A, 660V/32A;
 AC-3: Ue/Ie: 220/230V/18A, 380V/18A, 400/415V/18A, 440V/18A, 660V/11.5A;
 AC-3e: Ue/Ie: 220/230V/18A, 380V/18A, 400/415V/18A, 440V/18A, 660V/11.5A;
 AC-4: Ue/Ie: 220/230V/15A, 380V/15A, 400/415V/15A, 440V/15A, 660V/9.6A;

LC1E18...:

Ith: 32A;

AC-1: Ue/Ie: 220/230V/32A, 380V/32A, 400/415V/32A, 440V/32A;
 AC-3: Ue/Ie: 220/230V/18A, 380V/18A, 400/415V/18A, 440V/18A;
 AC-3e: Ue/Ie: 220/230V/18A, 380V/18A, 400/415V/18A, 440V/18A;
 AC-4: Ue/Ie: 220/230V/15A, 380V/15A, 400/415V/15A, 440V/15A;

LC1N09...S201:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A;
 AC-3: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A;
 AC-3e: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A;
 AC-4: Ue/Ie: 220/230V/9A, 380V/9A, 400/415V/9A, 440V/9A;

LC1N12...S201:

Ith: 25A;

AC-1: Ue/Ie: 220/230V/25A, 380V/25A, 400/415V/25A, 440V/25A;
 AC-3: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A;

Additional information (if necessary)

Date:

Apr.22,2025

Signature:

谢肇煦

Xie ZhaoXu

IEC**TECEE**

®

™

Ref. Certif. No.

CN71656

AC-3e: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A;

AC-4: Ue/Ie: 220/230V/12A, 380V/12A, 400/415V/12A, 440V/12A;

Us: AC24V/36V/48V/110V/220V/240V/380V/415V/440V 50Hz;

AC24V/110V/220V/380V/440V 60Hz;

AC24V/48V/110V/220V/230V/380V 50/60Hz;

Pole: 3P;

Frequency: 50/60Hz;

IP20(from front face only)

Auxiliary contacts: (body)

Ith:10A;

AC-15: Ue/Ie:380V/1.3A, 660V/0.75A;

DC-13: Ue/Ie: 220V/0.3A;

1NO or 1NC;


Page 3 of 3

Additional information (if necessary)

Date:

Apr.22,2025

Signature:



Xie ZhaoXu