



Ref. Certif. No.

ES2791-M2-AENORIEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKERS
WITH INTEGRAL OVERCURRENT PROTECTION FOR
HOUSEHOLD AND SIMILAR USES (RCBO'S)

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, RUE JOSEPH MONIER
RUEIL MALMAISON CEDEX (Francia)

Name and address of the manufacturer

SCHNEIDER ELECTRIC ESPAÑA, S.A.U
Camino BARRANQUET, 57
46133 MELIANA (Valencia - España)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be
reported on page 2) Additional Information on page 2A sample of the product was tested and found
to be in conformity withIEC 61009-1:2010
IEC 61009-1:2010/A1:2012
IEC 61009-1:2010/A2:2013
IEC 61009-2-1:1991As shown in the Test Report Ref. No. which forms part
of this CertificateGS06/26 EMC, GS06/26, GS07/25-M1, GS07/26, GS08/26,
GS11/25-M1, GS16/25-M1 to GS26/25-M1, GS385/26-M1
Head Report, GS535/25-M1 EMC, GS535/25-M1,
305068-TL3-0, 305068-TL3-1, 305068-TL7-2,
SPEC25AA5848_v4, SPEC25AA5849_v2, SPEC25AA5850_v2,
SPEC25AA5851_v3, SPEC25AA5852_v2 to
SPEC25AA5859_v2, SPEC25AA5862_v3, SPEC25AA5864_v2,
SPEC25AA5865_v3, SPEC26AA0653_v1 EMC

This CB Test Certificate is issued by the National Certification Body

AENOR CONFÍA S.A.U.
Cl Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2026-04-22

Signature: Rafael GARCÍA MEIRO
CEO

ANNEX TO CB CERTIFICATE N° ES2791-M2-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKERS WITH INTEGRAL OVERCURRENT PROTECTION FOR HOUSEHOLD AND SIMILAR USES (RCBO'S)

Trade mark: SCHNEIDER ELECTRIC

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual operating current	Rated short-circuit capacity	Rated residual making and breaking capacity	Tripping current	Type	Energy limiting class	Additional information
45A9DX1PN96B10A30mAA	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B13A30mAA	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B16A30mAA	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B20A30mAA	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B25A30mAA	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96B32A30mAA	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	B	A	3	Acti9 96mm
45A9DX1PN96C10A30mAA	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C10A30mAAC	1P+N	10 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C10A300mAA	1P+N	10 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C10A300mAAC	1P+N	10 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C13A30mAA	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C13A30mAAC	1P+N	13 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C13A300mAAC	1P+N	13 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C16A30mAA	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C16A30mAAC	1P+N	16 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C16A300mAA	1P+N	16 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C16A300mAAC	1P+N	16 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C20A30mAA	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C20A30mAAC	1P+N	20 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C20A300mAA	1P+N	20 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C20A300mAAC	1P+N	20 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C25A30mAA	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C25A30mAAC	1P+N	25 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C25A300mAA	1P+N	25 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C25A300mAAC	1P+N	25 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C32A30mAA	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C32A30mAAC	1P+N	32 A	230/240 V~	30 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
45A9DX1PN96C32A300mAA	1P+N	32 A	230/240 V~	300 mA	4500 A	4500 A	C	A	3	Acti9 96mm
45A9DX1PN96C32A300mAAC	1P+N	32 A	230/240 V~	300 mA	4500 A	4500 A	C	AC	3	Acti9 96mm
6A9DS1PN91B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91B13A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91B16A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 91mm
6A9DS1PN91C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6A9DS1PN91C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6A9DX1PN96B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B20A30mAA	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B25A30mAA	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96B32A30mAA	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Acti9 96mm
6A9DX1PN96C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C10A30mAAC	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C10A300mAA	1P+N	10 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C10A300mAAC	1P+N	10 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C13A30mAAC	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C13A300mAAC	1P+N	13 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C16A30mAAC	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C16A300mAA	1P+N	16 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C16A300mAAC	1P+N	16 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C20A30mAA	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C20A30mAAC	1P+N	20 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C20A300mAA	1P+N	20 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm

ANNEX TO CB CERTIFICATE N° ES2791-M2-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual operating current	Rated short-circuit capacity	Rated residual making and breaking capacity	Tripping current	Type	Energy limiting class	Additional information
6A9DX1PN96C20A300mAAC	1P+N	20 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C25A30mAA	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C25A30mAAC	1P+N	25 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C25A300mAA	1P+N	25 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C25A300mAAC	1P+N	25 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C32A30mAA	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C32A30mAAC	1P+N	32 A	230/240 V~	30 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6A9DX1PN96C32A300mAA	1P+N	32 A	230/240 V~	300 mA	6000 A	6000 A	C	A	3	Acti9 96mm
6A9DX1PN96C32A300mAAC	1P+N	32 A	230/240 V~	300 mA	6000 A	6000 A	C	AC	3	Acti9 96mm
6R9DS1PN91C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Acti9 91mm
6R9DX1PN91B10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91B13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91B16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	B	A	3	Resi9 91mm
6R9DX1PN91C10A30mAA	1P+N	10 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm
6R9DX1PN91C13A30mAA	1P+N	13 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm
6R9DX1PN91C16A30mAA	1P+N	16 A	230/240 V~	30 mA	6000 A	6000 A	C	A	3	Resi9 91mm

Temperature of use:

- -5°C to 40°C for Type AC
- -25°C to 40°C for Type A