


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 SCHNEIDER ELECTRIC ESPAÑA, S.A. Camino Barranquet, 57 46133 Meliana (Valencia) Spain
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	1P+N – Un = 230 V – Curve B – In = 4, 6, 10, 13, 16, 20 or 25 A type A – IΔn = 30 mA – Icn = 10000 A – IΔm = 4500 A (see also Additional Sheet and pages 4 and 6 of Test Report PB18-0026801-02-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	Series DPN Vigi (see also Additional Sheet and page 6 of Test Report PB18-0026801-02-00)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61009-1:2010, IEC 61009-1:2010/AMD1:2012, IEC 61009-1:2010/AMD2:2013, IEC 61009-2-1:1991 National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	PB18-0026801-02-00 and from PB18-0026801-02-01 to PB18-0026801-02-07

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-I-20138 Milano, Italy



Description of the RCBOs series DPN Vigi (type A, I_{cn} 10000 A)

Rated current	Generic reference
4 A	P1B10000B4A30
6 A	P1B10000B6A30
10 A	P1B10000B10A30
13 A	P1B10000B13A30
16 A	P1B10000B16A30
20 A	P1B10000B20A30
25 A	P1B10000B25A30