

IEC**IECEE**

®

™

Ref. Certif. No.

CN52132-A1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME**CB TEST CERTIFICATE**

Product

Circuit-breakers Incorporating Residual Current Protection

Name and address of the applicant

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the manufacturer

Schneider Electric Industries SAS
35 Rue Joseph Monier 92500 Rueil-Malmaison, France

Name and address of the factory

Schneider(Beijing)Medium & Low Voltage Co.,Ltd.
No.2 Liangshuihe 2nd Street, BJ Economic Technological
Development Area, Beijing 100176, P.R.China*Note: When more than one factory, please report on page 2* Additional information on page 2

Ratings and principal characteristics

See the Appendix

Trademark / Brand (if any)

Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

VigiComPacT NSX400F, VigiComPacT NSX400N, VigiComPacT NSX400H,
VigiComPacT NSX400S, VigiComPacT NSX400L, VigiComPacT NSX630F,
VigiComPacT NSX630N, VigiComPacT NSX630H, VigiComPacT NSX630S,
VigiComPacT NSX630L

Additional information (if necessary may also be reported on page 2)

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016(5th Edition); IEC
60947-2:2016/AMD1:2019

As shown in the Test Report Ref. No. which forms part of this Certificate

00901-V2021CQC-096662

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: <http://www.cqc.com.cn>

Date: May.21,2021

Signature:

Lu Mei

CB 0062593

VigiComPacT NSX400F, VigiComPacT NSX400N, VigiComPacT NSX400H,
 VigiComPacT NSX400S, VigiComPacT NSX400L, VigiComPacT NSX630F,
 VigiComPacT NSX630N, VigiComPacT NSX630H, VigiComPacT NSX630S,
 VigiComPacT NSX630L;

Ui: 800V;

Uimp:8kV

Ue: AC220/240V, AC380/415V, AC440V

In: 400A, 600A

Over-current release: Electronic

Ics: 100%Icu(F/N/S/L); 50%Icu(H)

Icu:

VigiComPacT NSX400/630F: 40kA (AC 220/240V), 36 kA (AC 380/415V), 30 kA (AC 440V).

VigiComPacT NSX400/630N: 85 kA (AC 220/240V), 50 kA (AC 380/415V), 42 kA (AC 440V).

VigiComPacT NSX400/630H: 100 kA (AC 220/240V), 70 kA (AC 380/415V), 65
 kA(AC440V).

VigiComPacT NSX400/630S: 120 kA (AC 220/240V), 100 kA (AC 380/415V), 90 kA (AC
 440V).

VigiComPacT NSX400/630L: 150 kA (AC 220/240V), 150 kA (AC 380/415V), 130 kA (AC
 440V).

VIGI 8.8 module:

non-time delay type(Type A): IΔn: 0.03A

time delay(Type A): IΔn: 0.1/0.3/0.5/1/3A adjustable

time delay(Type AC): IΔn: 10/30A adjustable

CVS 5.4 module:

time delay(Type AC): IΔn:0.3/1/3/10/30 adjustable

Residual current Release Type: Electronic

IΔm: 10kA (F), 21.25KA (N), 25KA (H); 37.5KA (S,L)

Selectivity category: A

Suitability for Isolation

Poles : 3P, 4P

Auxiliary circuits: 1NO1NC

Page 1 of 2

Additional information (if necessary)

Date:

May,21,2021

Signature:



Lu Mei

Standard type:

Ith: 6A;

AC-12: Ue/Ie: 24V/6A, 48V/6A, 110V/6A, 220/240V/6A,
380/440V/6A, 480V/6A, 660/690V/6A;AC-15: Ue/Ie: 24V/6A, 48V/6A, 110V/5A,
220/240V/4A, 380/440V/2A, 480V/1.5A, 660/690V/0.1A;

DC-12: Ue/Ie: 24V/6A, 48V/2.5A, 110V/0.6A, 250V/0.3A;

DC-14: Ue/Ie: 24V/1A, 48V/0.2A, 110V/0.05A, 250V/0.03A.

Low level type:

Ith: 5A;

AC-12: Ue/Ie: 24V/5A, 48V/5A, 110V/5A, 220/240V/5A, 380/440V/5A, 480V/4A;

AC-15: Ue/Ie: 24V/3A, 48V/3A, 110V/2.5A, 220/240V/2A, 380V/440V/1.5A, 480V/1A;

DC-12: Ue/Ie: 24V/5A, 48V/2.5A, 110V/0.6A, 250V/0.3A;

DC-14: Ue/Ie: 24V/1A, 48V/0.2A, 110V/0.05A, 250V/0.03A.

Electronic Accessories complied with Annex N:

Motor operating (MCH): Us: AC48V 50Hz; AC110/130-200/240V, 380/440V 50/60Hz;
DC24/30-48/60-110/130-250VShunt release(MN): Us: AC24-48-100/130-200/240 V 50/60Hz; AC380/415V 50Hz;
AC208/277V 60Hz; DC12-24-30-48-60-125-250VUndervoltage release(MX): Us: AC24-48-100/130-200/240V 50/60Hz; AC380/415V 50Hz;
AC208/277V 60Hz; DC:12-24-30-48-60-125-250V

Additional information (if necessary)

Date:

May.21,2021

Signature:



Lu Mei

IEC**IECEE**

®

™

Ref. Certif. No.

CN52132-A1

Name of the factory	Address of the factory
1.Schneider Electric Alpes	Voie Isaac Newton ZI Alpespace 73800 FRANCIN FRANCE

Additional information (if necessary)

Date: May.21,2021

Signature:



Lu Mei