

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens, F-38050 Grenoble Cedex 9
France

Name and address of the manufacturer

GEWISS S.p.A.
Via Domenico Bosatelli, 1, 24069 Cenate Sotto (BG)
Italy

Name and address of the factory

GEWISS PORTUGAL Indústria del Material Eléctrico, Unipessoal, Lda
Zona Industrial 2a fase - Bustelo, 4560-043 Penafiel
Portugal

Note: When more than one factory, please report on page 2

[Additional information on page 2](#)

Ratings and principal characteristics

3P or 4P; Un = 400 V; Curve B or C; In = 6, 10, 13, 16, 20, 25, or 32 A; type A, ASI, AC; I Δ n = 30 or 300 mA; Icn = 6000 A; I Δ m = 4500 A; (see also pages 7 and 9 of Test Report PB24-0104095-02-00)

Trademark / Brand (if any)



Schneider Electric

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Acti9 iC60 series
(see also Additional Sheet)

Additional information (if necessary may also be reported on page 2)

[Additional information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 61009-1:2010, IEC 61009-1:2010/AMD1:2012, IEC 61009-1:2010/AMD2:2013, IEC 61009-2-1:1991

National differences:

AU, EU Group Differences, NZ

As shown in the Test Report Ref. No. which forms part of this Certificate

PB24-0104095-02-00 and from PB24-0104095-02-01 to PB24-0104095-02-21

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43
Milano, 20138
Italy



Date: 2025-02-20

Signature: Fabio Taormina

Type reference of RCBOs Acti9 iC60 series ($I_{cn} = 6000 \text{ A}$) and related ratings (continues on page 2)

Number of poles	Curve	Rated current (I_n)	Type	Rated residual operating current ($I_{\Delta n}$)	Type reference
3P	C	6 A	A	30 mA	A9D67306
3P	C	10 A	A	30 mA	A9D67310
3P	C	16 A	A	30 mA	A9D67316
3P	C	25 A	A	30 mA	A9D67325
3P	C	32 A	A	30 mA	A9D67332
4P	C	6 A	A	30 mA	A9D67406
4P	C	6 A	A	300 mA	A9D52406
4P	C	6 A	AC	30 mA	A9D57406
4P	C	6 A	AC	300 mA	A9D55406
4P	C	6 A	ASI ⁽¹⁾	30 mA	A9D77406
4P	C	10 A	A	30 mA	A9D67410
4P	C	10 A	A	300 mA	A9D52410
4P	C	10 A	AC	30 mA	A9D57410
4P	C	10 A	AC	300 mA	A9D55410
4P	C	10 A	ASI ⁽¹⁾	30 mA	A9D77410
4P	C	13 A	A	30 mA	A9D67413
4P	C	13 A	ASI ⁽¹⁾	30 mA	A9D77413
4P	C	16 A	A	30 mA	A9D67416
4P	C	16 A	A	300 mA	A9D52416
4P	C	16 A	AC	30 mA	A9D57416
4P	C	16 A	AC	300 mA	A9D55416
4P	C	16 A	ASI ⁽¹⁾	30 mA	A9D77416
4P	C	20 A	A	30 mA	A9D67420
4P	C	20 A	A	300 mA	A9D52420
4P	C	20 A	AC	30 mA	A9D57420
4P	C	20 A	AC	300 mA	A9D55420
4P	C	20 A	ASI ⁽¹⁾	30 mA	A9D77420
4P	C	25 A	A	30 mA	A9D67425
4P	C	25 A	A	300 mA	A9D52425
4P	C	25 A	AC	30 mA	A9D57425
4P	C	25 A	AC	300 mA	A9D55425
4P	C	25 A	ASI ⁽¹⁾	30 mA	A9D77425
4P	C	32 A	A	30 mA	A9D67432
4P	C	32 A	A	300 mA	A9D52432
4P	C	32 A	AC	30 mA	A9D57432
4P	C	32 A	AC	300 mA	A9D55432
4P	C	32 A	ASI ⁽¹⁾	30 mA	A9D77432

(¹) – “ASI” type RCBOs are A-type RCBOs having an intentional short-time delay.

Type reference of RCBOs Acti9 iC60 series ($I_{cn} = 6000 \text{ A}$) and related ratings (continued from page 1)

Number of poles	Curve	Rated current (I_n)	Type	Rated residual operating current ($I_{\Delta n}$)	Type reference
4P	B	6 A	A	30 mA	A9D87406
4P	B	6 A	ASI ⁽¹⁾	30 mA	A9D97406
4P	B	10 A	A	30 mA	A9D87410
4P	B	10 A	ASI ⁽¹⁾	30 mA	A9D97410
4P	B	13 A	A	30 mA	A9D87413
4P	B	13 A	ASI ⁽¹⁾	30 mA	A9D97413
4P	B	16 A	A	30 mA	A9D87416
4P	B	16 A	ASI ⁽¹⁾	30 mA	A9D97416
4P	B	20 A	A	30 mA	A9D87420
4P	B	25 A	A	30 mA	A9D87425
4P	B	25 A	ASI ⁽¹⁾	30 mA	A9D97425
4P	B	32 A	A	30 mA	A9D87432
4P	B	32 A	ASI ⁽¹⁾	30 mA	A9D97432

⁽¹⁾ – “ASI” type RCBOs are A-type RCBOs having an intentional short-time delay.