

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Isolating switches

Name and address of the applicant

Schneider Electric Industries SAS
31 Rue Pierre Mendès France, Eybens, 38050 GRENOBLE CEDEX 9
France

Name and address of the manufacturer

Schneider Electric Industries SAS
31 Rue Pierre Mendès France, Eybens, 38050 GRENOBLE CEDEX 9
France

Name and address of the factory

ShangHai Schneider Electric Low Voltage Terminal Apparate Co., Ltd.
1319# PingAn Road
Shanghai, 201109
China*Note: When more than one factory, please report on page 2* [Additional information on page 2](#)

Ratings and principal characteristics

See Appendix 1

Trademark / Brand (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

Resi9

Additional information (if necessary may also be reported on page 2)

See the Appendix.

 [Additional information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60669-2-4:2004


Comments:

To be used in conjunction with IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

63334401/00 up to 63334401/06

This CB Test Certificate is issued by the National Certification Body

SGS Belgium N.V. – Division SGS-CEBEC
Riverside Business Park , Bld Internationaaleaan 55 , Build. A
BRUSSELS 1070
Belgium

Date: 2024-11-20

Signature: Calogero Lana

Ratings:

number of poles	:	1P, 2P, 3P & 4P
rated voltage (Un)	:	250 Vac & 415 Vac
rated current (In)	:	40 A & 63 A
utilization category	:	AC22A
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	6 kV under frame
rated conditional short-circuit current	:	6 kA
rated frequency	:	50 Hz / 60 Hz
SCPD	:	Silver Wire
degree of protection	:	IP 40 under frame / IP 20
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

Products References:

Modules de base			Circuit de puissance		
Ref com.	Pole	Pattern	In (A)	Un(V)	Inc(kA)
R9PS163	1	1	63	250	6
R9PS263	2	2	63	415	6
R9PS363	3	3	63	415	6
R9PS463	4	4	63	415	6
R9PS140	1	1	40	250	6
R9PS240	2	2	40	415	6
R9PS340	3	3	40	415	6
R9PS440	4	4	40	415	6

0 1 2 3 4 5

