

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER (WITH TYPE F AND B) WITHOUT INTEGRAL OVERCURRENT PROTECTION FOR HOUSEHOLD AND SIMILAR USES

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
35, RUE JOSEPH MONIER
RUEIL MALMAISON CEDEX (Francia)

Name and address of the manufacturer

SCHNEIDER ELECTRIC ESPAÑA, S.A.U
Camino BARRANQUET, 57
46133 MELIANA (Valencia - Spain)

Name and address of the factory

SAME AS ABOVE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark (if any)

SCHNEIDER ELECTRIC

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

See references on the Annex

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 61008-1:2010
IEC 61008-1:2010/A1:2012
IEC 61008-1:2010/A2:2013
IEC 61008-2-1:1990
IEC 62423:2009

As shown in the Test Report Ref. No. which forms part of this Certificate

GS13118, GS13318, GS13418, GS25118, GS25318, GS25518, GS28818, CEL-1154/22-1-5, CEL-1155/22-1-4, from GS263/23 to GS273/23, SPEC22AA6279_V1, SPEC22AA6332_V1, SPEC22AA6348_V1, from SPEC22AA6402_V1 to SPEC22AA6405_V1, SPEC22AA6902_V1, SPEC22AA6905_V1, SPEC22AA6907_V1, SPEC22AA6909_V1, SPEC22AA7121_V1, SPEC22AA7124_V1, SPEC22AA7126_V1, SPEC23AA6677_V1, SPEC23AA8062_V1, SPEC23AA8063_V1, FROM GS02/23 TO GS07/23, GS395/23, GS396/23, GS01/23-M2 Head Report

This CB Test Certificate is issued by the National Certification Body

AENOR CONFÍA S.A.U.
Cl Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2025-11-07

Signature: Rafael GARCÍA MEIRO
CEO



Ref. Certif. No.

ES2673-M2-AENOR

Factory information

SCHNEIDER ELECTRIC INDIA PRIVATE LIMITED
no. 172, Poonamallee bypass road, Poonamallee
600056 CHENNAI (Tamil Nadu - India)

Deviation / Other conformity Standard information

AS/NZS 61008-1:2015

AENOR CONFÍA S.A.U.
Cl Génova, 6
ES-28004 MADRID (SPAIN)

Date: 2025-11-07

Signature: Rafael GARCÍA MEIRO
CEO

ANNEX TO CB CERTIFICATE N° ES2673-M2-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

RESIDUAL CURRENT OPERATED CIRCUIT-BREAKER (WITH TYPE F AND B) WITHOUT INTEGRAL OVERCURRENT PROTECTION FOR HOUSEHOLD AND SIMILAR USES

Trade mark: SCHNEIDER ELECTRIC

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I _{Δm}	I _m	I _{nc}	I _{Δc}	Type	Additional information
B-IDD2P2510A	2P	25A	230/240V~	10mA	50Hz	500A	500A	3000A	3000A	A	1
B-IDD2P2510A-C	2P	25A	230/240V~	10mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD2P25100AC	2P	25A	230/240V~	100mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P2530A-A	2P	25A	230/240V~	30mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD2P2530A-B	2P	25A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	A	1
B-IDD2P2530A-C	2P	25A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD2P2530AC-A	2P	25A	230/240V~	30mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P2530AC-B	2P	25A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD2P2530A-F	2P	25A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	F	1
B-IDD2P2530ASI	2P	25A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	A-SI	1
B-IDD2P25300A	2P	25A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD2P25300AC-A	2P	25A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD2P25300AC-B	2P	25A	230/240V~	300mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P25300ACS	2P	25A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	AC-S	2
B-IDD2P25300A-F	2P	25A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	F	1
B-IDD2P40100AC	2P	40A	230/240V~	100mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P4030A-A	2P	40A	230/240V~	30mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD2P4030A-B	2P	40A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	A	1
B-IDD2P4030A-C	2P	40A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD2P4030AC-A	2P	40A	230/240V~	30mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P4030AC-B	2P	40A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD2P4030A-F	2P	40A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	F	1
B-IDD2P4030ASI	2P	40A	230/240V~	30mA	50Hz	500A	500A	3000A	3000A	A-SI	1
B-IDD2P40300A	2P	40A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	A	1
B-IDD2P40300AC-A	2P	40A	230/240V~	300mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD2P40300AC-B	2P	40A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD2P40300ACS	2P	40A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	AC-S	2
B-IDD2P40300A-F	2P	40A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	F	1
B-IDD2P40300AS	2P	40A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	A-S	1
B-IDD2P63100AC	2P	63A	230/240V~	100mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD2P6330A-A	2P	63A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	A	1
B-IDD2P6330A-B	2P	63A	230/240V~	30mA	50Hz	630A	630A	3000A	3000A	A	1
B-IDD2P6330A-C	2P	63A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD2P6330AC-A	2P	63A	230/240V~	30mA	50Hz	630A	630A	3000A	3000A	AC	2
B-IDD2P6330AC-B	2P	63A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD2P6330A-F	2P	63A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	F	1
B-IDD2P63300A	2P	63A	230/240V~	300mA	50Hz	630A	630A	6000A	6000A	A	1
B-IDD2P63300AC-A	2P	63A	230/240V~	300mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD2P63300AC-B	2P	63A	230/240V~	300mA	50Hz	630A	630A	3000A	3000A	AC	2
B-IDD2P63300ACS	2P	63A	230/240V~	300mA	50Hz	630A	630A	3000A	3000A	AC-S	2
B-IDD2P63300A-F	2P	63A	230/240V~	300mA	50Hz	500A	500A	3000A	3000A	F	1
B-IDD2P63300AS	2P	63A	230/240V~	300mA	50Hz	630A	630A	3000A	3000A	A-S	1
B-IDD4P25100AC	4P	25A	400/415V~	100mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P2530A	4P	25A	400/415V~	30mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD4P2530AC-A	4P	25A	400/415V~	30mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P2530AC-B	4P	25A	400/415V~	30mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD4P25300A	4P	25A	400/415V~	300mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD4P25300AC-A	4P	25A	400/415V~	300mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD4P25300AC-B	4P	25A	400/415V~	300mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P40100AC-A	4P	40A	400/415V~	100mA	50Hz	500A	500A	3000A	3000A	AC	2

ANNEX TO CB CERTIFICATE N° ES2673-M2-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I m	I n c	I Δ c	Type	Additional information
B-IDD4P40100AC-B	4P	40A	400/415V~	100mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P4030A-A	4P	40A	400/415V~	30mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD4P4030A-B	4P	40A	400/415V~	30mA	50Hz	500A	500A	3000A	3000A	A	1
B-IDD4P4030A-C	4P	40A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD4P4030AC-A	4P	40A	400/415V~	30mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P4030AC-B	4P	40A	400/415V~	30mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD4P4030A-F	4P	40A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	F	1
B-IDD4P4030AG	4P	40A	400/415V~	30mA	50Hz	500A	500A	6000A	6000A	A-G	1
B-IDD4P40300A	4P	40A	400/415V~	300mA	50Hz	500A	500A	6000A	6000A	A	1
B-IDD4P40300AC-A	4P	40A	400/415V~	300mA	50Hz	500A	500A	6000A	6000A	AC	2
B-IDD4P40300AC-B	4P	40A	400/415V~	300mA	50Hz	500A	500A	3000A	3000A	AC	2
B-IDD4P40300A-F	4P	40A	400/415V~	300mA	50Hz	500A	500A	3000A	3000A	F	1
B-IDD4P40300AS	4P	40A	400/415V~	300mA	50Hz	500A	500A	3000A	3000A	A-S	1
B-IDD4P63100AC-A	4P	63A	400/415V~	100mA	50Hz	630A	630A	3000A	3000A	AC	2
B-IDD4P63100AC-B	4P	63A	400/415V~	100mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD4P6330A-A	4P	63A	400/415V~	30mA	50Hz	630A	630A	3000A	3000A	A	1
B-IDD4P6330A-B	4P	63A	400/415V~	30mA	50Hz	630A	630A	6000A	6000A	A	1
B-IDD4P6330A-C	4P	63A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
B-IDD4P6330AC-A	4P	63A	400/415V~	30mA	50Hz	630A	630A	3000A	3000A	AC	2
B-IDD4P6330AC-B	4P	63A	400/415V~	30mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD4P6330AC-C	4P	63A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
B-IDD4P6330A-F	4P	63A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	F	1
B-IDD4P63300A	4P	63A	400/415V~	300mA	50Hz	630A	630A	6000A	6000A	A	1
B-IDD4P63300AC-A	4P	63A	400/415V~	300mA	50Hz	630A	630A	3000A	3000A	AC	2
B-IDD4P63300AC-B	4P	63A	400/415V~	300mA	50Hz	630A	630A	6000A	6000A	AC	2
B-IDD4P63300ACS	4P	63A	400/415V~	300mA	50Hz	630A	630A	3000A	3000A	AC-S	2
B-IDD4P63300A-F	4P	63A	400/415V~	300mA	50Hz	500A	500A	3000A	3000A	F	1
B-IDD4P63300AS	4P	63A	400/415V~	300mA	50Hz	630A	630A	3000A	3000A	A-S	1
IDSB2P2530AC	2P	25A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P2530ASI	2P	25A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB2P25300AC	2P	25A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P25300ASI-S	2P	25A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB2P40100AC	2P	40A	230/240V~	100mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P4030A-A	2P	40A	230/240V~	30mA	50Hz	630A	630A	4500A	4500A	A	1
IDSB2P4030A-B	2P	40A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	A	1
IDSB2P4030A-C	2P	40A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
IDSB2P4030AC-A	2P	40A	230/240V~	30mA	50Hz	630A	630A	4500A	4500A	AC	2
IDSB2P4030AC-B	2P	40A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	AC	2
IDSB2P4030AC-C	2P	40A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P4030ASI	2P	40A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB2P40300AC	2P	40A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P40300ASI-S	2P	40A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB2P63100AC	2P	63A	230/240V~	100mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P6330A-A	2P	63A	230/240V~	30mA	50Hz	630A	630A	4500A	4500A	A	1
IDSB2P6330A-B	2P	63A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	A	1
IDSB2P6330A-C	2P	63A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A	1
IDSB2P6330AC-A	2P	63A	230/240V~	30mA	50Hz	630A	630A	4500A	4500A	AC	2
IDSB2P6330AC-B	2P	63A	230/240V~	30mA	50Hz	630A	630A	6000A	6000A	AC	2
IDSB2P6330AC-C	2P	63A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P6330ASI	2P	63A	230/240V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB2P63300AC	2P	63A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB2P63300ASI-S	2P	63A	230/240V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB2P80100AC	2P	80A	230/240V~	100mA	50Hz	800A	800A	10000A	10000A	AC	2
IDSB2P8030AC	2P	80A	230/240V~	30mA	50Hz	800A	800A	10000A	10000A	AC	2

ANNEX TO CB CERTIFICATE N° ES2673-M2-AENOR

CERTIFIED REFERENCES AND THEIR PRINCIPAL CHARACTERISTICS

Type Ref.	No. of poles	Rated current	Rated voltage	Rated residual current	Frequency	I Δ m	I m	I n c	I Δ c	Type	Additional information
IDSB2P80300AC	2P	80A	230/240V~	300mA	50Hz	800A	800A	10000A	10000A	AC	2
IDSB4P2530AC	4P	25A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P2530ASI	4P	25A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB4P2530AC	4P	25A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P2530ASI-S	4P	25A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB4P40100AC	4P	40A	400/415V~	100mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P4030AC-A	4P	40A	400/415V~	30mA	50Hz	630A	630A	4500A	4500A	AC	2
IDSB4P4030AC-B	4P	40A	400/415V~	30mA	50Hz	630A	630A	6000A	6000A	AC	2
IDSB4P4030AC-C	4P	40A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P4030ASI	4P	40A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB4P4030AC	4P	40A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P4030ASI-S	4P	40A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB4P63100AC	4P	63A	400/415V~	100mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P6330AC	4P	63A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P6330ASI	4P	63A	400/415V~	30mA	50Hz	630A	630A	10000A	10000A	A-SI	1
IDSB4P6330AC	4P	63A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	AC	2
IDSB4P6330AC-S	4P	63A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	AC-S	2
IDSB4P6330ASI-S	4P	63A	400/415V~	300mA	50Hz	630A	630A	10000A	10000A	A-SI-S	1
IDSB4P80100AC	4P	80A	400/415V~	100mA	50Hz	800A	800A	10000A	10000A	AC	2
IDSB4P8030AC	4P	80A	400/415V~	30mA	50Hz	800A	800A	10000A	10000A	AC	2
IDSB4P80300AC	4P	80A	400/415V~	300mA	50Hz	800A	800A	10000A	10000A	AC	2

Remarks:

- (1) Temperature of use -25°C/40°C
- (2) Temperature of use -5°C/40°C