


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Circuit-breakers for overcurrent protection
Name and address of the applicant	Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France
Name and address of the manufacturer	Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 Merlin Gerin Alès 16 Boulevard Charles Peguy 30319 ALES CEDEX France
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	See Appendix 1
Trademark (if any)	SCHNEIDER ELECTRIC
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	C60L
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2 See Appendix
A sample of the product was tested and found to be in conformity with	IEC 60947-2:2016, IEC 60947-2:2016/AMD1:2019
As shown in the Test Report Ref. No. which forms part of this Certificate	58156004/00, 58156003/00, 58156002/00 up to 58156002/23

This CB Test Certificate is issued by the National Certification Body

SGS Belgium N.V. - Division SGS-CEBEC
Business Riverside Park, Avenue Internationalelaan 55 Build. D, BE-1070 BRUSSEL,
Belgium

Date: 2020-03-24

Signature: Calogero Lana

Ratings:

rated operational voltage (Ue)	:	240V / 415 V / 440V
number of poles	:	1P, 1P+N, 2P, 3P & 4P
rated current (In)	:	0,5 A up to 25 A
range of instantaneous tripping overcurrent (curve)	:	B & C
nature of supply	:	AC
rated frequency	:	50/60Hz
rated service short-circuit current (Ics)	:	25 kA / 12,25 kA / 10 kA
rated short-circuit capacity (Icu)	:	50 kA / 25 kA / 20 kA
method of operation	:	independent manual operation
suitability for isolation	:	Yes
rated impulse withstand voltage (Uimp)	:	6 kV
rated insulation voltage (Ui)	:	500 V
rated ambient temperature (ta)	:	+50°C
distance metal screen to terminals	:	20 mm
distance metal screen to side circuit-breaker	:	0 mm
utilization category	:	A
method of mounting	:	DIN-rail, in enclosure
protection against electric shock	:	IP 40, under cover plate
terminals	:	pillar terminals

Product References:MCB's Series C60L:

Reference	Number of poles	Rated voltage Ue (V)	Instantaneous tripping current Ii (A)	Rated current In (A)	Product references
TI125C60L1C0.5	1P	230/400 or 240/415	8.5 x In (C)	0.5	/
TI125C60L1C0.75	1P	230/400 or 240/415	8.5 x In (C)	0.75	/
TI125C60L1C1	1P	230/400 or 240/415	8.5 x In (C)	1	M9F17101
TI125C60L1C2	1P	230/400 or 240/415	8.5 x In (C)	2	M9F17102
TI125C60L1C3	1P	230/400 or 240/415	8.5 x In (C)	3	M9F17103
TI125C60L1C4	1P	230/400 or 240/415	8.5 x In (C)	4	M9F17104
TI125C60L1C6	1P	230/400 or 240/415	8.5 x In (C)	6	M9F17106
TI125C60L1C10	1P	230/400 or 240/415	8.5 x In (C)	10	M9F17110
TI125C60L1C13	1P	230/400 or 240/415	8.5 x In (C)	13	/
TI125C60L1C16	1P	230/400 or 240/415	8.5 x In (C)	16	M9F17116
TI125C60L1C20	1P	230/400 or 240/415	8.5 x In (C)	20	M9F17120
TI125C60L1C25	1P	230/400 or 240/415	8.5 x In (C)	25	M9F17125

TI125C60LPhNC0.5	1P+N	230 or 240	8.5 x In (C)	0.5	/
TI125C60LPhNC0.75	1P+N	230 or 240	8.5 x In (C)	0.75	/
TI125C60LPhNC1	1P+N	230 or 240	8.5 x In (C)	1	/
TI125C60LPhNC2	1P+N	230 or 240	8.5 x In (C)	2	/
TI125C60LPhNC3	1P+N	230 or 240	8.5 x In (C)	3	/
TI125C60LPhNC4	1P+N	230 or 240	8.5 x In (C)	4	/
TI125C60LPhN1C6	1P+N	230 or 240	8.5 x In (C)	6	/
TI125C60LPhNC10	1P+N	230 or 240	8.5 x In (C)	10	/
TI125C60LPhNC13	1P+N	230 or 240	8.5 x In (C)	13	/
TI125C60LPhNC16	1P+N	230 or 240	8.5 x In (C)	16	/
TI125C60LPhNC20	1P+N	230 or 240	8.5 x In (C)	20	/
TI125C60LPhNC25	1P+N	230 or 240	8.5 x In (C)	25	/

TI125C60L2C0.5	2P	400, 415 or 440	8.5 x In (C)	0.5	/
TI125C60L2C0.75	2P	400, 415 or 440	8.5 x In (C)	0.75	/
TI125C60L2C1	2P	400, 415 or 440	8.5 x In (C)	1	M9F17201
TI125C60L2C2	2P	400, 415 or 440	8.5 x In (C)	2	M9F17202
TI125C60L2C3	2P	400, 415 or 440	8.5 x In (C)	3	M9F17203
TI125C60L2C4	2P	400, 415 or 440	8.5 x In (C)	4	M9F17204
TI125C60L2C6	2P	400, 415 or 440	8.5 x In (C)	6	M9F17206
TI125C60L2C10	2P	400, 415 or 440	8.5 x In (C)	10	M9F17210
TI125C60L2C13	2P	400, 415 or 440	8.5 x In (C)	13	/
TI125C60L2C16	2P	400, 415 or 440	8.5 x In (C)	16	M9F17216
TI125C60L2C20	2P	400, 415 or 440	8.5 x In (C)	20	M9F17220
TI125C60L2C25	2P	400, 415 or 440	8.5 x In (C)	25	M9F17225

Reference	Number of poles	Rated voltage Ue (V)	Instantaneous tripping current Ii (A)	Rated current In (A)	Product references
TI125C60L3C0.5	3P	400, 415 or 440	8.5 x In (C)	0.5	/
TI125C60L3C0.75	3P	400, 415 or 440	8.5 x In (C)	0.75	/
TI125C60L3C1	3P	400, 415 or 440	8.5 x In (C)	1	M9F17301
TI125C60L3C2	3P	400, 415 or 440	8.5 x In (C)	2	M9F17302
TI125C60L3C3	3P	400, 415 or 440	8.5 x In (C)	3	M9F17303
TI125C60L3C4	3P	400, 415 or 440	8.5 x In (C)	4	M9F17304
TI125C60L3C6	3P	400, 415 or 440	8.5 x In (C)	6	M9F17306
TI125C60L3C10	3P	400, 415 or 440	8.5 x In (C)	10	M9F17310
TI125C60L3C13	3P	400, 415 or 440	8.5 x In (C)	13	/
TI125C60L3C16	3P	400, 415 or 440	8.5 x In (C)	16	M9F17316
TI125C60L3C20	3P	400, 415 or 440	8.5 x In (C)	20	M9F17320
TI125C60L3C25	3P	400, 415 or 440	8.5 x In (C)	25	M9F17325

TI125C60L4C0.5	4P	400, 415 or 440	8.5 x In (C)	0.5	/
TI125C60L4C0.75	4P	400, 415 or 440	8.5 x In (C)	0.75	/
TI125C60L4C1	4P	400, 415 or 440	8.5 x In (C)	1	M9F17401
TI125C60L4C2	4P	400, 415 or 440	8.5 x In (C)	2	M9F17402
TI125C60L4C3	4P	400, 415 or 440	8.5 x In (C)	3	M9F17403
TI125C60L4C4	4P	400, 415 or 440	8.5 x In (C)	4	M9F17404
TI125C60L4C6	4P	400, 415 or 440	8.5 x In (C)	6	M9F17406
TI125C60L4C10	4P	400, 415 or 440	8.5 x In (C)	10	M9F17410
TI125C60L4C13	4P	400, 415 or 440	8.5 x In (C)	13	/
TI125C60L4C16	4P	400, 415 or 440	8.5 x In (C)	16	M9F17416
TI125C60L4C20	4P	400, 415 or 440	8.5 x In (C)	20	M9F17420
TI125C60L4C25	4P	400, 415 or 440	8.5 x In (C)	25	M9F17425

Reference	Number of poles	Rated voltage Ue (V)	Instantaneous tripping current Ii (A)	Rated current In (A)	Product references
TI125C60L1B0.5	1P	230/400 or 240/415	4 x In (B)	0.5	/
TI125C60L1B0.75	1P	230/400 or 240/415	4 x In (B)	0.75	/
TI125C60L1B1	1P	230/400 or 240/415	4 x In (B)	1	/
TI125C60L1B2	1P	230/400 or 240/415	4 x In (B)	2	/
TI125C60L1B3	1P	230/400 or 240/415	4 x In (B)	3	/
TI125C60L1B4	1P	230/400 or 240/415	4 x In (B)	4	/
TI125C60L1B6	1P	230/400 or 240/415	4 x In (B)	6	/
TI125C60L1B10	1P	230/400 or 240/415	4 x In (B)	10	/
TI125C60L1B13	1P	230/400 or 240/415	4 x In (B)	13	/
TI125C60L1B16	1P	230/400 or 240/415	4 x In (B)	16	/
TI125C60L1B20	1P	230/400 or 240/415	4 x In (B)	20	/
TI125C60L1B25	1P	230/400 or 240/415	4 x In (B)	25	/

TI125C60LPhNB0.5	1P+N	230 or 240	4 x In (B)	0.5	/
TI125C60LPhNB0.75	1P+N	230 or 240	4 x In (B)	0.75	/
TI125C60LPhNB1	1P+N	230 or 240	4 x In (B)	1	/
TI125C60LPhNB2	1P+N	230 or 240	4 x In (B)	2	/
TI125C60LPhNB3	1P+N	230 or 240	4 x In (B)	3	/
TI125C60LPhNB4	1P+N	230 or 240	4 x In (B)	4	/
TI125C60LPhN1B6	1P+N	230 or 240	4 x In (B)	6	/
TI125C60LPhNB10	1P+N	230 or 240	4 x In (B)	10	/
TI125C60LPhNB13	1P+N	230 or 240	4 x In (B)	13	/
TI125C60LPhNB16	1P+N	230 or 240	4 x In (B)	16	/
TI125C60LPhNB20	1P+N	230 or 240	4 x In (B)	20	/
TI125C60LPhNB25	1P+N	230 or 240	4 x In (B)	25	/

TI125C60L2B0.5	2P	400, 415 or 440	4 x In (B)	0.5	/
TI125C60L2B0.75	2P	400, 415 or 440	4 x In (B)	0.75	/
TI125C60L2B1	2P	400, 415 or 440	4 x In (B)	1	/
TI125C60L2B2	2P	400, 415 or 440	4 x In (B)	2	/
TI125C60L2B3	2P	400, 415 or 440	4 x In (B)	3	/
TI125C60L2B4	2P	400, 415 or 440	4 x In (B)	4	/
TI125C60L2B6	2P	400, 415 or 440	4 x In (B)	6	/
TI125C60L2B10	2P	400, 415 or 440	4 x In (B)	10	/
TI125C60L2B13	2P	400, 415 or 440	4 x In (B)	13	/
TI125C60L2B16	2P	400, 415 or 440	4 x In (B)	16	/
TI125C60L2B20	2P	400, 415 or 440	4 x In (B)	20	/
TI125C60L2B25	2P	400, 415 or 440	4 x In (B)	25	/

Reference	Number of poles	Rated voltage Ue (V)	Instantaneous tripping current Ii (A)	Rated current In (A)	Product references
TI125C60L3B0.5	3P	400, 415 or 440	4 x In (B)	0.5	/
TI125C60L3B0.75	3P	400, 415 or 440	4 x In (B)	0.75	/
TI125C60L3B1	3P	400, 415 or 440	4 x In (B)	1	/
TI125C60L3B2	3P	400, 415 or 440	4 x In (B)	2	/
TI125C60L3B3	3P	400, 415 or 440	4 x In (B)	3	/
TI125C60L3B4	3P	400, 415 or 440	4 x In (B)	4	/
TI125C60L3B6	3P	400, 415 or 440	4 x In (B)	6	/
TI125C60L3B10	3P	400, 415 or 440	4 x In (B)	10	/
TI125C60L3B13	3P	400, 415 or 440	4 x In (B)	13	/
TI125C60L3B16	3P	400, 415 or 440	4 x In (B)	16	/
TI125C60L3B20	3P	400, 415 or 440	4 x In (B)	20	/
TI125C60L3B25	3P	400, 415 or 440	4 x In (B)	25	/
TI125C60L4B0.5	4P	400, 415 or 440	4 x In (B)	0.5	/
TI125C60L4B0.75	4P	400, 415 or 440	4 x In (B)	0.75	/
TI125C60L4B1	4P	400, 415 or 440	4 x In (B)	1	/
TI125C60L4B2	4P	400, 415 or 440	4 x In (B)	2	/
TI125C60L4B3	4P	400, 415 or 440	4 x In (B)	3	/
TI125C60L4B4	4P	400, 415 or 440	4 x In (B)	4	/
TI125C60L4B6	4P	400, 415 or 440	4 x In (B)	6	/
TI125C60L4B10	4P	400, 415 or 440	4 x In (B)	10	/
TI125C60L4B13	4P	400, 415 or 440	4 x In (B)	13	/
TI125C60L4B16	4P	400, 415 or 440	4 x In (B)	16	/
TI125C60L4B20	4P	400, 415 or 440	4 x In (B)	20	/
TI125C60L4B25	4P	400, 415 or 440	4 x In (B)	25	/