



# CB TEST CERTIFICATE

Ref. Certificate No.

BE-2463

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

Issued by: SGS Belgium NV - Division SGS CEBEC

Product: Isolating switches

Applicant: Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France

Manufacturer: Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France

Factory: Schneider Electric NV/SA Dieweg, 3 1180 BRUSSEL Belgium

Rating and principal characteristics: See page 2

Trade mark (if any): SCHNEIDER ELECTRIC

Type of Manufacturer's Testing Laboratories used: WMT

Model/Type reference: Series I

Additional information: /

Sample of product tested to be in conformity with IEC: 60947-3(ed.2);am1;am2

Test Report Ref. No: 58295601/00 up to 58295601/06

This CB Test Certificate is issued by the National Certification Body:

SGS Belgium NV - Division SGS CEBEC  
Riverside Business Park Avenue Internationalelaan 55 Build. D B - 1070  
Brussels, Belgium



Signed by: Calogero LANA

Date of issue: 2010-07-14

**Ratings:**

number of poles	:	1, 2, 3 & 4
rated voltage (Un)	:	250 Vac (1P) and 415 Vac (2P, 3P & 4P)
rated current (In)	:	40 A up to 125 A
utilization category	:	AC22A
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	6 kV under frame / 4 kV
rated conditional short-circuit current	:	5 kA for all, excepted 4,5 kV for 2P 125 A
SCPD	:	fuse type gG
rated frequency	:	50 Hz / 60 Hz
degree of protection	:	IP 40 under frame / IP 20
method of actuating	:	tumbler
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

---

Product References:

References	Number of Pole	Rated current (A)	Rated Voltage (V)
15024	1	40	250V
15013	1	63	250V
15090	1	100	250V
15057	1	125	250V
15020	2	40	415V
15014	2	63	415V
15091	2	100	415V
15058	2	125	415V
15023	3	40	415V
15015	3	63	415V
15092	3	100	415V
15059	3	125	415V
15019	4	40	415V
15016	4	63	415V
15093	4	100	415V
15060	4	125	415V