



CB TEST CERTIFICATE

Ref. Certificate No.

BE-2467

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

Issued by: SGS Belgium NV - Division SGS CEBEC

Product: Isolating switches

Applicant: Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France

Manufacturer: Schneider Electric Industries SAS 31, rue Pierre Mendès France, Eybens 38050 GRENOBLE CEDEX 09 France

Factory: Schneider Electric NV/SA Dieweg, 3 1180 BRUSSEL Belgium

Rating and principal characteristics: See page 2

Trade mark (if any): CLIPSAL


Type of Manufacturer's Testing Laboratories used: WMT

Model/Type reference: 4PSW & MSW

Additional information: /

Sample of product tested to be in conformity with IEC: 60947-3(ed.2);am1;am2

Test Report Ref. No: 58295601/00 up to 58295601/06



This CB Test Certificate is issued by the National Certification Body:

SGS Belgium NV - Division SGS CEBEC
Riverside Business Park Avenue Internationalelaan 55 Build. D B - 1070
Brussels, Belgium



Signed by: Calogero LANA

Date of issue: 2010-07-14

Ratings:

number of poles	:	1, 2 & 3
rated voltage (Un)	:	240 Vac (1P) & 415 Vac (2P & 3P)
rated current (In)	:	100 A
utilization category	:	AC22A
rated insulation voltage (Ui)	:	500 V
rated impulse withstand voltage (Uimp)	:	6 kV under frame / 4 kV
rated conditional short-circuit current	:	5 kA for all, excepted 4,5 kV for 2P 100 A
SCPD	:	fuse type gG
rated frequency	:	50 Hz / 60 Hz
degree of protection	:	IP 40 under frame / IP 20
method of actuating	:	tumbler
method of application	:	semi flush-type, DIN rail
terminals	:	screw-type

Product References:

References	Number of Pole	Rated current (A)	Rated Voltage (V)	SCHNEIDER ELECTRIC References
4PSW1100	1	100	240	15057
4PSW2100	2	100	415	15058
4PSW3100	3	100	415	15059
MSW1100	1	100	240	15057
MSW2100	2	100	415	15058
MSW3100	3	100	415	15059