


CB TEST CERTIFICATE

CERTIFICAT D'ESSAI OC

Product Produit	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)
Name and address of the Applicant Nom et adresse du demandeur	SCHNEIDER ELECTRIC INDUSTRIES SAS Electropole 31 Rue Pierre Mendes France, Eybens 31 38050 GRENOBLE CEDEX 9 France
Name and address of the manufacturer Nom et adresse du fabricant	SCHNEIDER ELECTRIC INDUSTRIES SAS Electropole 31 Rue Pierre Mendes France, Eybens 31 38050 GRENOBLE CEDEX 9 France
Name and address of the factory Nom et adresse de l'usine	Schneider Electric Espagna Camino Barranquet 57 SP- 46133 Meliana, Valencia Spain
Rating and principal characteristics Valeurs nominales et caractéristiques principales	1P+N; 230 V - 240 V; In 6-10-13-16-20-25-32-40 A; Curves B-C; I Δ n 30 mA; Type A - AC; Icn 6000 A (see Test Report Ref. No. PB16S0630865-02/00)
Trademark (if any) Marque de fabrique (si elle existe)	 SCHNEIDER ELECTRIC
Type of manufacturer's Testing Laboratories used Type de programme de laboratoire d'essais constructeur	
Model / Type Ref. Réf. de type	Series P4-6000A (See Additional Sheet)
Additional information (if necessary may also be reported on page 2) Les informations complémentaires (si nécessaire, peuvent être indiquées sur la 2ème page)	-
A sample of product was tested and found to be in conformity with IEC Un échantillon de ce produit a été essayé et été considéré conforme à la CEI	61009-1(ed.3);am1;am2 61009-2-1(ed.1)
National differences / Comments Les différences nationales / Commentaires	EU Group Differences, AU, NZ
As shown in the test report Ref. No. which forms part of this certificate Comme indiqué dans le rapport d'essais numéro de référence qui constitue partie de ce certificat	PB16S0630865-02/00; from PB16S0630865-02/01 to PB16S0630865-02/18

This CB Test Certificate is issued by the National Certification Body:

Ce Certificat d'essai OC est établi par l'Organisme National de Certification

 IMQ S.p.A.
 Via Quintiliano 43 I-20138 Milano, Italy


Description of range of the RCBOs - Series P4-6000A

Reference	Curve	I_n	Type	$I_{\Delta n}$	I_{nc}	Colour of handle			
P4B6AC30/6000	B	6 A	AC	30 mA	6000 A	White or anthracite			
P4B10AC30/6000		10 A				White or anthracite			
P4B13AC30/6000		13 A				White or anthracite			
P4B16AC30/6000		16 A				White or anthracite			
P4B20AC30/6000		20 A				White or anthracite			
P4B25AC30/6000		25 A				White or anthracite			
P4B32AC30/6000		32 A				White or anthracite			
P4B40AC30/6000		40 A				White or anthracite			
P4B6A30/6000		6 A	A			White or anthracite			
P4B10A30/6000		10 A				White or anthracite			
P4B13A30/6000		13 A				White or anthracite			
P4B16A30/6000		16 A				White or anthracite			
P4B20A30/6000		20 A				White or anthracite			
P4B25A30/6000		25 A				White or anthracite			
P4B32A30/6000		32 A				White or anthracite			
P4B40A30/6000		40 A				White or anthracite			
P4C6AC30/6000		C	6 A			AC	30 mA	6000 A	White or anthracite
P4C10AC30/6000			10 A						White or anthracite
P4C13AC30/6000			13 A						White or anthracite
P4C16AC30/6000			16 A						White or anthracite
P4C20AC30/6000	20 A		White or anthracite						
P4C25AC30/6000	25 A		White or anthracite						
P4C32AC30/6000	32 A		White or anthracite						
P4C40AC30/6000	40 A		White or anthracite						
P4C6A30/6000	6 A		A	White or anthracite					
P4C10A30/6000	10 A			White or anthracite					
P4C13A30/6000	13 A			White or anthracite					
P4C16A30/6000	16 A			White or anthracite					
P4C20A30/6000	20 A			White or anthracite					
P4C25A30/6000	25 A			White or anthracite					
P4C32A30/6000	32 A			White or anthracite					
P4C40A30/6000	40 A			White or anthracite					
P4C25Asi30/6000	25 A		A si ⁽¹⁾	White or anthracite					
P4C32Asi30/6000	32 A			White or anthracite					
P4C40Asi30/6000	40 A			White or anthracite					

⁽¹⁾ – A si-type RCBOs are A-type RCBOs having an intentional short-time delay