

CERTIFICATE

Issued to:
Applicant:
Schneider Electric Industries SAS
Electropole 38EQI
31 rue Pierre Mendes
38050 Grenoble Cedex 9, France

Manufacturer/Licensee:
Schneider Electric Industries SAS
Electropole 38EQI
31 rue Pierre Mendes
38050 Grenoble Cedex 9, France

Products : Surge protective devices
Trade name : SCHNEIDER ELECTRIC
Types/models : iQuick PRD 40r ...

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61643-11:2012; IEC 61643-11:2011;
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2115383

DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.


This certificate is issued on: 12 February 2015 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 2170494.03

DEKRA Certification B.V.



drs. G.J. Zoetbrood
Managing Director



F.S. Strikwerda
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Products	: Surge protective devices
Trade name	: SCHNEIDER ELECTRIC
Types	: iQuick PRD 40r 2P iQuick PRD 40r 3P iQuick PRD 40r 4P iQuickPRD Cartridge C 40-350 iQuickPRD Cartridge C Neutral-350
SPD type (and test class)	: Type 2 (II)
Short-circuit current rating (I_{scsr})	: 20 kA

Product data - type iQuick PRD 40r 2P

Commercial reference	: A9L16292
Number of poles	: 2-pole
Maximum continuous operating voltage (U_c)	: L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	: 20 kA
Maximum discharge current (I_{max})	: 40 kA
Voltage protection level (U_p)	: L/N: 2,5 kV N/PE 1,7 kV

Product data - type iQuick PRD 40r 3P

Commercial reference	: A9L16293
Number of poles	: 3-pole
Maximum continuous operating voltage (U_c)	: L/PEN: 350 Vac
Nominal discharge current (I_n)	: 20 kA
Maximum discharge current (I_{max})	: 40 kA
Voltage protection level (U_p)	: L/PEN: 2,5 kV

Product data - type iQuick PRD 40r 4P

Commercial reference	: A9L16294
Number of poles	: 4-pole
Maximum continuous operating voltage (U_c)	: L/N: 350 Vac N/PE: 264 Vac
Nominal discharge current (I_n)	: 20 kA
Maximum discharge current (I_{max})	: 40 kA
Voltage protection level (U_p)	: L/N: 2,5 kV N/PE: 1,7 kV

Product data - type iQuickPRD Cartridge C 40-350

Commercial reference	: A9L16310
Cartridge	: for iQuick PRD 40r for L-(PE)N protection

Product data - type iQuickPRD Cartridge C Neutral-350

Commercial reference	: A9L16313
Cartridge	: for iQuick PRD ... for N-PE protection

TESTS**Test requirements**

EN 61643-11:2012

IEC 61643-11:2011

Test result

The test results are laid down in DEKRA test file 2170494.03.

Remarks

This certificate replaces certificate 2170494.02 issued on 29 August 2014.

Conclusion

The examination proved that all test requirements were met.

Tested by : C.H.J. Addink

A blue ink signature of C.H.J. Addink, consisting of a stylized 'A' followed by a horizontal line.

Checked by : C.C. Burger

A blue ink signature of C.C. Burger, featuring a large, bold 'B' followed by a horizontal line.**Factory locations**

Schneider Electric Hungaria, Villamossagi Zrt.
Hock János út. 55, 8900, Zalaegerszeg
Hungary