


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product	Residual current operated circuit-breakers with integral overcurrent protection for household and similar uses (RCBOs)
Name and address of the applicant	SCHNEIDER ELECTRIC INDUSTRIES SAS 31 rue Pierre Mendès France, Eybens F-38050 Grenoble Cedex 9 France
Name and address of the manufacturer	GEWISS S.p.A. Via A. Volta, 1 24069 Cenate Sotto (BG) Italy
Name and address of the factory	<input type="checkbox"/> Additional information on page 2 GEWISS PORTUGAL Indústria del Material Eléctrico, Unipessoal, Lda Zona Industrial 2a fase - Bustelo 4560-043 Penafiel Portugal
<i>Note: When more than one factory, please report on page 2</i>	
Ratings and principal characteristics	2P or 3P – Un = 230 V – Curve B or C – In = 10, 13, 15, 16, 20, 25, or 32 A type A, A SI or AC – IΔn = 30 or 300 mA – Icn = 10000 A – IΔm = 4500 A (see also Additional Sheet and pages 6, 9 and 10 of Test Report PB20-0055075-03-00)
Trademark (if any)	 Schneider Electric
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	Series Acti9 iC60 (see also Additional Sheet and pages 9 and 10 of Test Report PB20-0055075-03-00)
Additional information (if necessary may also be reported on page 2)	<input type="checkbox"/> Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 61009-1:2010, IEC 61009-1:2010/AMD1:2012, IEC 61009-1:2010/AMD2:2013, IEC 61009-2-1:1991  National differences: EU Group Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	PB20-0055075-03-00 and from PB20-0055075-03-01 to PB20-0055075-03-22

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.  
Via Quintiliano 43, IT-20138 Milano, Italy

**Description of the RCBOs series Acti9 iC60 ( $I_{cn} = 10000 \text{ A}$ ) – continues on page 2**

Type reference	Number of poles	Curve	Rated current ( $I_n$ )	Type	Rated residual current ( $I_{\Delta n}$ )	Energy limiting class (1)
A9D37210	2P	B	10 A	A	30 mA	Class 3
A9D37213	2P	B	13 A	A	30 mA	Class 3
A9D37216	2P	B	16 A	A	30 mA	Class 3
A9D37220	2P	B	20 A	A	30 mA	Class 3
A9D37225	2P	B	25 A	A	30 mA	Class 3
A9D37232	2P	B	32 A	A	30 mA	Class 3
A9D50210	2P	C	10 A	AC	300 mA	Class 3
A9D50216	2P	C	16 A	AC	300 mA	Class 3
A9D50220	2P	C	20 A	AC	300 mA	Class 3
A9D50225	2P	C	25 A	AC	300 mA	Class 3
A9D50232	2P	C	32 A	AC	300 mA	Class 3
A9D07210	2P	C	10 A	AC	30 mA	Class 3
A9D07216	2P	C	16 A	AC	30 mA	Class 3
A9D07220	2P	C	20 A	AC	30 mA	Class 3
A9D07225	2P	C	25 A	AC	30 mA	Class 3
A9D07232	2P	C	32 A	AC	30 mA	Class 3
A9D17210	2P	C	10 A	A	30 mA	Class 3
A9D17213	2P	C	13 A	A	30 mA	Class 3
A9D17216	2P	C	16 A	A	30 mA	Class 3
A9D17220	2P	C	20 A	A	30 mA	Class 3
A9D17225	2P	C	25 A	A	30 mA	Class 3
A9D17232	2P	C	32 A	A	30 mA	Class 3
A9D27210	2P	C	10 A	A SI (1)	30 mA	Class 3
A9D27213	2P	C	13 A	A SI (1)	30 mA	Class 3
A9D27216	2P	C	16 A	A SI (1)	30 mA	Class 3
A9D27220	2P	C	20 A	A SI (1)	30 mA	Class 3
A9D27225	2P	C	25 A	A SI (1)	30 mA	Class 3
A9D27232	2P	C	32 A	A SI (1)	30 mA	Class 3
A9D54210	2P	C	10 A	A	300 mA	Class 3
A9D54216	2P	C	16 A	A	300 mA	Class 3

**Description of the RCBOs series Acti9 iC60 ( $I_{cn} = 10000 \text{ A}$ ) – continued from page 1**

Type reference	Number of poles	Curve	Rated current ( $I_n$ )	Type	Rated residual current ( $I_{\Delta n}$ )	Energy limiting class (1)
A9D54220	2P	C	20 A	A	300 mA	Class 3
A9D54225	2P	C	25 A	A	300 mA	Class 3
A9D54232	2P	C	32 A	A	300 mA	Class 3
A9D47210	2P	B	10 A	A SI (2)	30 mA	Class 3
A9D47213	2P	B	13 A	A SI (2)	30 mA	Class 3
A9D47216	2P	B	16 A	A SI (2)	30 mA	Class 3
A9D47220	2P	B	20 A	A SI (2)	30 mA	Class 3
A9D47225	2P	B	25 A	A SI (2)	30 mA	Class 3
A9D47232	2P	B	32 A	A SI (2)	30 mA	Class 3
A9D34215	2P	B	15 A	A	30 mA	Class 3
A9D34220 (3)	2P	B	20 A	A	30 mA	Class 3
A9D14215	2P	C	15 A	A	30 mA	Class 3
A9D14220 (4)	2P	C	20 A	A	30 mA	Class 3
A9D17310	3P	C	10 A	A	30 mA	Class 3
A9D17313	3P	C	13 A	A	30 mA	Class 3
A9D17316	3P	C	16 A	A	30 mA	Class 3
A9D17320	3P	C	20 A	A	30 mA	Class 1
A9D17325	3P	C	25 A	A	30 mA	Class 1
A9D17332	3P	C	32 A	A	30 mA	Class 1

(1) – According to EN 61009-1:2012 + A1:2014 + A2:2014 + A11:2015 + A12:2016 and EN 61009-2-1:1994 + A11:1998

(2) – “A SI”-type residual current units are A-type residual current units having an intentional short-time delay

(3) – Identical to the RCBO type reference A9D37220 but without the marking “EN 61009-1  $I_{\Delta m}=6000\text{A}$ ” on the side

(4) – Identical to the RCBO type reference A9D17220 but without the marking “EN 61009-1  $I_{\Delta m}=6000\text{A}$ ” on the side