



Ref. Certif. No.

FR_718789

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switches for household and similar fixed electrical installations
Smart Contactor (Electronic remote-controlled switch)

Name and address of the applicant

SCHNEIDER ELECTRIC INDUSTRIES SAS
31 rue Pierre Mendès France, Eybens
38050 GRENOBLE Cedex 9
FRANCE

Name and address of the manufacturer

DELTA DORE
Le Vieux Chêne
35270 Bonnemain
FRANCE

Name and address of the factory

DELTA DORE
Le Vieux Chêne
35270 Bonnemain
FRANCE

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

20AX / 230V ~
See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

A9C1B120

Additional information (if necessary may also be reported on page 2)

/

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017
IEC 60669-2-1:2021

As shown in the Test Report Ref. No. which forms part of this Certificate

TR N° 16965815-783360

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/03/2024



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre 5149836617
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

Signature: Julien GAUTHIER
Certification Officer

ANNEX


Ratings and main characteristics:

Type of electronic switch and its function (examples given in Annex AA)	Electronically operated mechanical switching device
Pattern number	1
Contact opening (gap)	micro-gap
Degree of protection	IP20
Method of actuating	push-button / other external influences
Method of mounting	panel-type
Method of installation	Design A
Type of terminals	screw-type for rigid and flexible conductors
Sortie par câble souple / Flexible cable outlet :	without
Rated current (A) - Rated load (VA or W)	20AX
Minimum current (A) - Minimum load (VA or W) :	/
Kind of load controlled	fluorescent lamps - motors - declared load
Type of control mechanism.....	electrical
Rated voltage (V)	230 V~
Rated frequency (Hz)	50Hz
Characteristics of fuses	/



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/03/2024



Signature: *Julien Gauthier*
Julien GAUTHIER
 Certification Officer